



TE Connectivity

## CUSTOMER DATA

PART NO.


1432868-1

SHT. 1  
OF 2

|                      |                        |                  |              |
|----------------------|------------------------|------------------|--------------|
| DRAWN<br>N.TABAKOVIC | APPROVAL<br>L. BENNETT | DATE<br>10-24-06 | SCALE<br>1:1 |
|----------------------|------------------------|------------------|--------------|

CUSTOMER  
TE\_CONNECTIVITY\_STANDARD

|           |        |   |     |
|-----------|--------|---|-----|
| TOLERANCE | 0.X    | = | +/- |
| UNLESS    | 0.XX   | = | +/- |
| SPECIFIED | 0.XXX  | = | +/- |
| OTHERWISE | ANGLES | = | +/- |



DO NOT SCALE THIS DRAWING

## CHANGES

| REV. | DATE    | CO                       | APP.   |
|------|---------|--------------------------|--------|
| B1   | 29MAR11 | REVISED PERECO-11-005139 | RK/HMR |

ELECTRICAL CHARACTERISTICS: (ALL DATA APPLIES @ 23°C UNLESS OTHERWISE SPECIFIED)COIL DATA:

|                    |                                  |
|--------------------|----------------------------------|
| NOMINAL VOLTAGE:   | 12 VDC                           |
| OPERATE VOLTAGE:   | 7.8 VDC MAXIMUM                  |
| RELEASE VOLTAGE:   | 1.2 VDC MINIMUM                  |
| COIL RESISTANCE:   | 90 OHMS +/- 10%                  |
| OPERATE TIME:      | 8 mSEC. MAXIMUM EXCLUDING BOUNCE |
| RELEASE TIME:      | 5 mSEC. MAXIMUM EXCLUDING BOUNCE |
| TEMPERATURE RANGE: | OPERATING -40°C TO +85°C         |

CONTACT DATA: (CONTACT DATA IS FORMATTED N.O./N.C.)

|                             |                                                                                                  |
|-----------------------------|--------------------------------------------------------------------------------------------------|
| CONTACT ARRANGEMENT:        | 1 FORM C (SPDT)                                                                                  |
| CONTACT MATERIAL:           | AgSnO (SILVER TIN-OXIDE)                                                                         |
| CONTACT MILLIVOLT DROP:     | 200mv @ 35A ON N.O. CONTACTS (AFTER SWITCHING)<br>250mv @ 20A ON N.C. CONTACTS (AFTER SWITCHING) |
| MAXIMUM MAKE CURRENT:       | 90A/30A (LAMP) @ 16 VDC                                                                          |
| MAXIMUM BREAK CURRENT:      | 40A/30A @ 16 VDC RESISTIVE                                                                       |
| MAXIMUM CONTINUOUS CURRENT: | 40A/30A @ 23°C , 35A/20A @ 85°C                                                                  |
| INITIAL BREAKDOWN CURRENT   | 500V RMS CONTACTS TO COIL                                                                        |

|                |                                                                     |
|----------------|---------------------------------------------------------------------|
| EXPECTED LIFE: | 100,000 OPERATIONS, 40 A, 14 VDC RESISTIVE ON NORMALLY OPEN CONTACT |
|----------------|---------------------------------------------------------------------|

MECHANICAL CHARACTERISTICS:

|                |                                        |
|----------------|----------------------------------------|
| EXPECTED LIFE: | 10 MILLION OPERATIONS, NO CONTACT LOAD |
| TERMINALS      | PLATED BRASS                           |
| ENCLOSURE:     | DUST COVER                             |



TE Connectivity

CUSTOMER DATA

PART NO.  
1432868-1

SHT. 2  
OF 2

DRAWN  
N.TABAKOVIC

APPROVAL  
L.BENNETT

DATE  
10-24-06

SCALE  
1:1


CUSTOMER  
TE\_CONNECTIVITY\_STANDARD

TOLERANCE  
UNLESS  
SPECIFIED  
OTHERWISE

0.X  
0.XX  
0.XXX  
ANGLES

=  
=  
=  
=

+/-  
+/-  
+/-  
+/-




DO NOT SCALE THIS DRAWING




REV B1

MILLIMETERS


MARKING TO INCLUDE:  
TYCO ELECTRONICS NAME, TE CONNECTIVITY PART NUMBER, SCHEMATIC,  
COIL VOLTAGE, COUNTRY OF ORIGIN, AND DATE CODE



K ASPECT



\* TERMINAL LOCATIONS  
APPLY AT THE BASE  
OF THE TERMINALS



SCHEMATIC DRAWING  
(BOTTOM VIEW)