



TE Connectivity
Swindon. UK

SPECIFICATION:
THIS ISSUE:
DATE:
REPLACES:

RW-2500-2
ISSUE 2
October 2011
Issue 1

TMS MARKER SLEEVES (TMS)

TMS Markers are for use in permanent marking applications up to 135°C, and are especially designed for applications in which flexibility and flame retardancy are important criteria.

1. SCOPE

This specification sheet, when used with RW-2500, defines the product characteristics and performance of TE Connectivity TMS Marker Sleeves.

2. REQUIREMENTS

2.1 MATERIAL

The sleeving shall be fabricated from irradiated, thermally-stabilized, modified polyolefin compound. It shall be homogeneous and essentially free from flaws, defects, pinholes, bubbles, seams, cracks or inclusions.

2.2 COLOR

The sleeves shall be supplied in white, unless otherwise specified.


2.3 PROPERTIES

The sleeves shall meet the requirements of Table 3.

2.4 FORM

The sleeves shall be cut lengths in accordance with Table 1, mounted on bandoliers suitable for automatic marking. Each sleeve can accommodate up to and including 18 typed characters per line for 1.50-inch length, and up to and including 21 typed characters per line for 1.75-inch length, 12 pitch.

While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this specification, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.



See Table 1

Dimensions are in inches

Figure 1

While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this specification, TE does not guarantee that it is error-free. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

If this document is printed it becomes uncontrolled.

TABLE 1
Sleeve Dimensions

Product Description	AS SUPPLIED				AS RECOVERED			
	Minimum Inside Diameter		Minimum Marking Length		Maximum Inside Diameter		Wall Thickness	
	inch	mm	inch	mm	inch	mm	inch	mm
TMS-3/32-1.50	0.093	2.36	1.50	38.10	0.046	1.17	0.023 ± .003	0.58 ± .08
TMS-1/8-1.50	0.125	3.17	1.50	38.10	0.062	1.57	0.023 ± .003	0.58 ± .08
TMS-1/8-OX-1.50	0.125	3.17	1.50	38.10	0.046	1.17	0.027 ± .003	0.69 ± .08
TMS-3/16-1.50	0.187	4.74	1.50	38.10	0.093	2.36	0.025 ± .003	0.64 ± .08
TMS-3/16-OX-1.50	0.187	4.74	1.50	38.10	0.062	1.57	0.029 ± .003	0.74 ± .08
TMS-1/4-1.50	0.250	6.35	1.50	38.10	0.125	3.17	0.025 ± .003	0.64 ± .08
TMS-1/4-OX-1.50	0.250	6.35	1.50	38.10	0.093	2.36	0.029 ± .003	0.74 ± .08
TMS-3/8-1.50	0.375	9.50	1.50	38.10	0.187	4.75	0.025 ± .003	0.64 ± .08
TMS-3/8-OX-1.50	0.375	9.50	1.70	43.18	0.125	3.17	0.028 ± .003	0.71 ± .08
TMS-1/2-1.50	0.475	12.07	1.60	40.64	0.250	6.35	0.025 ± .003	0.64 ± .08
TMS-3/32-1.75	0.093	2.36	1.75	44.45	0.046	1.17	0.023 ± .003	0.58 ± .08
TMS-1/8-1.75	0.125	3.17	1.75	44.45	0.062	1.57	0.023 ± .003	0.58 ± .08
TMS-1/8-OX-1.75	0.125	3.17	1.75	44.45	0.046	1.17	0.027 ± .003	0.69 ± .08
TMS-3/16-1.75	0.187	4.74	1.75	44.45	0.093	2.36	0.025 ± .003	0.64 ± .08
TMS-3/16-OX-1.75	0.187	4.74	1.75	44.45	0.062	1.57	0.029 ± .003	0.74 ± .08
TMS-1/4-1.75	0.250	6.35	1.75	44.45	0.125	3.17	0.025 ± .003	0.64 ± .08
TMS-1/4-OX-1.75	0.250	6.35	1.75	44.45	0.093	2.36	0.029 ± .003	0.74 ± .08
TMS-3/8-1.75	0.375	9.50	1.75	44.45	0.187	4.75	0.025 ± .003	0.64 ± .08
TMS-3/4	0.710	18.00	1.65	42.00	0.375	9.53	0.030 ± .004	0.76 ± .10
TMS-1-1/2	1.500	38.00	1.65	42.00	0.610	15.50	0.045 ± .004	1.15 ± .10

TABLE 2
Test Mandrel Dimensions for
Heat Shock, Heat Aging and
Low Temperature Flexibility

PRODUCT SIZE	MANDREL DIAMETER	
	inch	mm
3/32 through 3/16	5/16	7.9
1/4 through 1-1/2	3/4	19.0

While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this specification, TE does not guarantee that it is error-free or make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

If this document is printed it becomes uncontrolled.

TABLE 3
Requirements

PROPERTY	UNIT	REQUIREMENT	TEST METHOD
PHYSICAL			
Dimensions	Inches	In accordance with Table 1	
Dimensional Recovery 3 min. at 200°C (392°F)	Inches	In accordance with Table 1	Section 4.3.1.1 ASTM D 2671
Longitudinal Change 3 min. at 200°C (392°F)	Percent	0 to -10	
Tensile Strength	MPa (psi)	10.3 (1500) minimum	Section 4.3.2.1 ASTM D 2671 2 inches/minute
Ultimate Elongation	Percent	200 minimum	
Specific Gravity	---	1.35 maximum	Section 4.3.3 ASTM D 2671
Low Temperature Flexibility 4 hours at -55°C (-67°F)	---	No cracking	Section 4.3.5.1
Heat Shock 4 hours at 250°C (482°F) Followed by tests for: Print Performance	---	No dripping, flowing, or cracking	Section 4.3.6.1
	---	Legible	Section 4.3.9.2
Heat Aging 336 hours at 175°C (347°F) Followed by tests for: Print Performance	---	No cracking	Section 4.3.7.1
	---	Legible	Section 4.3.9.2
Copper Contact Corrosion 16 hours at 175°C (347°F)	---	No pitting or blackening of core	Section 4.3.14.1
Pull-Off Force: Size: 3/32 thru 1/4 Size: 3/8 and 1/2 Size: 3/4 and 1-1/2	N (Pounds)	22 (5.0) maximum	Section 4.3.8
	N (Pounds)	26 (6.0) maximum	
	N (Pounds)	23 (5.2) maximum	
Print Performance (SAE-AS-81531) (MIL-STD-202)			
	Rubs	50 minimum, legible	Section 4.3.9.2
	Strokes	50 minimum, legible	Section 4.3.9.3
ELECTRICAL			
Dielectric Strength	kV/mm (V/mil)	19.7 (500) minimum	Section 4.3.11.1 ASTM D 2671
Volume Resistivity	ohm-cm	10 ¹⁴ minimum	Section 4.3.12.1 ASTM D 2671
CHEMICAL			
Corrosive Effect 16 hours at 175°C (347°F)	---	Non Corrosive	Section 4.3.13.1 ASTM D 2671

While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this specification, TE does not guarantee that it is error-free or make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

If this document is printed it becomes uncontrolled.

TABLE 3 (Continued)
Requirements

PROPERTY	UNIT	REQUIREMENT	TEST METHOD
Flammability (FED-STD-228)	---	Burn time shall not exceed one minute, and not more than 25% of indicator flag shall be burned or charred. No dripping or flowing.	Section 4.3.15.3
Fungus Resistance	---	Rating of 1 or less	ASTM G 21
Water Absorption 24 hours at 23°C (73°F)	Percent	0.5 maximum	ASTM D 570
Fluid Resistance 24 hours at 23°C (73°F) JP-8 Fuel (MIL-DTL-83133) Skydrol 500 B4 Hydraulic Fluid (MIL PRF 5606) Aviation Gasoline (100/130) Lubricating Oil(MIL PRF 7808) Salt Water (5% salt solution) Anti-icing Fluid (SAE AS 8243) Followed by tests for: Mark Adherence SAE-AS-81531	---	---	Section 4.3.19.1
	---	Legible	Section 4.3.9.2

While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this specification, TE does not guarantee that it is error-free or make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

If this document is printed it becomes uncontrolled.