

LOC	DIST	REVISIONS				
AA	22	P	LTR	DESCRIPTION	DATE	DWN
			A	REV PER EC 0S11-0201-04	15JUN2005	GA

- 1

MATERIAL:HOUSING-HTN NYLON, BLACK, IR
REFLOW COMPATIBLE, UL 94V-0.
TERMINALS-.013[0.33] THICK PHOS BRONZE
PLATED WITH .000050[1.27μm] MINIMUM THICK
HARD GOLD IN LOCALIZED AREA AND .000150
[3.81μm] MINIMUM THICK MATTE TIN IN SOLDER
AREA OVER .000050[1.27μm] MINIMUM THICK
NICKEL UNDERPLATE.
- 2




JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.
3.

ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS
OTHERWISE SPECIFIED.
4.


ALL DIMENSIONS SHOWN IN BRACKETS [] ARE
IN MILLIMETERS.
- 5

SHORT IS REMOVED BY INSERTION OF MODULAR
PLUG.
- 6

USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN
PRODUCING THESE PCB HOLES.



SUGGESTED PANEL CUTOUT



SHORTING FEATURE

SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE

5557788-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ATTADIA - 15JUN2005	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: inches [mm]		CHK J. WESTMAN 15JUN2005				
		APVD S. FLICKINGER 15JUN2005	NAME MODULAR JACK ASSEMBLY, 8 POSITION RIGHT ANGLE,LOW PROFILE,SHORTING			
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.254] 3 PLC ± .005[0.127] 4 PLC ± - ANGLES ± - FINISH	PRODUCT SPEC 108-1163 APPLICATION SPEC 114-2048			
MATERIAL		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=5557788	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV A