


Between Series Adapters, Custom Configurations Available



8

Between Series Adapters solve a variety of connection problems where connectors of different types could ordinarily not be mated together. Each adapter has a different type coupling at each end allowing for a wide variety of interconnections

to fit almost all interconnection situations. All adapters are constructed of machined brass and are nickel plated.

| Stock No. | Mfr.'s Type | Fig. | Description                 | EACH  |       |         |
|-----------|-------------|------|-----------------------------|-------|-------|---------|
|           |             |      |                             | 1-24  | 25-99 | 100-499 |
| 202-0605  | 1303505     | 1    | N Male to BNC Male          | 15.02 | 12.87 | 10.73   |
| 202-0610  | 1313505     | 2    | N Male to BNC Female        | 5.46  | 4.68  | 3.90    |
| 202-0615  | 1323505     | 3    | N Female to BNC Female      | 6.63  | 5.68  | 4.74    |
| 202-0620  | 1307505     | 4    | N Male to UHF Male          | 5.46  | 4.68  | 3.90    |
| 202-0625  | 1317505     | 5    | N Male to UHF Female        | 7.41  | 6.38  | 5.29    |
| 202-0630  | 1327505     | 6    | N Female to UHF Female      | 7.61  | 6.52  | 5.43    |
| 202-0635  | 7311505     | 7    | UHF Male to N Female        | 6.01  | 5.15  | 4.29    |
| 202-0640  | 1308505     | 8    | N Male to F Male            | 5.01  | 4.42  | 4.02    |
| 202-0645  | 1318505     | 9    | N Male to F Female          | 6.76  | 6.09  | 5.53    |
| 202-0650  | 1328505     | 10   | N Female to F Female        | 5.42  | 4.65  | 3.87    |
| 202-0655  | 1309505     | 11   | N Male to SMA Male          | 6.01  | 5.15  | 4.29    |
| 202-0660  | 1319505     | 12   | N Male to SMA Female        | 5.65  | 4.85  | 4.04    |
| 202-0665  | 1329505     | 13   | N Female to SMA Female      | 5.65  | 4.85  | 4.04    |
| 202-0670  | 9311505     | 14   | SMA Male to N Female        | 6.83  | 5.85  | 4.88    |
| 202-0675  | 1325505     | 15   | N Female to TNC Female      | 5.07  | 4.35  | 3.62    |
| 202-0680  | 5311505     | 16   | TNC Male to N Female        | 5.07  | 4.35  | 3.62    |
| 202-0685  | 3315505     | 17   | BNC Male to TNC Female      | 3.48  | 3.08  | 2.79    |
| 202-0690  | 3325505     | 18   | BNC Female to TNC Female    | 4.68  | 4.01  | 3.34    |
| 202-0695  | 5313505     | 19   | TNC Male to BNC Female      | 3.86  | 3.31  | 2.76    |
| 202-0700  | 3316505     | 20   | BNC Male to Mini-UHF Female | 3.51  | 3.01  | 2.51    |
| 202-0705  | 6313505     | 21   | Mini-UHF Male to BNC Female | 2.73  | 2.34  | 1.95    |
| 202-0710  | 3307505     | 22   | BNC Male to UHF Male        | 4.08  | 3.51  | 3.27    |
| 202-0715  | 3317505     | 23   | BNC Male to UHF Female      | 3.71  | 3.18  | 2.65    |
| 202-0720  | 3327505     | 24   | BNC Female to UHF Female    | 4.10  | 3.51  | 2.93    |
| 202-0725  | 7313505     | 25   | UHF Male to BNC Female      | 5.46  | 4.68  | 3.90    |
| 202-0730  | 3318505     | 26   | BNC Male to F Female        | 3.12  | 2.67  | 2.23    |
| 202-0735  | 3328505     | 27   | BNC Female to F Female      | 3.43  | 2.94  | 2.45    |

| Stock No. | Mfr.'s Type | Fig. | Description                 | EACH  |       |         |
|-----------|-------------|------|-----------------------------|-------|-------|---------|
|           |             |      |                             | 1-24  | 25-99 | 100-499 |
| 202-0740  | 8313505     | 28   | F Male to BNC Female        | 2.93  | 2.51  | 2.09    |
| 202-0745  | 3309505     | 29   | BNC Male to SMA Male        | 10.14 | 8.69  | 7.24    |
| 202-0750  | 3319505     | 30   | BNC Male to SMA Female      | 5.85  | 5.01  | 4.18    |
| 202-0755  | 9313505     | 31   | SMA Male to BNC Female      | 7.80  | 6.69  | 5.57    |
| 202-0760  | 5316505     | 32   | TNC Male to Mini-UHF Female | 2.85  | 2.44  | 2.03    |
| 202-0765  | 5317505     | 33   | TNC Male to UHF Female      | 3.32  | 2.84  | 2.37    |
| 202-0770  | 5309505     | 34   | TNC Male to SMA Male        | 10.14 | 8.69  | 7.24    |
| 202-0775  | 5319505     | 35   | TNC Male to SMA Female      | 10.14 | 8.69  | 7.24    |
| 202-0780  | 5329505     | 36   | TNC Female to SMA Female    | 5.27  | 4.51  | 3.76    |
| 202-0785  | 9315505     | 37   | SMA Male to TNC Female      | 5.07  | 4.35  | 3.62    |
| 202-0790  | 6311505     | 38   | Mini-UHF Male to N Female   | 4.48  | 3.84  | 3.20    |
| 202-0795  | 6317505     | 39   | Mini-UHF Male to UHF Female | 3.74  | 3.21  | 2.67    |
| 202-0800  | 7316505     | 40   | UHF Male to Mini-UHF Female | 6.47  | 5.55  | 4.62    |
| 202-0805  | 9309505     | 41   | SMA Male to Mini-UHF Male   | 5.27  | 4.51  | 3.76    |
| 202-0810  | 9316505     | 42   | SMA Male to Mini-UHF Female | 5.93  | 5.08  | 4.23    |
| 202-0815  | 7309505     | 43   | UHF Male to SMA Male        | 5.27  | 4.51  | 3.76    |
| 202-0820  | 7319505     | 44   | UHF Female to SMA Male      | 5.27  | 4.51  | 3.76    |
| 202-0825  | 9317505     | 45   | SMA Female to UHF Male      | 5.46  | 4.68  | 3.90    |
| 202-0830  | R0842       | 46   | RCA Male to BNC Male        | 3.59  | 3.08  | 2.56    |
| 202-0835  | R0843       | 47   | RCA Female to BNC Male      | 2.11  | 1.81  | 1.50    |
| 202-0840  | R0844       | 48   | RCA Male to BNC Female      | 2.30  | 1.97  | 1.65    |
| 202-0845  | R0847       | 49   | RCA Male to F Male          | 2.22  | 1.91  | 1.59    |
| 202-0850  | R0849       | 50   | RCA Male to F Female        | 1.95  | 1.67  | 1.39    |
| 202-0855  | R0851       | 51   | RCA Female to F Male        | 1.76  | 1.50  | 1.25    |
| 202-0860  | R0811       | 52   | RCA Female to UHF Male      | 2.93  | 2.51  | 2.09    |
| 202-0865  | R0822       | 53   | RCA Male to UHF Female      | 2.54  | 2.17  | 1.81    |




RF Adapter Kit

ADPT1 Kit contains two each of the male and female types N, BNC, TNC SMA, UHF, Mini UHF and six universal adapters to attach interfaces, to make over 500 combinations of adapters. The ADPT2 Kit additionally contains broadcast grade F and RCA Types, plus 8 universal adapters. All components in this kit are gold plated.

|                                                      |      |        |
|------------------------------------------------------|------|--------|
| 202-0600. ADPT1. RF Universal Adapter Kit. 1-24..... | EACH | 132.60 |
| 25-99.....                                           | EACH | 113.66 |
| 100-499.....                                         | EACH | 94.71  |
| 202-0601. ADPT2. RF Universal Adapter Kit. 1-24..... | EACH | 161.85 |
| 25-99.....                                           | EACH | 138.73 |
| 100-499.....                                         | EACH | 115.61 |

RJ45 Category 5 Plugs and Boots

Category 5 Liner Plugs are supplied with an insertable liner for the conductors. The separated conductors are inserted into the liner, cut off squarely at bottom, inserted into RJ45 plug, then perfectly crimped. CXB300 series boots finish the installation with a color-coded strain relief assuring optimum performance. Kits and special packaging available.




| Stock No. | Mfr.'s Type | Description                                                       | EACH  |       |         |
|-----------|-------------|-------------------------------------------------------------------|-------|-------|---------|
|           |             |                                                                   | 1-24  | 25-99 | 100-499 |
| 202-0998  | 300166      | 6P6C Plug for Round Twisted Pair, Solid                           | .23   | .20   | .17     |
| 202-1000  | 300568      | 8P8C Category 5 Plug for Round Twisted Pair, Solid                | .57   | .49   | .41     |
| 202-1002  | 300568L     | 8P8C Category 5 Liner Plug for Round Twisted Pair, Solid          | 1.25  | 1.07  | .89     |
| 202-1004  | 300568S     | 8P8C Category 5 Shielded Liner Plug for Round Twisted Pair, Solid | 1.91  | 1.64  | 1.37    |
| 202-1006  | 300168      | 8P8C Non-Category 5 Plug for Round Twisted pair, Solid            | .43   | .37   | .31     |
| 202-1008  | 300268      | 8P8C Non-Category 5 Plug for Round Twisted Pair, Stranded         | .39   | .33   | .28     |
| 202-0604  | 300568-50   | 50 PK Category 5 Plug for Round Twisted Pair, Solid               | 30.00 | 27.00 | 25.50   |
| 202-120X  | CXB300      | RJ45 Strain Relief Cable Boot (Color*)                            | .39   | .33   | .28     |

\*Replace "X" in Stock No. for Color Selected; 1 — Beige, 2 — Black, 3 — Blue, 7 — White, 8 — Yellow.

EZ-RJ45™ Category 5 Connector

- Easy Conductor Identification
- Meets Enhanced Cat 5 and Level 6
- Trim with Utility Knife or Crimp and Trim with 3D45000 Tool

The new patented EZ-RJ45™ connector simplifies installation by allowing the pairs to be inserted through the connector. There is no difficult liner or wire bar to deal with. Inspection of the correct conductor order is done before crimping so no connector is wasted because of incorrect wiring. The conductors are able to be pulled forward so the pairs are very close to the contacts. This method allows the integrity of the pairs to maintain Category 5 and even enhanced Category 5 capabilities. The EZ-RJ45™ can be crimped with most any standard tool, then trimmed with a cutter or small utility knife. However, the new BD45000 crimp tool crimps and trims the exposed conductors in one operation. The vertical action of the crimper makes a uniform and positive crimp.



|                                                      |      |       |
|------------------------------------------------------|------|-------|
| 202-4000. 300568EZ. Cat-5 EZ-RJ45™ plug. 1-49.....   | EACH | .98   |
| 50-99.....                                           | EACH | .79   |
| 202-4001. 3D45000. Crimp tool for EZ-RJ45™ 1-49..... | EACH | 74.81 |
| 50-99.....                                           | EACH | 59.00 |