

SMD Inductors(Coils)

For Power Line(Wound, Magnetic Shielded)

Conformity to RoHS Directive

VLF Series VLF4014A

FEATURES

- Mount area: $3.5 \times 3.7\text{mm}$
- Low profile: 1.4mm max. height
- Generic use for portable DC to DC converter line.
- High magnetic shield construction should actualize high resolution for EMC protection.
- Available for automatic mounting in tape and reel package.
- The products contain no lead and also support lead-free soldering.
- It is a product conforming to RoHS directive.

APPLICATIONS

Power source inductor for mobile devices such as mobile phones, HDDs, and DSCs

ELECTRICAL CHARACTERISTICS


Part No.	Inductance (μH)	Inductance tolerance(%)	Test frequency (kHz)	DC resistance(Ω)		Rated current(A)* Based on inductance change max.	Based on temperature rise typ.
				max.	typ.		
VLF4014AT-4R7M1R1	4.7	± 20	100	0.16	0.14	1.2	1.1
VLF4014AT-100MR90	10	± 20	100	0.26	0.23	0.9	0.9

* Rated current: Value obtained when current flows and the temperature has risen to 40°C or when DC current flows and the nominal value of inductance has fallen by 30%, whichever is smaller.


TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC SUPERPOSITION CHARACTERISTICS

VLF4014AT-4R7M1R1




SHAPES AND DIMENSIONS



Dimensions in mm




RECOMMENDED PC BOARD PATTERN




Dimensions in mm

VLF4014AT-100MR90



TEST CIRCUIT



- Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.

- All specifications are subject to change without notice.