





- 1 WIRE INSULATION: .324-356 DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 FLASH PERMITTED $\pm .020$
- 4 STAMP "AMP 4 AL 13-78" SIZE AND LOCATION APPROX AS SHOWN



BODY: COPPER ASTM-B187 ANNEALED TIN PL PER ASTM B-545 .000150 MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, .000100 MIN THK	696872-1
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 21OCT05	TE Connectivity			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK MJ SPICER 21OCT05				
	0 PLC ± -	APVD MJ SPICER 21OCT05	NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM, WIRE SIZE: 4 ALUMINUM			
	1 PLC ± -	PRODUCT SPEC				
	2 PLC ± .01	APPLICATION SPEC				
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT 18.5 GRAMS	SIZE A2	CAGE CODE 00779	DRAWING NO C-696872	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 of 1	REV F		