




0.8

[.03] MIN.

BLUE NYLON.

COPPER SLEEVE

1.8

[.07]

*1-21 9MA

2

FOR "A" MAX INSUL DIA

9.9

[.38] MIN.

A

1.8

[.07]

R0.5

[R.02]

R0.9

[R.03]

SECTION A-A

SERRATIONS

23.6

[.93] MAX

A

SUPERSEDED BY

165172-2

3

PACKAGE QTY	DIM "A"	FINISH	MATERIAL	PART NO
100	4.3[.17]	TIN PLATED	COPPER	8-165172-1
1000	4.8[.19]	TIN PLATED	COPPER	165172-2
1000	4.6[.18]	TIN PLATED	COPPER	165172-1
1000	4.3[.17]	TIN PLATED	COPPER	165172

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm [INCHES]

0 PLC

± -

1 PLC

± -

2 PLC

± -

3 PLC

± -

4 PLC

± -

ANGLES

± -

FINISH

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

± -

1 PLC

± -

2 PLC

± -

3 PLC

± -

4 PLC

± -

ANGLES

± -

FINISH

-

MATERIAL

-

DWN

JR RUTH

19FEB04

CHK

T MICHIELUTTI

19FEB04

APVD

T MICHIELUTTI

19FEB04

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

STE

TE Connectivity

NAME

PIDG WIRE PIN (LONG)

-

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-165172

-

SCALE

5:1

SHEET

1 OF 1

REV

K2

1470-19 (3/11)