



3M™ THREE-WALL HEADER, 3000 SERIES

.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE




-X0XX

HEADER WITHOUT LATCH EJECTOR



-X2XX

HEADER WITH SHORT LATCH EJECTOR
FOR 3M SOCKETS WITHOUT STRAIN RELIEF



-X3XX

HEADER WITH LONG LATCH EJECTOR
FOR 3M SOCKETS WITH STRAIN RELIEF

2 PHYSICAL :

INSULATOR: HIGH TEMP GLASS FILLED POLYESTER (PCT)
MATERIAL: UL94V-0
FLAMMABILITY: BLACK
COLOR: BLACK
CONTACT: COPPER ALLOY
MATERIAL: PLATING
UNDER PLATING: 50μ"-150μ" [1.27μm-3.81μm] NICKEL-OVERALL
WIPING AREA: 30μ" [0.76μm] AVG. GOLD
SOLDER TAILS: (SEE ORDERING INFORMATION)
MARKINGS: 3M LOGO, PART IDENTIFICATION NUMBER AND ORIENTATION TRIANGLE

2 ELECTRICAL :

CURRENT RATING: 5.00A, 1 CONTACT POWERED
3.00A, 6 CONTACTS POWERED
1.75A, ALL CONTACTS POWERED
RATING CONDITIONS: EIA-364-070 METHOD 2, 30°C MAXIMUM
TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE
3M PRODUCT SPECIFICATION FOR DETAILED CURRENT DERATING
CURVES.

INSULATION RESISTANCE: >1 X 10⁹Ω AT 500 V_{DC}
WITHSTANDING VOLTAGE: 1,000V_{RMS} AT SEA LEVEL

2 ENVIRONMENTAL :

TEMPERATURE RATING: -55°C TO 105°C
PROCESS RATING: 260°C, PER J-STD-020C, SINGLE PASS
MOISTURE SENSITIVITY LEVEL: 1 (PER J-STD-020C SINGLE PASS)

ORDERING INFORMATION

X3XXX-XXXXXX

N= HIGH TEMP BLACK (PCT)/(RB PLATING REQ'D)

3M PART NUMBER:
(SEE TABLE 1)

PLATING:
RB = 200μ" [5.08μm] MATTE TIN TAILS

PIN CONFIGURATION:
1 = RIGHT ANGLE SOLDER TAILS
2 = STRAIGHT SOLDER TAILS

TAIL:
02 = FOR .062 [1.57] THICK BOARD
03 = FOR .094 TO .125 [2.39 TO 3.18] THICK BOARD

LATCH/EJECTOR SYSTEM:
0 = NO LATCH/EJECTOR INSTALLED
2 = SHORT ROLL PIN LATCH/EJECTORS
3 = LONG ROLL PIN LATCH/EJECTORS

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

UL FILE NO: E68080

- NOTES
- REGULATORY INFORMATION:
VISIT 3M.com/regs
 - IN THE EVENT OF CONFLICT
BETWEEN THIS DATA AND THAT
CONTAINED IN THE PRODUCT
SPECIFICATION, THE PRODUCT
SPECIFICATION TAKES PRECEDENT.
 - NOTCHES A & C WILL ACCOMMODATE
3M POLARIZING KEY: N3518).
 - MOUNTING HARDWARE:
FROM SOLDER SIDE OF PC BOARD
USE #4-24 THREAD CUTTING SCREW
(3M PART #3341-5) WITH
Ø.116 [2.95] MOUNTING HOLE.
FOR RIGHT ANGLE VERSION ONLY:
#2-56 BOLT AND NUT (3M PART
#3341-6) WITH Ø.106 [2.69]
MOUNTING HOLE MAY BE USED.

DIMENSIONS: INCHES [MM]
[MM] IS REF. ONLY

DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	1	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	2	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	3	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	4	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	5	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	6	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	7	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	8	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	9	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	10	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	11	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	12	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	13	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	14	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	15	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	16	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	17	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	18	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	19	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	20	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD

3M	3M Center St. Paul, MN 55144	© 3M COPYRIGHT 2024 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.
TITLE	HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA	
CAGE NUMBER	78-5100-0771-5	REV. L
MODEL	3400	DET. YES NO SHT 1 OF 5

3M™ THREE-WALL HEADER, 3000 SERIES

.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE







TABLE 1							
PIN QTY.	3M PART NUMBER	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	POLARIZING NOTCHES	PIN QTY.
10	3793	1.26 [32.1]	1.105 [28.04]	.865 [21.97]	.71 [18.0]	BC	10
14	3314	1.46 [37.2]	1.305 [33.12]	1.065 [27.05]	.91 [23.1]	BC	14
16	3408	1.56 [39.7]	1.405 [35.66]	1.165 [29.59]	1.01 [25.6]	ABC	16
20	3428	1.76 [44.8]	1.604 [40.74]	1.365 [34.67]	1.21 [30.7]	ABC	20
26	3429	2.06 [52.4]	1.905 [48.36]	1.665 [42.29]	1.51 [38.3]	ABC	26
34	3431	2.46 [62.6]	2.305 [58.52]	2.065 [52.45]	1.91 [48.5]	ABC	34
40	3432	2.76 [70.2]	2.605 [66.14]	2.365 [60.07]	2.21 [56.1]	ABC	40
50	3433	3.26 [82.9]	3.105 [78.84]	2.865 [72.77]	2.71 [68.8]	ABC	50
60	3372	3.76 [95.6]	3.605 [91.54]	3.365 [85.47]	3.21 [81.5]	ABC	60
64	3764	3.96 [100.7]	3.805 [96.62]	3.565 [90.55]	3.41 [86.6]	ABC	64

TABLE 2						
3M PART NUMBER SUFFIX	CONTACT TAIL	DIM. "E"	PIN CROSS SECTION			DIM. "G"
-1XX2	.062 [1.57] THICK PC BOARD	.112 [2.84]	DIM. "F" .0245+/- .0005 [.622]	DIAGONALS .028+/- .001 [.71]	CORNER RADIUS .0075 REF. [.191]	.035+/- .003 [.89] SEE NOTE 5
-2XX2						
-1X03	.094 [2.39] TO .125 [3.18] THICK PC BOARD	.155 [3.94]	.0245+/- .0005 [.622]	.028+/- .001 [.71]	.0075 REF. [.191]	.035+/- .003 [.89]
-2X03						



3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373


DESIGN REFERENCE		NEXT ASSEMBLY	
DRG CODES		DRG CODES	
DIVISION Interconnect Solutions		DIVISION CODE EMSD	
DO NOT SCALE DRAWING	SCALE	TOLERANCES EXCEPT AS NOTED	
THIRD ANGLE PROJECTION		INCHES .0 ±.1 .00 ±.01 .000 ±.005 .0000 ±.0002	
INTERPRET PER ASME Y14.5 - 2018		MILLIMETERS 0 ±.0 .00 ±.005 .000 ±.0002	
MAX. SURFACE ROUGHNESS		CAGE NUMBER	
ALL SURFACES MARKED ONLY		DRAWING NO. 78-5100-0771-5	
		REV. L	
		MODEL 3400	

L	115955	MAY 08,2024	JNC	FJR
K	97909	JUN 22,2021	JNC	SAN
J	93619	JAN 07,2021	JNC	SAN
H	60056	MAR 06,2015	JNC	RS
G	56068	AUG 05,2014	JNC	RS
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	CASTIGLIONE	DATE 05,2014	MFG	DATE
CHKD		DATE	APPR	DATE
			R. SCHERER	SEP 05,2014


3M Center St. Paul, MN 55144
© 3M COPYRIGHT 2024
This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.

HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA

3M™ THREE-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



RECOMMENDED MOUNTING HOLE PATTERN
(STRAIGHT VERSION)



RECOMMENDED MOUNTING HOLE PATTERN
(RIGHT ANGLE VERSION)

PART CUSTOMIZATION


THIS SPEC SHEET DETAILS OUR STANDARD OFFERING.

3M HAS SEVERAL CAPABILITIES THAT CAN PROVIDE A PART TAILORED TO YOUR SPECIFIC NEEDS. ASK YOUR 3M SALES REPRESENTATIVE OR CUSTOMER SERVICE FOR MORE DETAILS.


BOTH SNAP-IN AND ROLL PIN LATCHES MAY BE ORDERED SEPARATELY. SNAP-IN AND ROLL PIN STYLE LATCHES ARE DIMENSIONALLY AND FUNCTIONALLY EQUIVALENT. IF ORDERING SNAP-IN OR ROLL PIN STYLE LATCHES SEPARATELY, PLEASE USE THE BELOW CHART.

MATERIAL	SHORT LATCH	LONG LATCH	LATCH STYLE	COLOR
HIGH TEMP. (PCT)	N3505-2B	N3505-3B	ROLL PIN	BLACK
HIGH TEMP (PPA)	N3505-30B	N3505-31B	SNAP-IN	BLACK

- * SELECTIVE PIN REMOVAL (ATA OR OTHER COMPATABILITY)
- * WIRE WRAP TAILS STYLE




LONG




SHORT

SNAP-IN LATCHES



NOTE:
SNAP-IN LATCHES CAN ONLY BE ORDERED SEPARATELY AND ARE THE CUSTOMERS RESPONSIBILITY TO INSTALL.


POLARIZING POST



3M PART NO.	MATERIAL	COLOR
3201-4	LCP	BLACK



NOTE:
INSERT POST INTO ONE MOUNTING
HARDWARE HOLE ON BOTTOM OF HEADER.
SET POST TO PROTRUDE .115 [2.92]

POLARIZING KEY




3M PART NO.	MATERIAL	COLOR	DIM. "A"
N3518	LCP	BLACK	.02

NOTE:
#2216 B/A SCOTCHWELD CAN BE USED TO
ADHERE KEYS.

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
ACCESS CODES				DRFT	CASTIGLIONE	DATE	AUG 05,2014	MFG	DATE
				CHKD		DATE		APPR	DATE
								R. SCHERER	SEP 05,2014
DIVISION		DIVISION CODE		© 3M COPYRIGHT 2024					
Interconnect Solutions		EMSD		 3M Center St. Paul, MN 55144		This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED							
				INCHES		TITLE HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA			
				.00 ± .1					
				.00 ± .01					
				.000 ± .005					
				.0000 ± .0002					
THIRD ANGLE PROJECTION				MILLIMETERS					
				.00 ±					
				.0 ±					
				.00 ±					
				.000 ±					
MAX SURFACE ROUGHNESS				CAGE NUMBER		SIZE	DRAWING NO.	REV.	
				D		78-5100-0771-5	L		
✓ ☐ ALL SURFACES				MODEL		3400	DET. LISTS ☐ YES ☒ NO SHT 3 OF 5		
☒ MARKED ONLY									
						</			


3M™ THREE-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE

MOUNTING HARDWARE




3341-5

(INSTALL FROM BOTTOM OF BOARD)
PANHEAD THREAD CUTTING SCREW:
#4-24 X 5/16"
TYPE: USA STD BT, FEDERAL B6
MATERIAL: STAINLESS STEEL




3341-6

HEX HEAD BOLT, NUT AND WASHER:
BOLT - #2-56 X 1/2"
MATERIAL: STAINLESS STEEL




STRAIGHT VERSION INSTALL
(MUST BE INSERTED PRIOR TO
LATCH INSTALL)

RIGHT ANGLE VERSION INSTALL




3341-6


#2-56 NUT AND BOLT



#4-24 TYPE BT SELF THREADING SCREW
WHEN USING LATCHES, MAXIMUM LENGTH
OF SCREW IS .250 INCHES PLUS
THICKNESS OF THE BOARD.



3341-5



3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

DESIGN REFERENCE		NEXT ASSEMBLY		REV		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
XREF		XREF		DRFT		DATE		MFG		DATE	
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION CODE		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018	
Interconnect Solutions		EMSD		SCALE		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .00 ± .000		MAX SURFACE ROUGHNESS .000 ± .000	
3M		3M Center St. Paul, MN 55144		TITLE		HEADER, 3-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT AND RA		CAGE NUMBER		DRAWING NO. 78-5100-0771-5	
L		MAY 08,2024		JNC		FJR		REV.		L	
K		JUN 22,2021		JNC		SAN		DET		YES	
J		JAN 07,2021		JNC		SAN		SHT		4 OF 5	
H		MAR 06,2015		JNC		RS					
G		AUG 05,2014		JNC		RS					
ECO		AUG 05,2014		JNC		RS					
CASTIGLIONE		AUG 05,2014		MFG		R. SCHERER		SEP 05,2014			
DIVISION		DIVISION									

3M™ THREE-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.

3M Company
Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
http://www.3M.com/interconnect

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

L		115955	MAY 08,2024	JNC	FJR
K		97909	JUN 22,2021	JNC	SAN
J		93619	JAN 07,2021	JNC	SAN
H		60056	MAR 06,2015	JNC	RS
G		56068	AUG 05,2014	JNC	RS
REV		ECO	ISSUE DATE AND DESCRIPTION		DRFT
DRFT		C	DATE	DATE	DATE
CHKD		DATE	DATE	DATE	DATE
DIVISION		DIVISION CODE		EMSD	
Interconnect Solutions		DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED	
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018		MILLIMETERS	
MAX SURFACE ROUGHNESS		ALL SURFACES		CAGE NUMBER	
MARKED ONLY		ANGLES		DRAWING NO.	
				REV.	
				MODEL	
				LISTS	
				YES	
				NO	
				SHT	
				5	
				OF	
				5	