

SMD Power Inductor CDRH8D48/A




RoHS




Description

- Ferrite drum core construction.
- Magnetically shielded.
- L × W × H: 8.5 × 8.5 × 5.0 mm Max.
- Product weight: 1.1g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.
- Qualification to AEC-Q200.

Dimension - [mm]



Land pattern and Schematics - [mm]



Environmental Data

- Operating temperature range: -40°C ~ +125°C (including coil's self temperature rise).
- Storage temperature range: -40°C ~ +85°C
- Solder reflow temperature: 260 °C peak.

Packaging


- Carrier tape and reel packaging
- 14.5" diameter reel
- 1000pcs per reel

Applications

- Automotive and other high temperature, high reliability application.

SMD Power Inductor

CDRH8D48/A



Electrical Characteristics

Part No.	Stamp	Inductance [μ H] [Within] ※1	D.C.R. (m Ω) [Max.](Typ.) (at 20°C)	Rated current (A) (at 125°C) ※2
CDRH8D48/ANP-100MC	100	10 μ H $\pm$ 20%	38(30)	2.26
CDRH8D48/ANP-120MC	120	12 μ H $\pm$ 20%	50(40)	1.87
CDRH8D48/ANP-150MC	150	15 μ H $\pm$ 20%	63(50)	1.62
CDRH8D48/ANP-180MC	180	18 μ H $\pm$ 20%	75(60)	1.58
CDRH8D48/ANP-220MC	220	22 μ H $\pm$ 20%	88(70)	1.45
CDRH8D48/ANP-270MC	270	27 μ H $\pm$ 20%	106(85)	1.33
CDRH8D48/ANP-330MC	330	33 μ H $\pm$ 20%	125(100)	1.20
CDRH8D48/ANP-390MC	390	39 μ H $\pm$ 20%	156(125)	1.06
CDRH8D48/ANP-470MC	470	47 μ H $\pm$ 20%	188(150)	1.00
CDRH8D48/ANP-560MC	560	56 μ H $\pm$ 20%	238(190)	0.89
CDRH8D48/ANP-680MC	680	68 μ H $\pm$ 20%	275(220)	0.82
CDRH8D48/ANP-820MC	820	82 μ H $\pm$ 20%	312(250)	0.73
CDRH8D48/ANP-101MC	101	100 μ H $\pm$ 20%	394(315)	0.70
CDRH8D48/ANP-121MC	121	120 μ H $\pm$ 20%	438(350)	0.63
CDRH8D48/ANP-151MC	151	150 μ H $\pm$ 20%	580(465)	0.58

※1. Inductance measuring condition: at 100 kHz.













※2. Rated current: The DC current at which the inductance decreases to 65% of its nominal value or when $\Delta t=30^{\circ}\text{C}$, whichever is lower .

SMD Power Inductor CDRH8D48/A



Saturation Current & Temperature Rise Graph

— L (20°C) — L (125°C) — ΔT






SMD Power Inductor CDRH8D48/A





Saturation Current & Temperature Rise Graph

— L (20°C) — L (125°C) — ΔT



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel. +852-2880-6781
FAX. +852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel. +81-48-691-7300
FAX. +81-48-691-7340
sales@jp.sumida.com

Chicago

Tel. +1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel. +86-21-5836-3299
FAX. +86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel. +82-2-6237-0777
FAX. +82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel. +49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel. +86-755-8291-0228
FAX. +86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel. +65-6296-3388
FAX. +65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel. +49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel. +886-2-8751-2737
FAX. +886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel. +1-408-321-9660
FAX. +1-408-321-9308
sales@us.sumida.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sumida:

[CDRH8D48/ANP-120MC](#) [CDRH8D48/ANP-151MC](#) [CDRH8D48/ANP-180MC](#) [CDRH8D48/ANP-820MC](#)