

Silicon Zener Diode Series

1N957BUR-1 thru 1N986BUR-1



Features

- Available in JAN, JANTX and JANTXV per MIL-PRF-19500/117
- Standard voltage tolerances are plus/minus 5% with B suffix, 10% with A suffix identification.
- Tight tolerances available in plus or minus 2% or 1% with C or D suffix respectively.
- 500 mW power handling
- Hermetically sealed axial-leaded glass DO-213AA package.



AEROFLEX
A passion for performance.

Maximum Ratings

Operating & Storage Temperature: -65°C to +175°C

Thermal Resistance: 250°C/W

Steady-State Power: 0.5 watts


Forward Voltage @200 MA: 1.1 V for 1N957BUR-1 – 1N986BUR-1

Electrical Specifications @ +25 °C (Unless Otherwise Specified)

JEDEC TYPE Number (Note 1)	Normal Zener Voltage V_Z	Zener Test Current I_{ZT}	Maximum Zener Impedance			Maximum DC Zener Current I_{ZM}	Maximum Surge Current I_{ZSM}	Maximum Reverse Leakage		Maximum Temperature Coefficient α_{VZ}
	Volts	mA	$Z_{ZT} @ I_{ZT}$	$Z_{ZK} @ I_{ZK}$	I_{ZK}	mA	mA	$I_R @ V_R$	Volts	%/°C
1N957BUR-1	6.8	18.5	4.5	700	1.0	55	300	150	5.2	+0.05
1N958BUR-1	7.5	16.5	5.5	700	.5	50	275	75	5.7	+0.058
1N959BUR-1	8.2	15.0	6.5	700	.5	45	250	50	6.2	+0.065
1N960BUR-1	9.1	14.0	7.5	700	.5	41	225	25	6.9	+0.068
1N961BUR-1	10	12.5	8.5	700	.25	38	200	10	7.6	+0.075
1N962BUR-1	11	11.5	9.5	700	.25	32	175	5	8.4	+0.076
1N963BUR-1	12	10.5	11.5	700	.25	31	160	5	9.1	+0.077
1N964BUR-1	13	9.5	13	700	.25	28	150	5	9.9	+0.079
1N965BUR-1	15	8.5	16	700	.25	25	130	5	11.4	+0.082
1N966BUR-1	16	7.8	17	700	.25	24	120	5	12.2	+0.083
1N967BUR-1	18	7.0	21	750	.25	20	110	5	13.7	+0.085
1N968BUR-1	20	6.2	25	750	.25	18	100	5	15.2	+0.086
1N969BUR-1	22	5.6	29	750	.25	16	90	5	16.7	+0.087
1N970BUR-1	24	5.2	33	750	.25	15	80	5	18.2	+0.088
1N971BUR-1	27	4.6	41	750	.25	13	70	5	20.6	+0.090
1N972BUR-1	30	4.2	49	1000	.25	12	65	5	22.8	+0.091
1N973BUR-1	33	3.8	58	1000	.25	11	60	5	25.1	+0.092
1N974BUR-1	36	3.4	70	1000	.25	10	55	5	27.4	+0.093
1N975BUR-1	39	3.2	80	1000	.25	9.5	46	5	29.7	+0.094
1N976BUR-1	43	3.0	93	1000	.25	8.8	44	5	32.7	+0.095
1N977BUR-1	47	2.7	105	1500	.25	7.9	40	5	35.8	+0.095
1N978BUR-1	51	2.5	125	1500	.25	7.4	37	5	38.8	+0.096
1N979BUR-1	56	2.2	150	2000	.25	6.8	35	5	42.6	+0.096
1N980BUR-1	62	2.0	185	2000	.25	6.0	30	5	47.1	+0.097
1N981BUR-1	68	1.8	230	2000	.25	5.5	28	5	51.7	+0.097
1N982BUR-1	75	1.7	270	2000	.25	5.0	26	5	56.0	+0.098
1N983BUR-1	82	1.5	330	3000	.25	4.6	23	5	62.2	+0.098
1N984BUR-1	91	1.4	400	3000	.25	4.1	21	5	69.2	+0.099
1N985BUR-1	100	1.3	500	3000	.25	3.7	18	5	76.0	+0.11
1N986BUR-1	110	1.1	750	4000	.25	3.3	16	5	83.6	+0.11

NOTE 1: The JEDEC type numbers shown (B Suffix) have a $\pm 5\%$ tolerance on nominal Zener Voltage. The suffix A is used to identify $\pm 10\%$ tolerance; suffix C is used to identify $\pm 2\%$; and suffix D is used identify $\pm 1\%$; no suffix indicates $\pm 20\%$.

AEROFLEX
METELICS



LEADED DESIGN DATA

CASE: DO-213AA, Hermetically sealed glass case. (MELF, SOD-80, LL34)

LEAD FINISH: Tin / Lead

THERMAL RESISTANCE: ($R_{\theta JEC}$): 100 °C/W maximum at L = 0 inch




THERMAL IMPEDANCE: ($Z_{\theta JX}$): 25 °C/W maximum

POLARITY: Diode to be operated with the banded (cathode) end positive.

MOUNTING POSITION: Any.

MOUNTING SURFACE SELECTION: The Axial Coefficient of Expansion (COE) Of this Device is Approximately +6 PPM/°C. The COE of the Mounting Surface System Should Be Selected To Provide A Suitable Match With This Device.

Graphs



Aeroflex / Metelics, Inc.

975 Stewart Drive,
Sunnyvale, CA 94085
Tel: (408) 737-8181
Fax: (408) 733-7645

Sales: 888-641-SEMI (7364)

Hi-Rel Components
9 Hampshire Street,
Lawrence, MA 01840
Tel: (603) 641-3800
Fax: (978) 683-3264

www.aeroflex.com/metelics-hirelcomponents

54 Grenier Field Road,
Londonderry, NH 03053
Tel: (603) 641-3800
Fax: (603) 641-3500

ISO 9001: 2008 certified companies

www.aeroflex.com/metelics

metelics-sales@aeroflex.com

Aeroflex / Metelics, Inc. reserves the right to make changes to any products and services herein at any time without notice. Consult Aeroflex or an authorized sales representative to verify that the information in this data sheet is current before using this product. Aeroflex does not assume any responsibility or liability arising out of the application or use of any product or service described herein, except as expressly agreed to in writing by Aeroflex; nor does the purchase, lease, or use of a product or service from Aeroflex convey a license under any patent rights, copyrights, trademark rights, or any other of the intellectual rights of Aeroflex or of third parties.

Copyright 2012 Aeroflex / Metelics. All rights reserved.



Our passion for performance is defined by three attributes represented by these three icons: solution-minded, performance-driven and customer-focused.

AEROFLEX
A passion for performance.