



SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
			ON
ON	NONE		2-1, 5-4
2-3, 5-6	N/A		



PANEL MOUNTING

- NOTE:
- ALL DIMENSIONS IN MM [INCH]
 - GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
 - TERMINAL NUMBERS FOR REF ONLY
 - PLATING MATERIAL: GOLD
 - RATING: 0.4VA MAX @20V MAX (AC or DC)
 - ELECTRIC LIFE: 40,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
 - INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
 - DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
 - OPERATING TEMP.: -30°C to 85°C
 - ▲ DENOTES CRITICAL PARAMETER.
 - 2002/95/EC (ROHS) COMPLIANT
 - HARDWARE TO BE SHIPPED BULK:
T100011 - LOCK WASHER, QTY 1
T100015 - LOCK RING, QTY 1
T100000 - HEX NUT, QTY 2

C	19555	UPDATED SWITCH FUNC. TO ON-ON WAS (ON)-(ON)	12/30/10	BGL
B	16312	CLEANED UP MODEL; ADDED "12.30" DIM.	8/15/06	BO
A	16141	NEW PART RELEASE	6/14/06	CT
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 100DP1T6B11M1REH

E-SWITCH®



SCALE 2:1

DATE 6/14/2006


DR CT

DWG ST121045

REV C



ISOMETRIC



100DP1T6B11M1RE
(T121045)