




- NOTES:
- MATERIALS AND FINISHES(PLATING THICKNESS IN MICRO-INCHES):
BODY - BERYLLIUM COPPER, GOLD PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE, NATURAL
 - ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC 0- 6 GHz
C. VSWR(RETURN LOSS): 1.3 MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
 - MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -40°C TO +155°C

THIRD ANGLE PROJ. 

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	08-Aug-06	46108	CW
B	SEE SHEET 1,AND RELEASE TO ARFA	27-Oct-10	48320	SH



RECOMMENDED PCB MOUNTING HOLE

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°	MATERIAL	DRAWN S.LI	DATE 25-Oct-10	TITLE MCX P.C. BOARD STR. JACK NON MAGNETIC		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER GEFFERY	DATE 08-Aug-06				
	REFERENCE AND CONFIGURATION LEVEL:	APPROVED S.HSIEH	DATE 27-Oct-10	SCALE: 8.0:1.0	SHEET 2 OF 2	DRAWING NO.919-NMI09J-51P	
	FINISH	Root Folder\919-NMI09J-51P		DWG SIZE B	REV B	ITEM NO.919-NMI09J-51P PART NO.919-NMI09J-51P	