

Customer Information Sheet

DRAWING No.: SI751-XX

SHEET 2 OF 2






IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



RECOMMENDED PAD LAYOUT

ORDER CODE	FINISH
SI751-06	TIN/LEAD
SI751-46	100% TIN

SPECIFICATIONS:

MATERIAL = BRASS CuZn30 1/2 HARD

FINISH:

06 = 4 μ 90/10 TIN/LEAD

46 = 4 μ 100% TIN

ELECTRICAL:

CURRENT RATING = 2A MAX

CONTACT RESISTANCE = 20m Ω MAX

ENVIRONMENTAL:

OPERATING TEMPERATURE = -55°C TO +125°C

SB	4	06.02.14	12358
NAME	ISS.	DATE	C/NOTE
APPROVED:	S.BENNETT		
CHECKED:	M.PLESTED		
DRAWN:	W. J. BOURNE		
CUSTOMER REF.:			
ASSEMBLY DRG.:			

NOTES:

1. FOR TAPE AND REELED COMPONENTS, SEE DRAWING SI751-XXR.
2. PACKING: 1,000 PER BAG.

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ± 1 mm
X.X = ± 0.25 mm
X.XX = ± 0.10 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
SURFACE MOUNT TEST TERMINAL
(LOOSE)
DRAWING NUMBER:
SI751-XX
SHT
2
OF
2