

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

4SEI-3

4SEI-3

M

DRAWING
NUMBER

X X

ISSUE

3

REVISIONS

A	CO-54473
D J S	
2	FEB 84
B	CO56103
C J H	
12	NOV 84

REPLACES

RELEASE NO. PR-5586

CHECK

CHECK

16 JAN 76

13 D

CHECK

15 JAN 76


C E B

FO-52848-A

DRAWN

CORROSION RESISTANT
STEEL PLUNGER

ELASTOMER PLUNGER SEAL




NOTE -

- 1 MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON $.375 \pm .002$ CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS .26 OZ MAX, WEIGHT OF SWITCH WITH WIRE LEADS IS 1.30 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE-----5-17 OZ
 RELEASE FORCE-----4 OZ MIN
 RELEASE TRAVEL-----.004 MIN
 DIFFERENTIAL TRAVEL-----.004 MAX
 OVERTRAVEL-----.003 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

5A 250 VAC



L4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/.04	X X
ONE PLACE	X, X	0.4/.016	X, X X
TWO PLACES	X, XX	0.15/.006	X, X X X
THREE PLACES	X, XXX		X, X X X X
ANGLES			

SI METRIC

US CUSTOMARY

DESIGN UNITS



WEIGHT

3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[4SE1-3](#)