





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

**NOTES:****ELECTRICAL:**

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 45 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : FR50.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING : GOLD PLATING OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:


1. STORAGE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION: 0°C TO 70°C .

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.


CUL FILE NO. E163191

PART NUMBER: E556X-Q0LX2X

2-2C 1-3u" 2-6u" 3-15u"
4-4C 4-30u" 5-50u"
6-6C 4-A05-0040 (BK)
K-A05-0220 (GY)



PC Board Layout Component Side Shown

DETACHED LISTS	MM (INCH)		DFTD Qianpu	DATE 4/21/04'	FULL RISE ELECTRONIC CO., LTD	
	TOLERANCES EXCEPT AS NOTED		CHKD HERO	DATE 2004/6/1		
			MFO	DATE	TITLE MINI L/P ENTRY PCB JACK	
			APPLV SAMMY	DATE 2004/6/1		
			MATERIAL :			
	ANGLES ±		QT'Y :			
			FINISH :		DRAWING NO. GE553027	
	THIRD ANGLE PROJECTION		SCALE : 4:1		/PART NO. SEE NOTE	
					SIZE A3	
					REV 0	

DO NOT SCALE DRAWING		SHEET X	OF Y
----------------------	--	---------	------

8 7 6 5 4 3 2 1