







LEAD FREE	71.12	[2.800]	28	5-641216-8	 SUPERCEDED	71.12	[2.800]	28	2-641216-8
	68.58	[2.700]	27	5-641216-7		68.58	[2.700]	27	2-641216-7
	66.04	[2.600]	26	5-641216-6	 SUPERCEDED	66.04	[2.600]	26	2-641216-6
	63.50	[2.500]	25	5-641216-5		63.50	[2.500]	25	2-641216-5
	60.96	[2.400]	24	5-641216-4	 SUPERCEDED	60.96	[2.400]	24	2-641216-4
	58.42	[2.300]	23	5-641216-3		58.42	[2.300]	23	2-641216-3
	55.88	[2.200]	22	5-641216-2	 SUPERCEDED	55.88	[2.200]	22	2-641216-2
	53.34	[2.100]	21	5-641216-1		53.34	[2.100]	21	2-641216-1
	50.80	[2.000]	20	5-641216-0	 SUPERCEDED	50.80	[2.000]	20	2-641216-0
	48.26	[1.900]	19	4-641216-9		48.26	[1.900]	19	1-641216-9
	45.72	[1.800]	18	4-641216-8	 SUPERCEDED	45.72	[1.800]	18	1-641216-8
	43.18	[1.700]	17	4-641216-7		43.18	[1.700]	17	1-641216-7
	40.64	[1.600]	16	4-641216-6	 SUPERCEDED	40.64	[1.600]	16	1-641216-6
	38.10	[1.500]	15	4-641216-5		38.10	[1.500]	15	1-641216-5
	35.56	[1.400]	14	4-641216-4	 SUPERCEDED	35.56	[1.400]	14	1-641216-4
	33.02	[1.300]	13	4-641216-3		33.02	[1.300]	13	1-641216-3
	30.48	[1.200]	12	4-641216-2		30.48	[1.200]	12	1-641216-2
	27.94	[1.100]	11	4-641216-1		27.94	[1.100]	11	1-641216-1
	25.40	[1.000]	10	4-641216-0		25.40	[1.000]	10	1-641216-0
	22.86	[.900]	9	3-641216-9		22.86	[.900]	9	641216-9
20.32	[.800]	8	3-641216-8	20.32		[.800]	8	641216-8	
17.78	[.700]	7	3-641216-7	17.78		[.700]	7	641216-7	
15.24	[.600]	6	3-641216-6	LEAD FREE	15.24	[.600]	6	641216-6	
12.70	[.500]	5	3-641216-5		12.70	[.500]	5	641216-5	
10.16	[.400]	4	3-641216-4		10.16	[.400]	4	641216-4	
7.62	[.300]	3	3-641216-3		7.62	[.300]	3	641216-3	
5.08	[.200]	2	3-641216-2		5.08	[.200]	2	641216-2	
DIM (L) NO.OF POSN ASSEMBLY					DIM (L) NO.OF POSN ASSEMBLY				

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26-JAN-2005 S. HOOVER CHK 26-JAN-2005 D. BOSSI APVD 26-JAN-2005 D. BOSSI		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P/LC ± 1 P/LC ± 2 P/LC ± 0.13 [.005] 3 P/LC ± 4 P/LC ± ANGLES ±		NAME MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE RIGHT ANGLE POST, .000030 GOLD PLATED	
		PRODUCT SPEC APPLICATION SPEC		SIZE A1	
MATERIAL 		FINISH 		DRAWING NO 00779	
		WEIGHT		RESTRICTED TO 641216	
		CUSTOMER DRAWING		SCALE: 8:1 SHEET 1 of 1 REV AD	