

3M™ Conductive Floor Mat for Hard Floors

Conductive Rubber Floor Mat

Homogeneous conductive rubber construction provides resistance to wear, hot solder, oil grease, and solvents. This mat's conductive resistance value ensures rapid discharge from personnel wearing foot grounders. The low profile reduces trip hazard and is preferred for use with rolling carts or chairs. Mat can be reversed for double usage. Compatible with Constant Monitors.

Standards

Meets the requirements of ESD Standard 20.20, EIA 625, MIL-HDBK-263, and MIL-STD-1686.

Specifications

Resistance to Ground point (R_{TG}) 10^5 ohms
Resistance Top to Top (R_{TT}) 10^5 ohms
Thickness: 0.060 inches
Color: Black

Part Numbers

Mats Includes mat, two snaps, installed.

SIZE **BLACK P/N**
48x72 inches COND4872FM

Call for custom sizes.

Mat Kits Includes mat, two snaps, installed, and a 15 foot ground cord.

SIZE **BLACK P/N**
48x72 inches COND4872FM-F

Call for custom sizes.

Rolls Includes roll of matting material.



SIZE **BLACK P/N**
2x50 feet COND24600FM
3x50 feet COND36600FM
4x50 feet COND48600FM

See 3M Data Sheets for these related items:

3M™ Ground Cords

3M™ Snaps

3M™ Snap Tool



R - T - G?

R_{TG} is the resistance from one point on the mat's surface to the mat's ground point, and is the fundamental electrical test for a mat. A proper R_{TG} insures that a mat can conduct charge from a point on the surface to the mat ground point. The guideline in ESD STM-4.1 for R_{TG} is 1×10^6 to 1×10^9 ohms. ANSI/ESD S-20.20 has an upper limit of $<1 \times 10^9$ ohms.

R_{TT} is the resistance from one point on the mat's surface to another point. A proper R_{TT} insures the consistency of the mat's resistance properties. The ESD STM-4.1 guideline for R_{TT} is $>1 \times 10^6$ ohms.

P R O D U C T D A T A S H E E T

Mat - Conductive Rubber - FLOOR MAT

PRODUCT
CONDUCTIVE RUBBER FLOOR MAT

ITEM NUMBER
SEE ABOVE

DATASHEET
1136-C

3M Electronic Solutions Division
6801 River Place Blvd.
Austin, TX 78726-9000
US and Canada: 866-722-3736
Fax: 866-722-3735
Intl: 919-718-0000; Fax: 919-774-8174
email: 3Mstaticinfo@mmm.com; www.3M.com/static

3M is a trademark of 3M Company.
All other trademarks herein are the property
of their respective owners.



© 2008