



Slim, simple and strikingly IXUS

Inside a slim, stylish metal body the IXUS 125 HS packs a host of helpful features - so taking great shots is a breeze even in low light. Face ID prioritises friends and Full HD movies add to the fun.

The IXUS 125 HS is part of the Canon IXUS digital still camera range consisting of the below products:

IXUS 1100 HS, IXUS 500 HS, IXUS 310 HS, IXUS 230 HS, IXUS 220 HS, **IXUS 125 HS**, IXUS 115 HS.

Key Features:

- Slim metal body with unique IXUS style in stunning colours. 24mm ultra-wide, 5x optical zoom lens
- HS System with 16.1 Megapixel CMOS and DIGIC 5 for superb image quality even in low light
- Optical Image Stabilizer with Intelligent IS keeps photos and movies sharp and detailed
- Large 7.5 cm (3.0") PureColor II G LCD (460k) for great visibility and strength
- Full HD movies (1080p) with optical zoom and HDMI-CEC
- Smart Auto (58 scenes) for the ultimate in point and shoot
- Face ID can recognise and prioritise your favourite people
- High-speed Burst, Super Slow Motion Movie for capturing action
- Movie Digest (720p)
- Optional 3m waterproof case

Product Name	Mercury Code	EAN Code	
IXUS 125 HS (Silver)	6037B007AA	8714574579146	
IXUS 125 HS (Red)	6043B007AA	8714574579184	
IXUS 125 HS (Blue)	6046B007AA	8714574579221	
IXUS 125 HS (Pink)	6049B007AA	8714574579269	
IXUS 125 HS (Green)	6052B007AA	8714574579306	
What's in the box: Digital Camera IXUS 125 HS, Wrist Strap WS-800, Battery Pack NB-11L, Battery Charger CB-2LDE, AC Cable, Interface Cable IFC-400PCU, User Manual Kit.			

Accessories	Mercury Code	EAN Code
Battery Pack NB-11L	6212B001AA	4960999844022
Battery Charger CB-2LDE(E)	6214B001AA	4960999844091
AC Adapter Kit ACK-DC90	6216B003AA	4960999844169
Soft Leather Case DCC-1300	0035X471	8714574575810
Waterproof case WP-DC330L	5709B001AA	4960999844336

Technical Specifications

IMAGE SENSOR Type Effective Pixels Colour Filter Type	1/2.3 type back-illuminated CMOS Approx. 16.1M Primary Colour
IMAGE PROCESSOR Type	DIGIC 5 with iSAPS technology
LENS Focal Length Zoom Maximum f/number Construction Image Stabilisation	4.3 – 21.5 mm (35 mm equivalent: 24 – 120 mm) Optical 5x. ZoomPlus 10x. Digital Approx. 4x (with Digital Tele-Converter Approx. 1.6x or 2.0x and Safety Zoom ^[1]). Combined Approx. 20x f/2.7 – f/5.9 6 elements in 5 groups (1 double sided aspherical UA lens, 2 double sided aspherical lenses and 1 single sided aspherical UA lens) Yes (lens shift-type), Approx. 3.5-stop. Intelligent IS
FOCUSING Type AF System/ Points AF Modes AF Point Selection AF Lock AF Assist Beam Closest Focusing Distance	TTL AiAF (Face Detection / 9-point), 1-point AF (fixed to centre) Single, Continuous (Auto mode only), Servo AF/AE ^[10] , Tracking AF Size (Normal, Small) On/Off Selectable Yes 3 cm (W) from front of lens in macro
EXPOSURE CONTROL Metering modes AE Lock Exposure Compensation ISO sensitivity ^[3]	Evaluative (linked to Face Detection AF frame), Centre-weighted average, Spot (centre) On/Off Selectable +/- 2 EV in 1/3 stop increments Enhanced i-Contrast for automatic dynamic range correction AUTO, 100, 200, 400, 800, 1600, 3200
SHUTTER Speed	1 – 1/2000 sec. (factory default) 15 – 1/2000 sec. (total range varies by shooting mode)
WHITE BALANCE Type Settings	TTL Auto (including Face Detection WB), Daylight, Cloudy, Tungsten, Fluorescent, Fluorescent H, Custom. Multi-area WB correction available in Smart Auto. White Balance Compensation in Underwater mode.
LCD MONITOR Monitor Coverage Brightness	7.5 cm (3.0") PureColor II G LCD (TFT), Approx. 461,000 dots Approx. 100% Adjustable to one of five levels. Quick-bright LCD
FLASH Modes Slow Sync Speed Red-Eye Reduction Flash Exposure Compensation Flash Exposure Lock Built-in Flash Range External Flash	Auto, Manual Flash On / Off, Slow Synchro Yes. Fastest speed 1/2000 sec. Yes Face Detection FE, Smart Flash Exposure Yes 50 cm – 3.5 m (W) / 90 cm – 2.0 m (T) Canon High Power Flash HF-DC2
SHOOTING Modes Modes in Movie Photo Effects Drive modes Continuous Shooting	Smart Auto (58 scenes detected), P, Movie Digest, Portrait, Smooth Skin, Smart Shutter (Smile, Wink Self-Timer, FaceSelf-Timer), High-speed Burst (4.0MP), Handheld Night Scene, Low Light (4.0MP), Fish-eye Effect, Miniature Effect, Toy Camera Effect, Soft Focus, Monochrome, Super Vivid, Poster Effect, Color Accent, Color Swap, Underwater, Snow, Long Shutter, Stitch Assist Smart Auto (21 scenes detected), P, Portrait, Miniature Effect, Monochrome, Super Vivid, Poster Effect, Color Accent, Color Swap, Underwater, Snow, iFrame Movie, Super Slow Motion Movie My Colors (My Colors Off, Vivid, Neutral, Sepia, Black & White, Positive Film, Lighter Skin Tone, Darker Skin Tone, Vivid Blue, Vivid Green, Vivid Red, Custom Color) Single, Continuous, Self-Timer Approx. 2.0 shots/sec., High-speed Burst (4.0MP): Approx. 5.8 shots/sec., (until memory card becomes full) ^[6] ^[7]

RECORDING PIXELS / COMPRESSION Image Size Compression Movies Movie Length	4:3 - (L) 4608 x 3456, (M1) 3264 x 2448, (M2) 1600 x 1200, (S) 640 x 480 16:9 - (L) 4608 x 2592, (M1) 3264 x 1832, (M2) 1920 x 1080, (S) 640 x 360 3:2 - (L) 4608 x 3072, (M1) 3264 x 2176, (M2) 1600 x 1064, (S) 640 x 424 1:1 - (L) 3456 x 3456, (M1) 2448 x 2448, (M2) 1200 x 1200, (S) 480 x 480 Resize in playback (M2, S, XS)* *XS is half the length and width of S Superfine, Fine (Full HD) 1920 x 1080, 24 fps, (HD) 1280 x 720, 30 fps, (L) 640 x 480, 30 fps Super Slow Motion Movie (L) 640 x 480, 120fps, (M) 320 x 240, 240fps Miniature Effect (HD, L) 6fps, 3fps, 1.5 fps iFrame Movie (HD) (Full HD & HD) Up to 4 GB or 10 min. 00 sec. ^[11] (L) Up to 4 GB or 1 hour ^[7] (Movie Digest) Up to 4GB or 29 min. 59 sec. (Super Slow Motion Movie) 30 sec.
FILE TYPES Still Image Type Movies	JPEG compression, (Exif 2.3 [Exif Print] compliant) / Design rule for Camera File system, Digital Print Order Format [DPOF] Version 1.1 compliant MOV [H.264 + Linear PCM (monaural)] iFrame
DIRECT PRINT Canon Printers PictBridge	Canon SELPHY Compact Photo Printers and Canon Inkjet Printers supporting PictBridge (iD Photo Print, Fixed Size Print and Movie Print supported on SELPHY CP & ES printers only) Yes
OTHER FEATURES Red-Eye Correction My Camera / My Menu My Category Intelligent Orientation Sensor Histogram Playback zoom Self Timer Menu Languages	Yes, during shooting and playback Start-up image and camera sounds customisation Image tagging feature Yes Yes Approx. 2x – 10x Approx. 2 or 10 sec., Custom English, German, French, Dutch, Danish, Finnish, Italian, Norwegian, Swedish, Spanish, Simplified Chinese, Chinese (traditional), Japanese, Russian, Portuguese, Korean, Greek, Polish, Czech, Hungarian, Turkish, Thai, Arabic, Ukrainian, Romanian, Farsi, Malaysian, Hindi, Indonesian, Vietnamese
INTERFACE Computer Other	Hi-Speed USB (MTP, PTP) dedicated connector (Mini-B compatible) HDMI Mini Connector (HDMI-CEC compatible), A/V output (PAL/NTSC)
MEMORY CARD Type	SD, SDHC, SDXC
SUPPORTED OPERATING SYSTEM PC & Macintosh	Windows 7 SP1 / Vista SP2 / XP SP3 Mac OS X v10.6 – 10.7
SOFTWARE Browsing & Printing Other	ImageBrowser EX PhotoStitch
POWER SOURCE Batteries Battery life A/C Power Supply	Rechargeable Li-ion Battery NB-11L (battery and charger supplied) Approx. 170 shots ^[8] Approx. 180 min. playback Optional, AC Adapter Kit ACK-DC90
ACCESSORIES Cases / Straps Waterproof / Weatherproof Case Flash Power Supply & Battery Chargers Other	Soft Leather Case DCC-1300, IXUS Metal or Leather Strap Waterproof Case (3m) WP-DC330L Canon High Power Flash HF-DC2 AC Adapter Kit ACK-DC90, Battery Charger CB-2LDE Canon HDMI Cable HTC-100
PHYSICAL SPECIFICATIONS Operating Environment Dimensions (WxHxD) Weight	0 – 40°C, 10 – 90% humidity 93.2 x 57.0 x 20.0 mm Approx. 135 g (including battery/batteries and memory card)

All data is based on Canon standard testing methods (according to CIPA Standards) except where indicated. Subject to change without notice.

[1] Depending on the image size selected.

[3] Standard Output Sensitivity / Recommended Exposure Index. According to ISO 12232:2006 (20th April 2006) which specifies the method for assigning and reporting ISO speed ratings for digital still cameras.

[6] Under conditions where the flash does not fire.

[7] Depending on memory card speed / capacity / compression setting.

[8] Using the batteries and memory card format supplied with the camera (where included), except where indicated.

[10] Some settings limit availability.

[11] The following Speed Class memory cards are required for maximum record time: (HD) 1280 x 720 Speed Class 4 or above. (Full HD) 1920 x 1080 Speed Class 6 or above. (iFrame) 1280 x 720 Speed Class 6 or above.

Logistics information

Pack Description	Quantity	Dimensions (L x W x H in mm)	Weight (Net / Gross in kg)
Each	1	159 x 138 x 61	0.284 / 0.373
Carton	15	447 x 326 x 202	5.6 / 6.39
Euro Pallet	375	1200 x 800 x 1160	- / 153