

Customer Information Sheet

DRAWING No.: D6XXX-XX

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

PART No.	No. OF CONTACTS	No. OF CENTRE BARS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'
D6206-XX	6	0	7.62	5.08	10.16	7.62
D6208-XX	8	0	10.16	7.62	10.16	7.62
D6214-XX	14	0	17.78	15.24	10.16	7.62
D6216-XX	16	0	20.32	17.78	10.16	7.62
D6218-XX	18	0	22.86	20.32	10.16	7.62
D6220-XX	20	1	25.40	22.86	10.16	7.62
D6222-XX	22	1	27.94	25.40	12.70	10.16
D6224-XX	24	1	30.48	27.94	17.78	15.24
D6228-XX	28	1	35.62	33.02	17.78	15.24
D6232-XX	32	1	40.64	38.10	17.78	15.24
D6240-XX	40	2	50.80	48.26	17.78	15.24
D6248-XX	48	2	60.96	58.42	25.28	22.86
D6264-XX	64	2	81.28	78.74	25.28	22.86
D6724-XX	24	1	30.48	27.94	12.70	10.16
D6922-XX	22	1	27.94	25.40	10.16	7.62
D6924-XX	24	0	30.48	27.94	10.16	7.62
D6948-XX	48	2	60.96	58.42	17.78	15.24

SPECIFICATION:

MATERIAL:

MOULDING:

01 FINISH = GLASS-FILLED POLYESTER UL94V-0, BLACK

46 FINISH = HIGH TEMP. POLYAMIDE 46, UL94V-0, BLACK

CONTACTS = BRASS

FINISH:

CONTACTS = 3.5-5.0µ 100% TIN OVER 2µ NICKEL

ELECTRICAL:

CURRENT RATING AT 25°C = 1.5A

CURRENT RATING AT 85°C = 0.25A

CONTACT RESISTANCE (INITIAL) = 15 mΩ MAX

CONTACT RESISTANCE (AFTER CONDITIONING) = 23 mΩ MAX

INSULATION RESISTANCE (INITIAL) = 1,000 MΩ MIN

INSULATION RESISTANCE (AFTER CONDITIONING) = 100 MΩ MIN

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

PACKING:

TUBE

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C004XX (LATEST ISSUE)

NOTES:

1. RECOMMENDED PCB HOLE SIZE = Ø0.80mm MIN.

ORDER CODE:

D6XXX-XX


PITCH CODE
SEE TABLE

TOTAL No. OF CONTACTS


FINISH:

01 = 100% TIN


46 = 100% TIN (HIGH TEMP MOULD)

ILLUSTRATION OF
NUMBER OF CENTRE BARS
(SEE TABLE)



0 BARS



1 BAR



2 BARS



JMB	9	07.12.05	8905
NAME	ISS.	DATE	C/NOTE
APPROVED:			
CHECKED:			
DRAWN:		D. FAIRS	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN INC U.S.A. TEL: (812) 542 2540 FAX: (812) 542 2541	HARWIN PLC U.K. TEL: 023 9231 4545 FAX: 023 9231 4590	HARWIN PTE SINGAPORE TEL: 65 6779 4909 FAX: 65 6779 3868
--	--	---

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

DIL I.C. SLOTTED
HEADER ASSEMBLY

DRAWING NUMBER:

D6XXX-XX

SHT
2 OF 2