


## Aktive Differential-Tastköpfe | Active Differential Probes

TT-SI 9101 | TT-SI 9110 | TT-SI 9010

Mitgeliefertes Zubehör /  
Supplied Accessories



| Specifications                                                                               | Type | TT-SI 9101                                                                              | TT-SI 9110                                                                                | TT-SI 9010                                                                                |
|----------------------------------------------------------------------------------------------|------|-----------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|
| Order Number                                                                                 |      | 15111                                                                                   | 15120                                                                                     | 15106                                                                                     |
| Bandwidth                                                                                    |      | DC to 100MHz (-3dB)                                                                     | DC to 100MHz (-3dB)                                                                       | DC to 70MHz (-3dB)                                                                        |
| Attenuation Ratio                                                                            |      | 1:10 / 1:100                                                                            | 1:100 / 1:1000                                                                            | 1:100 / 1:1000                                                                            |
| Accuracy                                                                                     |      | ±2%                                                                                     | ±2%                                                                                       | ±2%                                                                                       |
| Rise Time                                                                                    |      | 3,5ns                                                                                   | 3,5ns                                                                                     | 5ns                                                                                       |
| Input Impedance                                                                              |      | 4MΩ // 7pF each side to ground                                                          | 4MΩ // 7pF each side to ground                                                            | 10MΩ // 10pF each side to ground                                                          |
| Input Voltage<br>– Differential Range                                                        |      | 1:10 ±70V (DC + peak AC)<br>or 70Vrms<br>1:100 ±700V (DC + peak AC)<br>or 700Vrms       | 1:100 ±140V (DC + peak AC)<br>or 140Vrms<br>1:1000 ±1400V (DC + peak AC)<br>or 1000Vrms   | 1:100 ±700V (DC + peak AC)<br>or 700Vrms<br>1:1000 ±7000V (DC + peak AC)<br>or 2500Vrms   |
| – Common Mode Range                                                                          |      | 1:10 ±700V (DC + peak AC)<br>or 700Vrms<br>1:100 ±700V (DC + peak AC)<br>or 700Vrms     | 1:100 ±1400V (DC + peak AC)<br>or 1000Vrms<br>1:1000 ±1400V (DC + peak AC)<br>or 1000Vrms | 1:100 ±7000V (DC + peak AC)<br>or 2500Vrms<br>1:1000 ±7000V (DC + peak AC)<br>or 2500Vrms |
| – Absolute max. Voltage<br>(Differential Mode)                                               |      | 1:10 ±1400V (DC + peak AC)<br>or 1000Vrms<br>1:100 ±1400V (DC + peak AC)<br>or 1000Vrms | 1:100 ±1400V (DC + peak AC)<br>or 1000Vrms<br>1:1000 ±1400V (DC + peak AC)<br>or 1000Vrms | 1:100 ±7000V (DC + peak AC)<br>or 2500Vrms<br>1:1000 ±7000V (DC + peak AC)<br>or 2500Vrms |
| (Common Mode)                                                                                |      | 1:10 ±1400V (DC + peak AC)<br>or 1000Vrms<br>1:100 ±1400V (DC + peak AC)<br>or 1000Vrms | 1:100 ±1400V (DC + peak AC)<br>or 1000Vrms<br>1:1000 ±1400V (DC + peak AC)<br>or 1000Vrms | 1:100 ±7000V (DC + peak AC)<br>or 2500Vrms<br>1:1000 ±7000V (DC + peak AC)<br>or 2500Vrms |
| Overvoltage Category                                                                         |      | CAT III                                                                                 | CAT III                                                                                   | CAT I                                                                                     |
| Output<br>– Swing<br>– Offset (typical)<br>– Noise (typical)<br>– Source Impedance (typical) |      | ±7V (into 50kΩ load)<br><±5mV<br>0,9mVrms<br>50Ω                                        | ±1,4V (into 50kΩ load)<br><±5mV<br>0,9mVrms<br>50Ω                                        | ±1,4V (into 50kΩ load)<br><±5mV<br>0,9mVrms<br>50Ω                                        |
| CMRR (typical)                                                                               |      | -85dB @ 50Hz, -55dB @ 1MHz                                                              | -80dB @ 60Hz, -60dB @ 1MHz                                                                | -80dB @ 50Hz, -60dB @ 1MHz                                                                |

Technische Änderungen vorbehalten | All specifications and characteristics are subject to change without notice

Power requirements: 4 x AA Cells or Mains Adaptor 6VDC/200mA or regulated 9VDC/120mA

Dimensions: (L x W x H) 202mm x 83mm x 38mm

Length: BNC Cable 90cm - Input Leads 30/60cm

Weight: 500g