


2				1			
LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G2	TOLERANCE CORRECTION	23JUL2013	KJK	RP

NOTES:

- 1 FOR MINI-APPLICATOR CRIMPING.
- 2 UNDERCOATING:1,25µm Ni,SELECTIVE:0,8µm Au, ZONE 1: 0,5µm MIN. GOLD FLASH.
- 3 UNDERCOATING:1,25µm Ni,SELECTIVE:0,8µm Au, REMAINDER: GOLD FLASH.
- 4 ZONE 1:BRIGHT TIN/LEAD PLATED.
- 5 PRE-TIN PLATED 2,0µm.
- 6 MATERIAL: PHOSPHOR BRONZE
- 7 OBSOLETE



GOLD	3	167419-4	167418-4
GOLD	2	167419-2	167418-2 7
TIN	5	167419-1	167418-1
FINISH		LOOSE PIECE	PART NUMBER

WIRE RANGE :
0,20-0,58 mm² 24-20 AWG
INSULATION RANGE :
1,6 MAX. DIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.v.LIEMPT 03 DEC 98	 TE Connectivity		
		CHK J.v.LIEMPT			
		APVD E.LEIJTENS	NAME		
		PRODUCT SPEC	AMPMODU MOD.4 RECEPTACLE, S.C.P. STRIP		
		APPLICATION SPEC			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-167418
		CUSTOMER DRAWING	SCALE 8:1	SHEET 1 OF 1	REV G2