

# CDx4AC74 Dual Positive-Edge-Triggered D-Type Flip-Flops With Clear And Preset

## 1 Features

- AC types feature 1.5V to 5.5V operation and balanced noise immunity at 30% of the supply
- Speed of bipolar F, AS, and S, with significantly reduced power consumption
- Balanced propagation delays
- $\pm 24\text{mA}$  output drive current – fanout to 15 F devices
- SCR-latchup-resistant CMOS process and circuit design

## 2 Description

The 'AC74 dual positive-edge-triggered devices are D-type flip-flops.


### Device Information

| PART NUMBER | PACKAGE <sup>(1)</sup> | PACKAGE SIZE <sup>(2)</sup> | BODY SIZE <sup>(3)</sup> |
|-------------|------------------------|-----------------------------|--------------------------|
| CDx4AC74    | J (CDIP, 14)           | 19.56mm × 7.9mm             | 19.56mm × 6.67mm         |
|             | N (PDIP, 14)           | 19.3mm × 9.4mm              | 19.3mm × 6.35mm          |
|             | D (SOIC, 14)           | 8.65mm × 6mm                | 8.65mm × 3.9mm           |

(1) For more information, see [Section 10](#).

(2) The package size (length × width) is a nominal value and includes pins, where applicable.

(3) The body size (length × width) is a nominal value and does not include pins.



Copyright © 2016, Texas Instruments Incorporated


**Logic Diagram, Each Flip-Flop (Positive Logic)**



## Table of Contents

|                                                                                |          |                                                                  |           |
|--------------------------------------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                                                        | <b>1</b> | <b>6 Detailed Description</b> .....                              | <b>10</b> |
| <b>2 Description</b> .....                                                     | <b>1</b> | 6.1 Overview.....                                                | 10        |
| <b>3 Pin Configuration and Functions</b> .....                                 | <b>3</b> | 6.2 Functional Block Diagram.....                                | 10        |
| <b>4 Specifications</b> .....                                                  | <b>4</b> | 6.3 Device Functional Modes.....                                 | 10        |
| 4.1 Absolute Maximum Ratings.....                                              | 4        | <b>7 Application and Implementation</b> .....                    | <b>11</b> |
| 4.2 ESD Ratings.....                                                           | 4        | 7.1 Layout.....                                                  | 11        |
| 4.3 Recommended Operating Conditions.....                                      | 4        | <b>8 Device and Documentation Support</b> .....                  | <b>12</b> |
| 4.4 Thermal Information.....                                                   | 4        | 8.1 Documentation Support (Analog).....                          | 12        |
| 4.5 Electrical Characteristics.....                                            | 5        | 8.2 Receiving Notification of Documentation Updates....          | 12        |
| 4.6 Timing Requirements, $V_{CC} = 1.5\text{ V}$ .....                         | 5        | 8.3 Support Resources.....                                       | 12        |
| 4.7 Timing Requirements, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ .....        | 5        | 8.4 Trademarks.....                                              | 12        |
| 4.8 Timing Requirements, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .....          | 6        | 8.5 Electrostatic Discharge Caution.....                         | 12        |
| 4.9 Switching Characteristics, $V_{CC} = 1.5\text{ V}$ .....                   | 6        | 8.6 Glossary.....                                                | 12        |
| 4.10 Switching Characteristics, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ ..... | 6        | <b>9 Revision History</b> .....                                  | <b>12</b> |
| 4.11 Switching Characteristics, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .....   | 7        | <b>10 Mechanical, Packaging, and Orderable Information</b> ..... | <b>13</b> |
| 4.12 Operating Characteristics.....                                            | 7        |                                                                  |           |
| <b>5 Parameter Measurement Information</b> .....                               | <b>8</b> |                                                                  |           |

## 3 Pin Configuration and Functions



**Figure 3-1. CD54AC74 F Package, 14-Pin CDIP; CD74AC74 E or M Package, 14-Pin PDIP or SOIC (Top View)**

### Pin Functions

| PIN                       |     | I/O    | DESCRIPTION                                    |
|---------------------------|-----|--------|------------------------------------------------|
| NAME                      | NO. |        |                                                |
| 1 $\overline{\text{CLR}}$ | 1   | Input  | Channel 1, Clear Input, Active Low             |
| 1D                        | 2   | Input  | Channel 1, Data Input                          |
| 1CLK                      | 3   | Input  | Channel 1, Positive edge triggered clock input |
| 1 $\overline{\text{PRE}}$ | 4   | Input  | Channel 1, Preset Input, Active Low            |
| 1Q                        | 5   | Output | Channel 1, Output                              |
| 1 $\overline{\text{Q}}$   | 6   | Output | Channel 1, Inverted Output                     |
| GND                       | 7   | —      | Ground                                         |
| 2 $\overline{\text{Q}}$   | 8   | Output | Channel 2, Inverted Output                     |
| 2Q                        | 9   | Output | Channel 2, Output                              |
| 2 $\overline{\text{PRE}}$ | 10  | Input  | Channel 2, Preset Input, Active Low            |
| 2CLK                      | 11  | Input  | Channel 2, Positive edge triggered clock input |
| 2D                        | 12  | Input  | Channel 2, Data Input                          |
| 2 $\overline{\text{CLR}}$ | 13  | Input  | Channel 2, Clear Input, Active Low             |
| V <sub>CC</sub>           | 14  | —      | Positive Supply                                |

## 4 Specifications

### 4.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                              |                                                   | MIN                                                       | MAX | UNIT    |
|------------------------------|---------------------------------------------------|-----------------------------------------------------------|-----|---------|
| V <sub>CC</sub>              | Supply voltage range                              | -0.5                                                      | 6   | V       |
| I <sub>IK</sub> <sup>1</sup> | Input clamp current                               | (V <sub>I</sub> < 0 or V <sub>I</sub> > V <sub>CC</sub> ) |     | ±20 mA  |
| I <sub>OK</sub> <sup>1</sup> | Output clamp current                              | (V <sub>O</sub> < 0 or V <sub>O</sub> > V <sub>CC</sub> ) |     | ±50 mA  |
| I <sub>O</sub>               | Continuous output current                         | (V <sub>O</sub> = 0 to V <sub>CC</sub> )                  |     | ±50 mA  |
|                              | Continuous current through V <sub>CC</sub> or GND |                                                           |     | ±100 mA |
| T <sub>stg</sub>             | Storage temperature range                         | -65                                                       | 150 | °C      |

- (1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

### 4.2 ESD Ratings

|                    |                         | VALUE                                                             | UNIT    |
|--------------------|-------------------------|-------------------------------------------------------------------|---------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup> | ±2000 V |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

### 4.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                 |                                    |                                  | T <sub>A</sub> = 25°C |                 | -55°C to 125°C |                 | -40°C to 85°C |                 | UNIT |
|-----------------|------------------------------------|----------------------------------|-----------------------|-----------------|----------------|-----------------|---------------|-----------------|------|
|                 |                                    |                                  | MIN                   | MAX             | MIN            | MAX             | MIN           | MAX             |      |
| V <sub>CC</sub> | Supply voltage                     |                                  | 1.5                   | 5.5             | 1.5            | 5.5             | 1.5           | 5.5             | V    |
| V <sub>IH</sub> | High-level input voltage           | V <sub>CC</sub> = 1.5 V          | 1.2                   |                 | 1.2            |                 | 1.2           |                 | V    |
|                 |                                    | V <sub>CC</sub> = 3 V            | 2.1                   |                 | 2.1            |                 | 2.1           |                 |      |
|                 |                                    | V <sub>CC</sub> = 5.5 V          | 3.85                  |                 | 3.85           |                 | 3.85          |                 |      |
| V <sub>IL</sub> | Low-level input voltage            | V <sub>CC</sub> = 1.5 V          |                       | 0.3             |                | 0.3             |               | 0.3             | V    |
|                 |                                    | V <sub>CC</sub> = 3 V            |                       | 0.9             |                | 0.9             |               | 0.9             |      |
|                 |                                    | V <sub>CC</sub> = 5.5 V          |                       | 1.65            |                | 1.65            |               | 1.65            |      |
| V <sub>I</sub>  | Input voltage                      |                                  | 0                     | V <sub>CC</sub> | 0              | V <sub>CC</sub> | 0             | V <sub>CC</sub> | V    |
| V <sub>O</sub>  | Output voltage                     |                                  | 0                     | V <sub>CC</sub> | 0              | V <sub>CC</sub> | 0             | V <sub>CC</sub> | V    |
| I <sub>OH</sub> | High-level output current          | V <sub>CC</sub> = 4.5 V to 5.5 V |                       | -24             |                | -24             |               | -24             | mA   |
| I <sub>OL</sub> | Low-level output current           | V <sub>CC</sub> = 4.5 V to 5.5 V |                       | 24              |                | 24              |               | 24              | mA   |
| Δt/Δv           | Input transition rise or fall rate | V <sub>CC</sub> = 1.5 V to 3 V   |                       | 50              |                | 50              |               | 50              | ns/V |
|                 |                                    | V <sub>CC</sub> = 3.6 V to 5.5 V |                       | 20              |                | 20              |               | 20              |      |

- (1) All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

### 4.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                        | CDx4AC74 |          | UNIT |
|-------------------------------|----------------------------------------|----------|----------|------|
|                               |                                        | N (PDIP) | D (SOIC) |      |
|                               |                                        | 14 PINS  | 14 PINS  |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance | 80       | 119.9    | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 4.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS                       |                                 | $V_{CC}$ | $T_A = 25^\circ\text{C}$ |     | $-55^\circ\text{C to } 125^\circ\text{C}$ |     | $-40^\circ\text{C to } 85^\circ\text{C}$ |     | UNIT          |
|-----------|---------------------------------------|---------------------------------|----------|--------------------------|-----|-------------------------------------------|-----|------------------------------------------|-----|---------------|
|           |                                       |                                 |          | MIN                      | MAX | MIN                                       | MAX | MIN                                      | MAX |               |
| $V_{OH}$  | $V_I = V_{IH} \text{ or } V_{IL}$     | $I_{OH} = -50 \mu\text{A}$      | 1.5 V    | 1.4                      |     | 1.4                                       |     | 1.4                                      |     | V             |
|           |                                       |                                 | 3 V      | 2.9                      |     | 2.9                                       |     | 2.9                                      |     |               |
|           |                                       |                                 | 4.5 V    | 4.4                      |     | 4.4                                       |     | 4.4                                      |     |               |
|           |                                       | $I_{OH} = -4 \text{ mA}$        | 3 V      | 2.58                     |     | 2.4                                       |     | 2.48                                     |     |               |
|           |                                       | $I_{OH} = -24 \text{ mA}$       | 4.5 V    | 3.94                     |     | 3.7                                       |     | 3.8                                      |     |               |
|           |                                       | $I_{OH} = -50 \text{ mA}^{(1)}$ | 5.5 V    |                          |     | 3.85                                      |     |                                          |     |               |
| $V_{OL}$  | $V_I = V_{IH} \text{ or } V_{IL}$     | $I_{OL} = 50 \mu\text{A}$       | 1.5 V    | 0.1                      |     | 0.1                                       |     | 0.1                                      |     | V             |
|           |                                       |                                 | 3 V      | 0.1                      |     | 0.1                                       |     | 0.1                                      |     |               |
|           |                                       |                                 | 4.5 V    | 0.1                      |     | 0.1                                       |     | 0.1                                      |     |               |
|           |                                       | $I_{OL} = 12 \text{ mA}$        | 3 V      | 0.36                     |     | 0.5                                       |     | 0.44                                     |     |               |
|           |                                       | $I_{OL} = 24 \text{ mA}$        | 4.5 V    | 0.36                     |     | 0.5                                       |     | 0.44                                     |     |               |
|           |                                       | $I_{OL} = 50 \text{ mA}^{(1)}$  | 5.5 V    |                          |     | 1.65                                      |     |                                          |     |               |
| $I_L$     | $V_I = V_{CC} \text{ or } \text{GND}$ | $I_O = 0$                       | 5.5 V    | $\pm 0.1$                |     | $\pm 1$                                   |     | $\pm 1$                                  |     | $\mu\text{A}$ |
|           |                                       |                                 | 5.5 V    | 4                        |     | 80                                        |     | 40                                       |     | $\mu\text{A}$ |
| $C_i$     |                                       |                                 |          | 10                       |     | 10                                        |     | 10                                       |     | pF            |

- (1) Test one output at a time, not exceeding 1-second duration. Measurement is made by forcing indicated current and measuring voltage to minimize power dissipation. Test verifies a minimum 50- $\Omega$  transmission-line drive capability at 85°C and 75- $\Omega$  transmission-line drive capability at 125°C.

## 4.6 Timing Requirements, $V_{CC} = 1.5 \text{ V}$

over recommended operating free-air temperature range,  $V_{CC} = 1.5 \text{ V}$  (unless otherwise noted)

|                    |                                            |                                                                    | $-55^\circ\text{C to } 125^\circ\text{C}$ |     | $-40^\circ\text{C to } 85^\circ\text{C}$ |     | UNIT |
|--------------------|--------------------------------------------|--------------------------------------------------------------------|-------------------------------------------|-----|------------------------------------------|-----|------|
|                    |                                            |                                                                    | MIN                                       | MAX | MIN                                      | MAX |      |
| $f_{\text{clock}}$ | Clock frequency                            |                                                                    |                                           | 9   |                                          | 10  | MHz  |
| $t_w$              | Pulse duration                             | $\overline{\text{PRE}}$ or $\overline{\text{CLR}}$ low             |                                           | 50  |                                          | 44  | ns   |
|                    |                                            | CLK                                                                |                                           | 56  |                                          | 49  |      |
| $t_{\text{su}}$    | Setup time                                 | Data                                                               |                                           | 44  |                                          | 39  | ns   |
|                    |                                            | $\overline{\text{PRE}}$ or $\overline{\text{CLR}}$ inactive        |                                           |     |                                          |     | ns   |
| $t_h$              | Hold time                                  | Data after $\text{CLK}\uparrow$                                    |                                           | 0   |                                          | 0   | ns   |
| $t_{\text{rec}}$   | Recovery time, before $\text{CLK}\uparrow$ | $\overline{\text{CLR}}\uparrow$ or $\overline{\text{PRE}}\uparrow$ |                                           | 34  |                                          | 30  | ns   |

## 4.7 Timing Requirements, $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$

over recommended operating free-air temperature range,  $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

|                    |                 |                                                        | $-55^\circ\text{C to } 125^\circ\text{C}$ |     | $-40^\circ\text{C to } 85^\circ\text{C}$ |     | UNIT |
|--------------------|-----------------|--------------------------------------------------------|-------------------------------------------|-----|------------------------------------------|-----|------|
|                    |                 |                                                        | MIN                                       | MAX | MIN                                      | MAX |      |
| $f_{\text{clock}}$ | Clock frequency |                                                        |                                           | 79  |                                          | 90  | MHz  |
| $t_w$              | Pulse duration  | $\overline{\text{PRE}}$ or $\overline{\text{CLR}}$ low |                                           | 5.6 |                                          | 4.9 | ns   |
|                    |                 | CLK                                                    |                                           | 6.3 |                                          | 5.5 |      |

**CD54AC74, CD74AC74**

SCHS231E – NOVEMBER 1998 – REVISED AUGUST 2024

over recommended operating free-air temperature range,  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

|           |                            |                                               | –55°C to 125°C |     | –40°C to 85°C |     | UNIT |
|-----------|----------------------------|-----------------------------------------------|----------------|-----|---------------|-----|------|
|           |                            |                                               | MIN            | MAX | MIN           | MAX |      |
| $t_{su}$  | Setup time                 | Data                                          | 4.9            |     | 4.3           |     | ns   |
|           |                            | $\overline{PRE}$ or $\overline{CLR}$ inactive |                |     |               |     | ns   |
| $t_h$     | Hold time                  | Data after CLK↑                               | 0              |     | 0             |     | ns   |
| $t_{rec}$ | Recovery time, before CLK↑ | $\overline{CLR}$ ↑ or $\overline{PRE}$ ↑      | 4.7            |     | 4.1           |     | ns   |

**4.8 Timing Requirements,  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$** 

over recommended operating free-air temperature range,  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

|             |                            |                                               | –55°C to 125°C |     | –40°C to 85°C |     | UNIT |
|-------------|----------------------------|-----------------------------------------------|----------------|-----|---------------|-----|------|
|             |                            |                                               | MIN            | MAX | MIN           | MAX |      |
| $f_{clock}$ | Clock frequency            |                                               |                | 110 |               | 125 | MHz  |
| $t_w$       | Pulse duration             | $\overline{PRE}$ or $\overline{CLR}$ low      | 4              |     | 3.5           |     | ns   |
|             |                            | CLK                                           | 4.5            |     | 3.9           |     |      |
| $t_{su}$    | Setup time                 | Data                                          | 3.5            |     | 3.1           |     | ns   |
|             |                            | $\overline{PRE}$ or $\overline{CLR}$ inactive |                |     |               |     | ns   |
| $t_h$       | Hold time                  | Data after CLK↑                               | 0              |     | 0             |     | ns   |
| $t_{rec}$   | Recovery time, before CLK↑ | $\overline{CLR}$ ↑ or $\overline{PRE}$ ↑      | 2.7            |     | 2.4           |     | ns   |

**4.9 Switching Characteristics,  $V_{CC} = 1.5\text{ V}$** 

over recommended operating free-air temperature range,  $V_{CC} = 1.5\text{ V}$ ,  $C_L = 50\text{ pF}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

| PARAMETER | FROM (INPUT)                         | TO (OUTPUT)         | –55°C to 125°C |     | –40°C to 85°C |     | UNIT |
|-----------|--------------------------------------|---------------------|----------------|-----|---------------|-----|------|
|           |                                      |                     | MIN            | MAX | MIN           | MAX |      |
| $f_{max}$ |                                      |                     | 9              |     | 10            |     | MHz  |
| $t_{PLH}$ | CLK                                  | Q or $\overline{Q}$ |                | 125 |               | 114 | ns   |
| $t_{PHL}$ |                                      |                     |                | 125 |               | 114 |      |
| $t_{PLH}$ | $\overline{PRE}$ or $\overline{CLR}$ | Q or $\overline{Q}$ |                | 132 |               | 120 | ns   |
| $t_{PHL}$ |                                      |                     |                | 144 |               | 131 |      |

**4.10 Switching Characteristics,  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$** 

over recommended operating free-air temperature range,  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

| PARAMETER | FROM (INPUT)                         | TO (OUTPUT)         | –55°C to 125°C |      | –40°C to 85°C |      | UNIT |
|-----------|--------------------------------------|---------------------|----------------|------|---------------|------|------|
|           |                                      |                     | MIN            | MAX  | MIN           | MAX  |      |
| $f_{max}$ |                                      |                     | 79             |      | 90            |      | MHz  |
| $t_{PLH}$ | CLK                                  | Q or $\overline{Q}$ | 3.5            | 14   | 3.6           | 12.7 | ns   |
| $t_{PHL}$ |                                      |                     | 3.5            | 14   | 3.6           | 12.7 |      |
| $t_{PLH}$ | $\overline{PRE}$ or $\overline{CLR}$ | Q or $\overline{Q}$ | 3.7            | 14.7 | 3.8           | 13.4 | ns   |
| $t_{PHL}$ |                                      |                     | 4              | 16.1 | 4.1           | 14.6 |      |

#### 4.11 Switching Characteristics, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$

over recommended operating free-air temperature range,  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))


| PARAMETER  | FROM (INPUT)                         | TO (OUTPUT)    | -55°C to 125°C |      | -40°C to 85°C |      | UNIT |
|------------|--------------------------------------|----------------|----------------|------|---------------|------|------|
|            |                                      |                | MIN            | MAX  | MIN           | MAX  |      |
| $f_{\max}$ |                                      |                | 110            |      | 125           |      | MHz  |
| $t_{PLH}$  | CLK                                  | Q or $\bar{Q}$ | 2.5            | 10   | 2.6           | 9.1  | ns   |
| $t_{PHL}$  |                                      |                | 2.5            | 10   | 2.6           | 9.1  |      |
| $t_{PLH}$  | $\overline{PRE}$ or $\overline{CLR}$ | Q or $\bar{Q}$ | 2.6            | 10.5 | 2.7           | 9.5  | ns   |
| $t_{PHL}$  |                                      |                | 2.9            | 11.5 | 3             | 10.4 |      |

#### 4.12 Operating Characteristics

$T_A = 25^\circ\text{C}$


| PARAMETER |                               | TYP | UNIT |
|-----------|-------------------------------|-----|------|
| $C_{pd}$  | Power dissipation capacitance | 55  | pF   |

## 5 Parameter Measurement Information




$^\dagger$  When  $V_{CC} = 1.5\ \text{V}$ ,  $R1 = R2 = 1\ \text{k}\Omega$


LOAD CIRCUIT




VOLTAGE WAVEFORMS  
PULSE DURATION




VOLTAGE WAVEFORMS  
RECOVERY TIME



VOLTAGE WAVEFORMS  
SETUP AND HOLD AND INPUT RISE AND FALL TIMES



VOLTAGE WAVEFORMS  
PROPAGATION DELAY AND OUTPUT TRANSITION TIMES



VOLTAGE WAVEFORMS  
OUTPUT ENABLE AND DISABLE TIMES

Figure 5-1. Load Circuit and Voltage Waveforms



- A.  $C_L$  includes probe and test-fixture capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_r = 3 \text{ ns}$ ,  $t_f = 3 \text{ ns}$ . Phase relationships between waveforms are arbitrary.
- D. For clock inputs,  $f_{max}$  is measured with the input duty cycle at 50%.
- E. The outputs are measured one at a time with one input transition per measurement.
- F.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
- G.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
- H.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .

| TEST              | S1                |
|-------------------|-------------------|
| $t_{PLH}/t_{PHL}$ | Open              |
| $t_{PLZ}/t_{PZL}$ | $2 \times V_{CC}$ |
| $t_{PHZ}/t_{PZH}$ | GND               |

## 6 Detailed Description

### 6.1 Overview

The 'AC74 dual positive-edge-triggered devices are D-type flip-flops.

A low level at the preset (PRE) or clear (CLR) inputs sets or resets the outputs, regardless of the levels of the other inputs. When PRE and CLR are inactive (high), data at the data (D) input meeting the setup time requirements is transferred to the outputs on the positive-going edge of the clock pulse. Clock triggering occurs at a voltage level and is not related directly to the rise time of the clock pulse. Following the hold-time interval, data at the D input can be changed without affecting the levels at the outputs.

### 6.2 Functional Block Diagram




Figure 6-1.

### 6.3 Device Functional Modes

Table 6-1. Function Table (Each Flip-flop)

| INPUTS |     |     |   | OUTPUTS          |                  |
|--------|-----|-----|---|------------------|------------------|
| PRE    | CLR | CLK | D | Q                | $\bar{Q}$        |
| L      | H   | X   | X | H                | L                |
| H      | L   | X   | X | L                | H                |
| L      | L   | X   | X | H <sup>(1)</sup> | H <sup>(1)</sup> |
| H      | H   | ↑   | H | H                | L                |
| H      | H   | ↑   | L | L                | H                |
| H      | H   | L   | X | Q <sub>0</sub>   | $\bar{Q}_0$      |

- (1) This configuration is nonstable; that is, it does not persist when PRE or CLR returns to its inactive (high) level.

## 7 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### Power Supply Recommendations

The power supply may be any voltage between the minimum and maximum supply voltage rating located in [Section 4.3](#).

Each  $V_{CC}$  terminal must have a good bypass capacitor to prevent power disturbance. A 0.1- $\mu$ F capacitor is recommended for devices with a single supply. If there are multiple  $V_{CC}$  terminals, then 0.01- $\mu$ F or 0.022- $\mu$ F capacitors are recommended for each power terminal. It is permissible to parallel multiple bypass capacitors to reject different frequencies of noise. Multiple bypass capacitors may be paralleled to reject different frequencies of noise. The bypass capacitor must be installed as close to the power terminal as possible for the best results.


### 7.1 Layout

#### 7.1.1 Layout Guidelines

Inputs must not float when using multiple bit logic devices. In many cases, functions or parts of functions of digital logic devices are unused. Some examples include situations when only two inputs of a triple-input AND gate are used, or when only 3 of the 4-buffer gates are used. Such input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states.

Specified in [Layout Example for the CD74AC74](#) are rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, they are tied to GND or  $V_{CC}$ , whichever makes more sense or is more convenient.

#### 7.1.2 Layout Example



**Figure 7-1. Example layout for the CD74AC74**

## 8 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 8.1 Documentation Support (Analog)

#### 8.1.1 Related Documentation

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

**Table 8-1. Related Links**

| PARTS    | PRODUCT FOLDER             | SAMPLE & BUY               | TECHNICAL DOCUMENTS        | TOOLS & SOFTWARE           | SUPPORT & COMMUNITY        |
|----------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| CD54AC74 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| CD74AC74 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |

### 8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](#). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 8.3 Support Resources

TI E2E™ [support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 8.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 8.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 8.6 Glossary

[TI Glossary](#)

This glossary lists and explains terms, acronyms, and definitions.

## 9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision D (December 2002) to Revision E (August 2024)                                                                                                                                                                                                                                                                         | Page |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Added <i>Device Information</i> table, <i>Pin Functions</i> table, <i>ESD Ratings</i> table, <i>Thermal Information</i> table, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section ..... | 1    |
| • Updated RθJA values: D = 86 to 119.9, all values in °C/W.....                                                                                                                                                                                                                                                                             | 4    |

## 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">CD54AC74F3A</a> | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54AC74F3A         |
| CD54AC74F3A.A               | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54AC74F3A         |
| <a href="#">CD74AC74E</a>   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74AC74E           |
| CD74AC74E.A                 | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74AC74E           |
| <a href="#">CD74AC74M</a>   | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | AC74M               |
| <a href="#">CD74AC74M96</a> | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | AC74M               |
| CD74AC74M96.A               | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | AC74M               |
| CD74AC74M961G4              | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | AC74M               |
| CD74AC74M961G4.A            | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | AC74M               |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF CD54AC74, CD74AC74 :**

- Catalog : [CD74AC74](#)
- Military : [CD54AC74](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications


## TUBE




\*All dimensions are nominal

| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD74AC74E   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74AC74E   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74AC74E.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74AC74E.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |



**D0014A****PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

**NOTES:**


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.

# EXAMPLE BOARD LAYOUT


D0014A

SOIC - 1.75 mm max height


SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



NON SOLDER MASK  
DEFINED



SOLDER MASK  
DEFINED

SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

**J 14**

## GENERIC PACKAGE VIEW

**CDIP - 5.08 mm max height**


CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4040083-5/G


J0014A



## PACKAGE OUTLINE

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

### NOTES:


1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

# EXAMPLE BOARD LAYOUT



J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 5X




4214771/A 05/2017


N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **<br>DIM      | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

NOTES:

- A. All linear dimensions are in inches (millimeters).  
B. This drawing is subject to change without notice.
-  Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).  
 The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025