

Customer Information Sheet

DRAWING No.: R30-500XX02

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)



NOT TO SCALE

THIRD ANGLE PROJECTION



ALL DIMENSIONS IN mm

ALL SPACERS UP TO
& INCLUDING 25mm LONG

25mm SPACER DOES NOT REQUIRE
THE TAPPED HOLE TO BE THRO, BUT
MUST HAVE A MINIMUM THREAD LENGTH
OF 10mm FROM BOTH ENDS.



ALL SPACERS
OVER 25mm LONG



PART No.	LI
R30-5000402	4.00
R30-5000502	5.00
R30-5000602	6.00
R30-5000702	7.00
R30-5000802	8.00
R30-5000902	9.00

PART No.	LI
R30-5001002	10.00
R30-5001102	11.00
R30-5001202	12.00
R30-5001302	13.00
R30-5001402	14.00
R30-5001502	15.00

PART No.	LI
R30-5001602	16.00
R30-5001802	18.00
R30-5002002	20.00
R30-5002502	25.00
R30-5005502	55.00

ORDER CODE:
R30-500XX02
LENGTH LI IN mm

CP	6	19.03.10	10710
NAME	ISS.	DATE	C/NOTE
APPROVED:		C.PENROSE	
CHECKED:		R.ADDE	
DRAWN:		WJ BOURNE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

BRASS
CW614N M TO BS EN 12164
(CuZn39Pb3)

FINISH: NICKEL

S/AREA: mm²

TITLE:

M3 CIRCULAR
FEMALE SPACER

DRAWING NUMBER:

R30-500XX02

SHT
2 OF 2