

CMOS Analog Switches

FEATURES

- Analog Signal Range: $\pm 15\text{ V}$
- Fast Switching— t_{ON} : 150 ns
- Low On-Resistance— $r_{\text{DS(on)}}$: 30 Ω
- Single Supply Operation
- Latch-up Proof
- CMOS Compatible

BENEFITS

- Full Rail-to-Rail Analog Signal Range
- Low Signal Error
- Low Power Dissipation

APPLICATIONS

- Low Level Switching Circuits
- Programmable Gain Amplifiers
- Portable and Battery Powered Systems

DESCRIPTION



The DG300A/DG301A/DG302A monolithic CMOS switches feature three switch configuration options (SPST, SPDT, and DPST) for precision applications in communications, instrumentation and process control, where low leakage switching combined with low power consumption are required.

Designed on the Vishay Siliconix PLUS-40 CMOS process, these switches are latch-up proof, and are designed to block up to 30 V peak-to-peak when off. An epitaxial layer prevents latchup.

In the on condition the switches conduct equally well in both directions (with no offset voltage) and minimize error conditions with their low on-resistance.



Featuring low power consumption (3.5 mW typ) these switches are ideal for battery powered applications, without sacrificing switching speed. Designed for break-before-make switching action, these devices are CMOS and quasi TTL compatible. Single supply operation is allowed by connecting the V– rail to 0 V.

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE	
Logic	Switch
0	OFF
1	ON


Logic "0" $\leq 0.8\text{ V}$
Logic "1" $\geq 4\text{ V}$



TRUTH TABLE		
Logic	SW ₁	SW ₂
0	OFF	ON
1	ON	OFF

Logic "0" $\leq 0.8\text{ V}$
Logic "1" $\geq 4\text{ V}$

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE	
Logic	Switch
0	OFF
1	ON

Logic "0" ≤ 0.8 V
Logic "1" ≥ 4 V

ORDERING INFORMATION		
Temp Range	Package	Part Number
DG300A		
0 to 70°C	14-Pin Plastic DIP	DG300ACJ
-55 to 125°C	14-Pin CerDIP	DG300AAK
		DG300AAK/883
		JM38510/11601BCA
	14-Pin Sidebrazed	JM38510/11601BCC
	10-Pin Metal Can	DG300AAA/883
		JM38510/11601BIA
DG301A		
0 to 70°C	14-Pin Plastic DIP	DG301ACJ
-55 to 125°C	14-Pin CerDIP	DG301AAK/883
		JM38510/11602BCA
	14-Pin Sidebrazed	JM38510/11602BCC
	10-Pin Metal Can	DG301AAA
		DG301AAA/883
		JM38510/11602BIA
DG302A		
0 to 70°C	14-Pin Plastic DIP	DG302ACJ
-55 to 125°C	14-Pin CerDIP	DG302AAK
		DG302AAK/883
		JM38510/11603BCA
	14-Pin Sidebrazed	JM38510/11603BCC

ABSOLUTE MAXIMUM RATINGS

Voltages Referenced to V₋

V₊ 44 V

GND 25 V

Digital Inputs^{NO TAG}, V_S, V_D (V₋) -2 V to (V₊) +2V or
30 mA, whichever occurs first

Current, Any Terminal 30 mA

Continuous Current, S or D
(Pulsed at 1 ms, 10% duty cycle max) 100 mA

Storage Temperature (A Suffix) -65 to 150°C
(C Suffix) -65 to 125°C

Power Dissipation^{NO TAG}

14-Pin Plastic DIP^{NO TAG} 470 mW

14-Pin CerDIP^{NO TAG} 825 mW

10-Pin Metal Can^{NO TAG} 450 mW

Notes:

- Signals on S_X, D_X, or IN_X exceeding V₊ or V₋ will be clamped by internal diodes. Limit forward diode current to maximum current ratings.
- All leads welded or soldered to PC Board.
- Derate 6.5 mW/°C above 25°C
- Derate 11 mW/°C above 75°C
- Derate 6 mW/°C above 75°C

SCHEMATIC DIAGRAM (TYPICAL CHANNEL)










FIGURE 1.

**SPECIFICATIONS^a**







Parameter	Symbol	Test Conditions Unless Specified V+ = 15 V, V− = −15 V VIN = 0.8 V or VIN = 4 V ^f	Temp ^b	Typ ^c	A Suffix −55 to 125°C		C Suffix 0 to 70°C		Unit
					Min ^d	Max ^d	Min ^d	Max ^d	
Analog Switch									
Analog Signal Range ^e	V _{ANALOG}		Full		−15	15	−15	15	V
Drain-Source On-Resistance	r _{DS(on)}	V _D = ±10 V, I _S = −10 mA	Room Full	30		50 75		50 75	Ω
Source Off Leakage Current	I _{S(off)}	V _S = ±14 V, V _D = ∓14 V	Room Hot	±0.1	−1 −100	1 100	−5 −100	5 100	nA
Drain Off Leakage Current	I _{D(off)}		Room Hot	±0.1	−1 −100	1 100	−5 −100	5 100	
Drain On Leakage Current	I _{D(on)}	V _D = V _S = ±14 V	Room Hot	±0.1	−1 −100	1 100	−5 −100	5 100	
Digital Control									
Input Current with Input Voltage High	I _{INH}	V _{IN} = 5 V	Room Full	−0.001	−1 −1		−1		μA
		V _{IN} = 15 V	Room Full	0.001		1 1		1	
Input Current with Input Voltage Low	I _{INL}	V _{IN} = 0 V	Room Full	−0.001	−1 −1		−1		
Dynamic Characteristics									
Turn-On Time	t _{ON}	See Figure NO TAG	Room	150		300			ns
Turn-Off Time	t _{OFF}		Room	130		250			
Break-Before-Make Time	t _{OPEN}	DG301A Only Figure NO TAG	Room	50					
Charge Injection	Q	C _L = 1 nF, R _{gen} = 0 Ω V _{gen} = 0 V, Figure NO TAG	Room	8					pC
Source-Off Capacitance	C _{S(off)}	V _S , V _D = 0 V, f = 1 MHz	Room	14					pF
Drain-Off Capacitance	C _{D(off)}		Room	14					
Channel-On Capacitance	C _{D(on)}		Room	40					
Input Capacitance	C _{in}	f = 1 MHz		V _{IN} = 0 V	Room	6			
				V _{IN} = 15 V	Room	7			
Off-Isolation	OIRR	V _{IN} = 0 V, R _L = 1 kΩ V _S = 1 V _{rms} , f = 500 kHz	Room	62					dB
Crosstalk (Channel-to-Channel)	X _{TALK}		Room	74					
Power Supplies									
Positive Supply Current	I ⁺	V _{IN} = 4 V (One Input) All Others = 0 V	Room Full	0.23		0.5 1		1	mA
Negative Supply Current	I [−]		Room Full	−0.001	−10 −100		−100		
Positive Supply Current	I ⁺	V _{IN} = 0.8 V (All Inputs)	Room Full	0.001		10 100		100	μA
Negative Supply Current	I [−]		Room Full	−0.001	−10 −100		−100		







Notes:

- Refer to PROCESS OPTION FLOWCHART.
- Room = 25°C, Full = as determined by the operating temperature suffix.
- Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
- The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this data sheet.
- Guaranteed by design, not subject to production test.
- V_{IN} = input voltage to perform proper function.

**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)**

TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)



TEST CIRCUITS

FIGURE 2. Switching Time

FIGURE 3. Break-Before-Make SPDT (DG301A)

FIGURE 4. Charge Injection


APPLICATION HINTS^{NO TAG}

V+ Positive Supply Voltage (V)	V- Negative Supply Voltage (V)	GND Voltage (V)	V _{IN} Logic Input Voltage V _{INH(min)} /V _{INL(max)} (V)	V _S or V _D Analog Voltage Range (V)
15	-15	0	4/0.8	-15 to 15
20	-20	0	4/0.8	-20 to 20
15	0	0	4/0.8	0 to 15

Note:

a. Application Hints are for DESIGN AID ONLY, not guaranteed and not subject to production testing.

APPLICATIONS

The DG300A series of analog switches will switch positive analog signals while using a single positive supply. This facilitates their use in applications where only one supply is available. The trade-offs of using single supplies are:

1) Increased $r_{DS(on)}$; 2) slower switching speed. The analog voltage should not go above or below the supply voltages which in single operation are V+ and 0 V. (See Input Switching Threshold vs. Positive Supply Voltage Curve.)




FIGURE 5. Single Supply Op Amp Switching


APPLICATIONS


FIGURE 6. Low Power Instrumentation Amplifier with Digitally Selectable Inputs and Gain