




## Features

- TO-220 housing
- Low inductance
- Resistor electrically isolated from the backplate
- High power rating
- AEC-Q200 qualified
- RoHS compliant\*

## Applications

- Power supplies
- Motor drives
- Test and measurement
- Rectifiers

## PWR220T-35 Series Power Resistor

### General Information

Bourns® PWR220T-35 Series is a TO-220 DPAK style power resistor. Manufactured using thick film on alumina ceramic technology, it is used in current measurement, snubber, bleeder and discharge circuits.

### Electrical & Thermal Characteristics

| Parameter                                        | Value(s)                                   |
|--------------------------------------------------|--------------------------------------------|
| Resistance (See Popular Resistance Values table) | 0.02 $\Omega$ to 130 K $\Omega$            |
| Power Rating @ 25 °C Case Temperature            | 35 W                                       |
| Tolerance                                        | $\pm 1\%$ **, $\pm 5\%$                    |
| TCR<br>0.02 $\Omega$ < R < 130.0K $\Omega$       | $\pm 100$ PPM/°C                           |
| Thermal Resistance - R <sub>thj</sub>            | 3.7 °C/W                                   |
| Inductance                                       | 0.1 $\mu$ H maximum                        |
| Operating Voltage                                | $\sqrt{P \cdot R}$ with a maximum of 250 V |
| Dielectric Strength                              | 2 KV AC                                    |
| Insulation Resistance                            | 10 G $\Omega$                              |
| Operating Temperature                            | -55 °C to 155 °C                           |

\*\* Available for most values. Check Popular Resistance Values table.

### Reliability Characteristics

| Parameter                                                                                                       | Specification           |
|-----------------------------------------------------------------------------------------------------------------|-------------------------|
| Short Term Overload (2x Pr for R < 2 $\Omega$ , 1.6 x Pr for R $\geq$ 2 $\Omega$ , V < 1.5 x Operating Voltage) | $\Delta R$ $\pm 0.25\%$ |
| Load Life (1000 hours at rated power)                                                                           | $\Delta R$ $\pm 1.0\%$  |
| Thermal Shock (-55 °C to 155 °C, 5 cycles)                                                                      | $\Delta R$ $\pm 0.5\%$  |
| Resistance to Soldering Heat (10 seconds at 270 °C)                                                             | $\Delta R$ $\pm 0.5\%$  |
| Vibration (20 G 10-2000 Hz .06 " D.A.)                                                                          | $\Delta R$ $\pm 0.25\%$ |
| Terminal Strength (MIL-STD-202, Method 211 Test A1)                                                             | $\Delta R$ $\pm 0.2\%$  |
| Shock (Saw Tooth: 100 g/6 ms)                                                                                   | $\Delta R$ $\pm 0.5\%$  |
| Humidity (Steady State) 1000 hrs. 85 °C/85 % RH                                                                 | $\Delta R$ $\pm 0.5\%$  |
| High Temperature Exposure (100 hrs - 40 % Pr @ +125 °C)                                                         | $\Delta R$ $\pm 0.5\%$  |


### Material Characteristics

Resistor ..... Thick film  
Substrate ..... Alumina (AL2O3)  
Housing ..... Epoxy  
Pins ..... Tinned Copper (Sn/Cu)  
Flammability ..... Conforms to UL-94V0

### Packaging

..... 50 pcs./tube

### Typical Part Marking



### Popular Resistance Values

| Code | Resistance Value   | Code | Resistance Value |
|------|--------------------|------|------------------|
| R020 | 0.02 $\Omega$ ***  | 1000 | 100 $\Omega$     |
| R025 | 0.025 $\Omega$ *** | 1200 | 120 $\Omega$     |
| R030 | 0.03 $\Omega$ ***  | 1500 | 150 $\Omega$     |
| R033 | 0.033 $\Omega$ *** | 2000 | 200 $\Omega$     |
| R040 | 0.04 $\Omega$ ***  | 2500 | 250 $\Omega$     |
| R050 | 0.05 $\Omega$ ***  | 3000 | 300 $\Omega$     |
| R075 | 0.075 $\Omega$ *** | 3300 | 330 $\Omega$     |
| R100 | 0.1 $\Omega$       | 4000 | 400 $\Omega$     |
| R150 | 0.15 $\Omega$      | 4700 | 470 $\Omega$     |
| R200 | 0.2 $\Omega$       | 5000 | 500 $\Omega$     |
| R250 | 0.25 $\Omega$      | 5600 | 560 $\Omega$     |
| R300 | 0.3 $\Omega$       | 7500 | 750 $\Omega$     |
| R330 | 0.33 $\Omega$      | 1001 | 1.0 K $\Omega$   |
| R400 | 0.4 $\Omega$       | 1501 | 1.5 K $\Omega$   |
| R500 | 0.5 $\Omega$       | 2001 | 2.0 K $\Omega$   |
| R750 | 0.75 $\Omega$      | 2501 | 2.5 K $\Omega$   |
| 1R00 | 1 $\Omega$         | 3001 | 3.0 K $\Omega$   |
| 1R50 | 1.5 $\Omega$       | 3301 | 3.3 K $\Omega$   |
| 2R00 | 2 $\Omega$         | 4001 | 4.0 K $\Omega$   |
| 2R50 | 2.5 $\Omega$       | 5001 | 5.0 K $\Omega$   |
| 3R00 | 3 $\Omega$         | 7501 | 7.5 K $\Omega$   |
| 3R30 | 3.3 $\Omega$       | 1002 | 10 K $\Omega$    |
| 4R00 | 4 $\Omega$         | 1502 | 15 K $\Omega$    |
| 5R00 | 5 $\Omega$         | 2002 | 20 K $\Omega$    |
| 7R50 | 7.5 $\Omega$       | 2502 | 25 K $\Omega$    |
| 8R00 | 8 $\Omega$         | 3002 | 30 K $\Omega$    |
| 10R0 | 10 $\Omega$        | 3302 | 33 K $\Omega$    |
| 12R0 | 12 $\Omega$        | 4002 | 40 K $\Omega$    |
| 15R0 | 15 $\Omega$        | 4702 | 47 K $\Omega$    |
| 20R0 | 20 $\Omega$        | 5002 | 50 K $\Omega$    |
| 25R0 | 25 $\Omega$        | 5602 | 56 K $\Omega$    |
| 27R0 | 27 $\Omega$        | 6802 | 68 K $\Omega$    |
| 30R0 | 30 $\Omega$        | 7502 | 75 K $\Omega$    |
| 33R0 | 33 $\Omega$        | 8202 | 82 K $\Omega$    |
| 40R0 | 40 $\Omega$        | 1003 | 100 K $\Omega$   |
| 47R0 | 47 $\Omega$        | 1153 | 115 K $\Omega$   |
| 50R0 | 50 $\Omega$        | 1203 | 120 K $\Omega$   |
| 56R0 | 56 $\Omega$        | 1253 | 125 K $\Omega$   |
| 75R0 | 75 $\Omega$        | 1303 | 130 K $\Omega$   |

\*\*\* 5 % Tolerance

\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.


Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.


# PWR220T-35 Series Power Resistor

**BOURNS®**

## Product Dimensions



## Pulse Power Rating



The energy absorbed by the resistor expressed in Joules can be calculated by multiplying the peak power of the pulse in watts times the length of the pulse in seconds.

The energy should not exceed the limits shown in the graph. The overload voltage should not exceed 1.5 times the maximum operating voltage.

## How to Order

**PWR 220 T - 35 - 10R0 F**

Model \_\_\_\_\_  
PWR = Power Resistor

Package \_\_\_\_\_  
220 = TO-220 Style

Pin Style \_\_\_\_\_  
T = Through-hole


Power \_\_\_\_\_  
35 = 35 W

Resistance Value \_\_\_\_\_  
<100 ohms ... "R" represents decimal point  
(examples: 7R50 = 7.5  $\Omega$ ; R500 = 0.5  $\Omega$ )

$\geq 100$  ohms.... First three digits are significant, fourth digit represents number of zeros to follow  
(examples: 2000 = 200 ohms; 3002 = 30K ohms)

Absolute Tolerance \_\_\_\_\_  
J = 5 %  
F = 1 %

## Derating Curve



REV. 05/15

Specifications are subject to change without notice. The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.