

LAN Components

10BASE-T

Pulse Transformers

TLA-3T105/109/110/112


FEATURES

- 16-pin SOP package (1.27mm=50mil pin pitch).
- TLA-3T105 is suitable for use with AMD's Am79C984A, 985, 988A.
- TLA-3T109 is suitable for use with LSI LOGIC's 80C24, 80C25, NS's DP83959, LEVEL ONE's LXT905, 908.
- TLA-3T110 is suitable for use with LEVEL ONE's LXT901A, 907A, 914, 915, 944, FUJITSU's MB86964, CIRRUS LOGIC's CS8900A(5V).
- TLA-3T112 is suitable for use with CIRRUS LOGIC's CS8900A(3.3V).
- Tape and reel packaging are available (TLA-3T1□□-T: Tape and reel, TLA-3T1 □□: Bulk).
- ISO9001/QS9000 quality standards certification.


GENERAL SPECIFICATIONS

Pulse transformer	2
Common-mode choke	2
Port	1
Operating temperature range	0 to +70°C
Storage temperature range	-40 to +85°C
Withstanding voltage	Erms:2000V[60s]

SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM



RECOMMENDED PC BOARD PATTERN



ELECTRICAL CHARACTERISTICS

Part No.	Turns ratio 1,2,3:16,15,14 6,7,8:11,10,9	Inductance (μH)min.[100kHz] 1-3 6-8	Leakage inductance (μH)max.[100kHz] 1-3[16-14 shorted] 6-8[11-9 shorted]	Inter-winding stray capacitance (pF)max.[100kHz] 1,3-16,14 6,8-11,9	DC resistance (Ω)max. 1-3 6-8
TLA-3T105(-T)	1CT:1CT	130	0.3	12	0.5
	1CT:1CT	130	0.3	12	0.5
TLA-3T109(-T)	2CT:1CT	130	0.35	12	0.5
	1CT:1CT	130	0.35	12	0.5
TLA-3T110(-T)	1CT:1CT	130	0.35	12	0.5
	1CT:1.41CT	130	0.35	12	0.5
TLA-3T112(-T)	1CT:1CT	130	0.35	12	0.85
	1CT:2.5CT	130	0.35	12	0.85

• Ta=25°C

LAN Components

10BASE-T


Pulse Transformers

TLA-3T105/109/110/112

PACKAGING STYLES


Quantity : 1000pieces/reel

TAPE DIMENSIONS



Dimensions in mm

REEL DIMENSIONS




Dimensions in mm

A	B	C	D	E	F	W	W ₁
ø330±2	ø80±1	ø13.5±0.2	ø21±0.8	2±0.5	3-40°	24.4+2, -0	2±0.5

RECOMMENDED SOLDERING CONDITION

REFLOW SOLDERING



- Temperature is measured on the top of products body(Using thermocoupler for measurement).
- This profile is reference data we recommend. Please check in your actual process.