





10 9 8 7 6 5 4 3 2 1




10.0	19.5	17.6	20.26	502430-9030	90
	17.5	15.6	18.26	502430-8030	80
	15.5	13.6	16.26	502430-7030	70
7.0	13.5	11.6	14.26	502430-6030	60
	11.5	9.6	12.26	502430-5030	50
4.0	9.5	7.6	10.26	502430-4030	40
	7.9	6.0	8.66	502430-3230	32
3.4	6.7	4.8	7.46	502430-2630	26
	6.3	4.4	7.06	502430-2430	24
	5.9	4.0	6.66	502430-2230	22
2.4	5.5	3.6	6.26	502430-2030	20
	4.3	2.4	5.06	502430-1430	14
D	C	B	A	EMBOSSED TAPE PACKAGE ORDER No.	CKT.

CONNECTOR SERIES No. : 502430-***39

REVISED EC NO: J2010-1588 DRWN: TANI GUCHI 01/2010/02/02 CHKD: THIRATA 2010/02/02 APPR: MSASAO 2010/02/03	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	DRAWN BY RTAKEUCHI	DATE 2007/12/26	TITLE 0.4 B-TO-B CONN. HGT=1.0 W=2.6 PLUG ASSY WITH TAPE				
		10 OVER 30 UNDER	± ---	CHECKED BY MSASAO	DATE 2007/12/26					
		30 OVER	± ---	APPROVED BY MSASAO	DATE 2007/12/26	MOLEX INCORPORATED				
		ANGULAR ± --- °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-502430-003		1 OF 2			
D	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



嵌合断面図 (参考)
MATED DRAWING (REFERENCE)



P.C.BOARD PATTERN LAYOUT
(REFERENCE)

注記 NOTES

1. 使用材料 MATERIAL
- ウェハー : 液晶ポリマー (LCP) ガラス充填 UL94V-0 (黒)
WAFER:LIQUID CRYSTAL POLYMER(GLASS FILLED) UL94V-0 (COLOR:BLACK)
- ピン : りん青銅 (t=0.08)
PIN : PHOSPHOR BRONZE (t=0.08)
- 金具 : りん青銅 (t=0.15)
FITTING NAIL : PHOSPHOR BRONZE (t=0.15)
- 吸着テープ : ポリイミド
VACUUM TAPE : POLYIMIDE

2. メッキ仕様 PLATING
- ピン PIN
- 金メッキ 0.1 マイクロメートル以上
GOLD 0.2MICROMETER MINIMUM
- 下地メッキ : ニッケルメッキ 1.0 マイクロメートル以上
UNDER PLATING : NICKEL 1.0MICROMETER MINIMUM
- ※コンタクト部とテール部はニッケルメッキによって分断されている金メッキです。
DIVIDE INTO PARTS THE GOLD PLATING OF THE CONTACT AND THE TAIL PART BY THE NICKEL PLATING.
- ※封孔処理品


- 金具 FITTING NAIL
- フラッシュ金メッキ
FLASH Au PLATING
- 下地メッキ : ニッケルメッキ 1.0 マイクロメートル以上
UNDER PLATING : NICKEL 1.0MICROMETER MINIMUM

- △ (全極数 / 2) = 偶数の場合に適用。
APPLY FOR (CIRCUIT/2)=EVEN.
4. 嵌合相手 : 502426 シリーズ
MATE WITH : 502426 SERIES.
5. テール平坦度は、 0.08 以下
テール及び金具の平坦度は、 0.1 以下
TAIL COPLANARITY TO BE 0.08MAXIMUM.
TAIL AND FITTING NAIL COPLANARITY TO BE 0.1MAXIMUM.
6. ELV 及び RoHS適合品
ELV AND RoHS COMPLIANT.
- △ 斜線部はパターン書込み禁止範囲と半田禁止範囲を示す。
ただし、斜線部に同一配線を配置する場合はレジストを施し、この部分に半田は無きこと。
NO PATTERN CIRCUIT AND NO SOLDER ALLOWED IN THE SHADED AREA.
HOWEVER, IF NEEDED TO ADD A TRACE OF THE SAME CIRCUIT, PUT THE SOLDER-RESIST, YET NO SOLDER ALLOWED IN THE AREA.



REVISED EC NO: J2010-1588 DRWN: TIAN GUCHI 012010/02/02 CHKD: THIRATA 2010/02/02 APPR: MSASAO 2010/02/03	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	DRAWN BY RTAKEUCHI	DATE 2007/12/26	TITLE 0.4 B-TO-B CONN. HGT=1.0 W=2.6 PLUG ASSY WITH TAPE				
		10 OVER 30 UNDER	± ---	CHECKED BY MSASAO	DATE 2007/12/26					
		30 OVER	± ---	APPROVED BY MSASAO	DATE 2007/12/26	MOLEX INCORPORATED				
		ANGULAR	± --- °	MATERIAL NO. SEE SHEET 1						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

注記 NOTES


- 製品詳細寸法については製品単体図面を参照下さい。
RE DETAILED DIMENSION, SEE PRODUCT DRAWING.
- 梱包数量 : 3000 個/リール
NUMBER OF CONNECTORS : 3000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- 材料 MATERIAL
キャリアテープ (CARRIER TAPE) : ポリスチレン (POLYSTYRENE)
トップテープ (TOP TAPE) : PET , PE , PEF
リール (REEL) : ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>
- ELV 及び RoHS 適合品。
ELV AND RoHS COMPLIANT.



REVISED EC NO: J2010-1588 DRWN: TIAN GUCHI 012010/02/02 CHKD: THIRATA 2010/02/02 APPR: MSASAO 2010/02/03	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	MODEL NO. 502430-***30	THIRD ANGLE PROJECTION
		10 UNDER	± ---	DRAWN BY RTAKEUCHI	DATE 2007/12/26	TITLE 0.4 B-TO-B CONN. HGT=1.0 W=2.6 PLUG WITH TAPE EMBSTP PKG			
		10 OVER 30 UNDER	± ---	CHECKED BY MSASAO	DATE 2007/12/26				
		30 OVER	± ---	APPROVED BY MSASAO	DATE 2007/12/26	MOLEX INCORPORATED			
		ANGULAR ± --- °		MATERIAL NO.					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-502430-004		1 OF 4	
D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							



16	21.4	17.4	7.58	502430-2630		26
			7.18	502430-2430		24
			6.78	502430-2230		22
			6.38	502430-2030		20
			5.18	502430-1430		14
キャリアテープ幅 CARRIER TAPE WIDTH	C	B	(A)	MATERIAL No.		CKT.
				MODEL No.	502430-**30	

REVISED

EC NO.: J2010-1588

DRWN: TANI GUCHI 01 2010/02/02

CHKD: THIRATA 2010/02/02

APPR: MSASAO 2010/02/03

REV

GENERAL TOLERANCES
(UNLESS SPECIFIED)

10 UNDER ± ---

10 OVER 30 UNDER ± ---

30 OVER ± ---

ANGULAR ± --- °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY RTAKEUCHI

DATE 2007/12/26

CHECKED BY MSASAO

DATE 2007/12/26

APPROVED BY MSASAO

DATE 2007/12/26

MATERIAL NO.

SEE TABLE

SIZE A3

DIMENSION STYLE
MM ONLY

SCALE ---

DESIGN UNITS
METRIC


THIRD ANGLE
PROJECTION

0.4 B-T-O-B CONN. HGT=1.0
W=2.6 PLUG WITH TAPE
EMBSTP PKG

MOLEX INCORPORATED


DOCUMENT NO. SD-502430-004

SHEET NO. 2 OF 4



24	29.4	25.4	14.38	502430-6030		60
			12.38	502430-5030		50
			10.38	502430-4030		40
			8.78	502430-3230		32
キャリアテープ幅 CARRIER TAPE WIDTH	C	B	(A)	MATERIAL No.		CKT.
				MODEL No.	502430-***30	

REVISED EC NO: J2010-1588 DRWN: TIAN GUCHI 012010/02/02 CHKD: THIRATA 2010/02/02 APPR: MSASAO 2010/02/03	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		10 UNDER ± ---		DRAWN BY DATE RTAKEUCHI 2007/12/26		TITLE 0.4 B-TO-B CONN. HGT=1.0 W=2.6 PLUG WITH TAPE EMBSTP PKG			
		10 OVER 30 UNDER ± ---		CHECKED BY DATE MSASAO 2007/12/26					
		30 OVER ± ---		APPROVED BY DATE MSASAO 2007/12/26					
		ANGULAR ± --- °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-502430-004		3 OF 4	
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			



32	37.4	33.4	20.38	502430-9030	90
			18.38	502430-8030	80
			16.38	502430-7030	70
キャリアテープ幅 CARRIER TAPE WIDTH	C	B	(A)	MATERIAL No.	CKT.
				MODEL No.	502430-**30

REVISED	EC NO: J2010-1588 DRAWN: TIAN GUOCHI 01/2010/02/02 CHKD: 2010/02/02 APPR: MSASAO 2010/02/03	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
			10 UNDER	± ---	DRAWN BY	DATE	TITLE 0.4 B-TO-B CONN. HGT=1.0 W=2.6 PLUG WITH TAPE EMBSTP PKG		
			10 OVER 30 UNDER	± ---	CHECKED BY	DATE			
			30 OVER	± ---	APPROVED BY	DATE			
			ANGULAR	± --- °	MSASAO	2007/12/26	MOLEX INCORPORATED		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-502430-004		SHEET NO. 4 OF 4
	D	REV				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		