


D

C

B

A



1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
2. MATES WITH PLUG P/N 172167-1.
3. COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
4. RECOMMENDED FOR EDGE MOUNTING.
5. 0.00381 MIN MATTE TIN LEAD OVER 0.00127 MIN NICKEL ENTIRE LENGTH OF PIN.
6. 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MIN MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
7. 0.00381 MIN MATTE TIN OVER 0.00127 MIN NICKEL ENTIRE LENGTH OF PIN.
8. 0.00076 MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 MIN MATTE TIN IN THE LOCALIZED TIN PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57 THICK P.C. BOARD

2.070	.0815	12.70	.500
1.57	.062	9.86	.388
1.40	.055	9.80	.386
1.00	.039	7.34	.289
0.76	.030	6.86	.270
0.25	.010	6.10	.240
0.13	.005	5.99	.236
0.08	.003	5.33	.210
0.05	.002	5.08	.200
0.00381	0.000150	4.14	.163
0.00127	0.000050	3.86	.152
0.00076	0.000030	3.68	.145
MM	IN	MM	IN
CONVERSION TABLE			

BRASS	8	NYLON, UL94V-0	WHITE	1-770968-1
BRASS	7	NYLON, UL94V-0	WHITE	1-770968-0
BRASS	6	NYLON, UL94V-0	WHITE	770968-2
BRASS	5	NYLON, UL94V-0	WHITE	770968-1
MATERIAL	FINISH	MATERIAL	COLOR	PART NO.
PIN		HOUSING		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. CARPENTER
24JUL03

CHK
C. JONES
24JUL03

APVD
C. JONES
24JUL03

TE Connectivity

DIMENSIONS:
mm

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.13

4 PLC ± -

ANGLES ± -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

NAME

HEADER ASSEMBLY, RIGHT ANGLE, WITH SHORT PEG, 4 CIRCUIT, MINI UNIVERSAL MATE-N-LOK(TM)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

MATERIAL
SEE TABLE

FINISH
SEE TABLE

770968

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV H