



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
DY	-	C1		REVISED PER ECO-11-005139	19MAR11	RK HMR

- NOTE:
- 1 MATERIAL: THERMOPLASTIC, UL 94V-0
 - 2 POST CONTACT: COPPER ALLOY
 - 3 FINISH: BRIGHT TIN OVER NICKEL UNDERPLATE ALL OVER
 - 4 SEE FIGURE 1 FOR KINK 'FOOTPRINT'
 - 5 ⊕ KINK DIRECTION OPPOSITE FROM ●


BLACK	28.0	33.0	28.0±0.2	34.0	30.00	16P	3-1735446-6
	26.0	31.0	26.0±0.2	32.0	28.00	15P	3-1735446-5
	24.0	29.0	24.0±0.2	30.0	26.00	14P	3-1735446-4
	22.0	27.0	22.0±0.2	28.0	24.00	13P	3-1735446-3
	20.0	25.0	20.0±0.2	26.0	22.00	12P	3-1735446-2
	18.0	23.0	18.0±0.2	24.0	20.00	11P	3-1735446-1
	16.0	21.0	16.0±0.2	22.0	18.00	10P	3-1735446-0
	14.0	19.0	14.0±0.2	20.0	16.00	9P	2-1735446-9
	12.0	17.0	12.0±0.2	18.0	14.00	8P	2-1735446-8
	10.0	15.0	10.0±0.2	16.0	12.00	7P	2-1735446-7
	8.0	13.0	8.0±0.2	14.0	10.00	6P	2-1735446-6
	6.0	11.0	6.0±0.2	12.0	8.00	5P	2-1735446-5
	4.0	9.0	4.0±0.2	10.0	6.00	4P	2-1735446-4
	2.0	7.0	2.0 ^{+0.2} _{-0.08}	8.0	4.00	3P	2-1735446-3
NATURAL	28.0	33.0	28.0±0.2	34.0	30.00	16P	1-1735446-6
	26.0	31.0	26.0±0.2	32.0	28.00	15P	1-1735446-5
	24.0	29.0	24.0±0.2	30.0	26.00	14P	1-1735446-4
	22.0	27.0	22.0±0.2	28.0	24.00	13P	1-1735446-3
	20.0	25.0	20.0±0.2	26.0	22.00	12P	1-1735446-2
	18.0	23.0	18.0±0.2	24.0	20.00	11P	1-1735446-1
	16.0	21.0	16.0±0.2	22.0	18.00	10P	1-1735446-0
	14.0	19.0	14.0±0.2	20.0	16.00	9P	1735446-9
	12.0	17.0	12.0±0.2	18.0	14.00	8P	1735446-8
	10.0	15.0	10.0±0.2	16.0	12.00	7P	1735446-7
	8.0	13.0	8.0±0.2	14.0	10.00	6P	1735446-6
	6.0	11.0	6.0±0.2	12.0	8.00	5P	1735446-5
	4.0	9.0	4.0±0.2	10.0	6.00	4P	1735446-4
	2.0	7.0	2.0 ^{+0.2} _{-0.08}	8.0	4.00	3P	1735446-3
COLOUR	E	D	C	B	A	POS	PART NUMBER





SECTION X - X



SECTION Y - Y



TE LOGO



KINKING FORMING 3PLC

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC ±	
		1 PLC ±	
		2 PLC ±	
		3 PLC ±	
		4 PLC ±	
		ANGLES ±	
MATERIAL		FINISH	
1 2		3	

DWN	WYLEE	14 NOV 2006
CHK	KT GOH	11 APR 2007
APVD	SF LEONG	1 JUN 2007
PRODUCT SPEC		
108-51087		
APPLICATION SPEC		
-		
WEIGHT		
-		
CUSTOMER DRAWING		

TE Connectivity		
NAME		
2.0mm PITCH HPI POST HEADER WITH LOCK, VERTICAL		
SIZE	CAGE CODE	DRAWING NO
A3	00779	C-1735446
SCALE		SHEET
5:1		1 OF 2
REV		C1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

©

COPYRIGHT

BY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR


DESCRIPTION

DATE


DWN

APVD

SEE SHEET 1




POSITION 1




8.20±0.3

7~16P


 $\varnothing 0.80^{+0.1}_{-0}$
TYP


RECOMMENDED PCB LAYOUT

 (NON ACCUMULATIVE TOLERANCE)
 (PCB THK = 1.0~1.6mm)


4.00±0.3

4~6P




2.00±0.3

3P

FIG.1

5

3P	●	⊕	●													
4P	●	○	⊕	●												
5P	●	○	⊕	○	●											
6P	●	○	○	⊕	○	●										
7P	○	●	○	⊕	○	●	○									
8P	○	●	○	○	⊕	○	●	○								
9P	○	●	○	○	⊕	○	○	●	○							
10P	○	●	○	○	○	⊕	○	○	●	○						
11P	○	●	○	○	○	⊕	○	○	○	●	○					
12P	○	●	○	○	○	○	⊕	○	○	○	●	○				
13P	○	●	○	○	○	○	⊕	○	○	○	○	●	○			
14P	○	●	○	○	○	○	⊕	○	○	○	○	○	●	○		
15P	○	●	○	○	○	○	○	⊕	○	○	○	○	○	●	○	
16P	○	●	○	○	○	○	○	○	⊕	○	○	○	○	○	●	○
POS	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16

		DWN WYLEE 14 NOV 2006		 TE Connectivity		
		CHK KT GOH 11 APR 2007				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 2.0mm PITCH HPI POST HEADER WITH LOCK, VERTICAL		
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ± ANGLES ±				
MATERIAL SEE SHEET 1		FINISH SEE SHEET 1		PRODUCT SPEC 108-51087		SIZE A3
				APPLICATION SPEC -		
				WEIGHT -		CAGE CODE 00779
				CUSTOMER DRAWING		
				DRAWING NO C-1735446		SCALE 5:1
				SHEET 2 OF 2		REV C1