SPEC

Spec No.	TQ3C-8EAF0-E1YAK04-00				
Date	March 18, 2015				

TYPE: TCG066AALPAANN-GN00

< 6.6 inch transmissive color TFT with LED >

CONTENTS

- 1. Application
- 2. Construction and outline
- 3. Mechanical specifications
- 4. Absolute maximum ratings
- 5. Electrical characteristics
- 6. Optical characteristics
- 7. Interface signals
- 8. Input timing characteristics
- 9. Backlight characteristics
- 10. Lot number identification
- 11. Warranty
- 12. Precautions for use
- 13. Reliability test data
- 14. Outline drawing



KYOCERA DISPLAY CORPORATION

This specification is subject to change without notice. Consult Kyocera before ordering.

Original	Designed by: Engineering dept.			Confirmed by: QA dept.	
Issue Date	Prepared	Checked	Approved	Checked	Approved
March 18, 2015	M. Koyama	Y. Yamazaki	W. Yano	O. Sato	1-Hamars



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	-

Warning

- 1. This Kyocera LCD module has been specifically designed for use only in electronic devices and industrial machines in the area of audio control, office automation, industrial control, home appliances, etc. The module should not be used in applications where the highest level of safety and reliability are required and module failure or malfunction of such module results in physical harm or loss of life, as well as enormous damage or loss. Such fields of applications include, without limitation, medical, aerospace, communications infrastructure, atomic energy control. Kyocera expressly disclaims any and all liability resulting in any way to the use of the module in such applications.
- 2. Customer agrees to indemnify, defend and hold Kyocera harmless from and against any and all actions, claims, damages, liabilities, awards, costs, and expenses, including legal expenses, resulting from or arising out of Customer's use, or sale for use, or Kyocera modules in applications.

Caution

1. Kyocera shall have the right, which Customer hereby acknowledges, to immediately scrap or destroy tooling for Kyocera modules for which no Purchase Orders have been received from the Customer in a two-year period.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	-

Revision record

Date Designed by : 1 Prepared				Confirmed by	: QA dept.		
		Prepa	ıred	Checked	Approved	Checked	Approved
Dor- Nt.	D-4-	D			Danasiasi		
Rev.No.	Date	Page			Descripti	ons	



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	1

1. Application

This document defines the specification of TCG066AALPAANN-GN00. (RoHS Compliant)

2. Construction and outline

LCD : Transmissive color dot matrix type TFT

Backlight system : LED

Polarizer : Glare treatment

Additional circuit : Timing controller, Power supply (3.3V input)

(without constant current circuit for LED Backlight)

3. Mechanical specifications

Item	Specification	Unit
Outline dimensions 1)	27.75(W)×196.9(H)×6.3(D)	mm
Active area	18.906(W)×164.4(H) (16.55cm/6.52 inch(Diagonal))	mm
Dot format	92×(R,G,B)(W)×800(H)	dot
Dot pitch	0.0685(W)×0.2055(H)	mm
Base color 2)	Normally White	-
Mass	TBD	g

1) Projection not included. Please refer to outline for details.

Portrait mode

2) Due to the characteristics of the LCD material, the color varies with environmental temperature.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	2

4. Absolute maximum ratings

4-1. Electrical absolute maximum ratings

Item		Symbol	Min.	Max.	Unit
Supply voltage for logic		$V_{ m DD}$	(-0.3)	(4.0)	V
Input signal voltage	1)	$V_{\rm IN}$	(-0.3)	(V _{DD} +0.5)	V
LED forward current	2) 3)	IF	-	100	mA

- 1) Input signal : CK, R0 \sim R5, G0 \sim G5, B0 \sim B5, ENAB
- 2) For each "AN-CA"
- 3) Do not apply reversed voltage.

4-2. Environmental absolute maximum ratings

Item		Symbol	Min.	Max.	Unit
Operating temperature	1)	T_{OP}	-20	70	°C
Storage temperature	2)	T_{STO}	-30	80	$^{\circ}\mathrm{C}$
Operating humidity	3)	H_{OP}	10	4)	%RH
Storage humidity	3)	Hsto	10	4)	%RH
Vibration		-	5)	5)	-
Shock		-	6)	6)	-

- 1) Operating temperature means a temperature which operation shall be guaranteed. Since display performance is evaluated at 25°C, another temperature range should be confirmed.
- 2) Temp. = -30°C < 48h, Temp. = 80°C < 168hStore LCD at normal temperature/humidity. Keep them free from vibration and shock. An LCD that is kept at a low or a high temperature for a long time can be defective due to other conditions, even if the low or high temperature satisfies the standard. (Please refer to "Precautions for Use" for details.)
- 3) Non-condensing
- 4) Temp. \leq 40°C, 85%RH Max.

Temp. > 40°C, Absolute humidity shall be less than 85%RH at 40°C.

5)

Frequency	10∼55 Hz	Acceleration value
Vibration width	0.15mm	$(0.3\sim 9 \text{ m/s}^2)$
Interval	10-55-10	Hz 1 minutes

2 hours in each direction X, Y, Z (6 hours total) EIAJ ED-2531

6) Acceleration: 490 m/s², Pulse width: 11 ms

3 times in each direction: $\pm X$, $\pm Y$, $\pm Z$

EIAJ ED-2531



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	3

5. Electrical characteristics

 $\overline{\text{Temp.}} = -20 \sim 70^{\circ}\text{C}$

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Supply voltage 1)	$V_{ m DD}$	-	(3.0)	(3.3)	(3.6)	V
Current consumption	I_{DD}	2)	-	75	100	mA
Permissive input ripple voltage	V_{RP}	-	-	-	(-100)	mVp-p
I	V_{IL}	"Low" level	(0)	-	(0.8)	V
Input signal voltage 3)	V _{IH}	"High" level	(2.0)	-	(V _{DD})	V

1) V_{DD}-turn-on conditions

TBD

2) Display pattern:

 $V_{DD} = 3.3V$, Temp. = 25°C

1 2 3 · · · · · · · · · · · · · · · · · 800(dot)

TBD

3) Input signal : CK, R0 \sim R5, G0 \sim G5, B0 \sim B5, ENAB



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	4

6. Optical characteristics


Measuring spot = ϕ 6.0mm, Temp. = 25°C

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	
D .:	Rise	$ au_{ m r}$	$\theta = \phi = 0^{\circ}$	-	8	-	ms	
Response time	Down	τd	$\theta = \phi = 0^{\circ}$	-	22	-	ms	
T7: 1		θ upper		-	80	-	1	
Viewing angle View direction	range	θ LOWER	CD > 10	-	60	-	deg.	
: 6 o'cloc		φ left	CR≧10	-	80	-	1	
(Gray III	(Gray inversion)			-	80	-	deg.	
Contrast ratio		CR	$\theta = \phi = 0^{\circ}$	400	800	-	-	
Brightness		L	IF=60mA/Line	(280)	(400)	-	cd/m²	
	D. J	X	0 / 00	0.590	0.640	0.690		
	Red	у	$\theta = \phi = 0$ °	0.275	0.325	0.375		
	G	X	$\theta = \phi = 0^{\circ}$	0.260	0.310	0.360		
Chromaticity	Green	у	$\theta - \phi = 0$	0.575	0.625	0.675	_	
coordinates	Λ		$\theta = \phi = 0^{\circ}$	0.100	0.150	0.200	-	
	Blue	у	$\theta - \phi = 0$	0.000	0.050	0.100		
	Wilsian	X	0 - 4 -00	0.255	0.305	0.355		
	White	у	$\theta = \phi = 0^{\circ}$		0.335	0.385		

6-1. Definition of contrast ratio

 $CR(Contrast ratio) = \frac{Brightness with all pixels "White"}{Brightness with all pixels "Black"}$


6-2. Definition of response time





Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	5

6-3. Definition of viewing angle



6-4. Brightness measuring points

- 1) Rating is defined as the white brightness at center of display screen.
- 2) 5 minutes after LED is turned on. (Ambient Temp.= 25° C)



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	6

7. Interface signals

No.	Symbol	Description	I/O	Note
1	CK	Clock signal for sampling each data signal	I	
2	GND	GND	-	
3	GND	GND	-	
4	ENAB	Signal to settle the horizontal display position (positive)	I	
5	GND	GND	-	
6	GND	GND	-	
7	R0	RED data signal(LSB)	I	
8	R1	RED data signal	Ι	
9	R2	RED data signal	I	
10	R3	RED data signal	I	
11	R4	RED data signal	I	
12	R5	RED data signal(MSB)	I	
13	GND	GND	-	
14	GND	GND	-	
15	G0	GREEN data signal(LSB)	I	
16	G1	GREEN data signal	I	
17	G2	GREEN data signal	I	
18	G3	GREEN data signal	I	
19	G4	GREEN data signal	I	
20	G5	GREEN data signal(MSB)	I	
21	GND	GND	-	
22	GND	GND	-	
23	В0	BLUE data signal(LSB)	I	
24	B1	BLUE data signal	I	
25	B2	BLUE data signal	I	
26	В3	BLUE data signal	I	
27	B4	BLUE data signal	I	
28	B5	BLUE data signal(MSB)	I	
29	GND	GND	-	
30	GND	GND	-	
31	VDD	3.3V power supply	I	
32	VDD	3.3V power supply	I	
33	VDD	3.3V power supply	I	
34	VDD	3.3V power supply	I	
35	GND	GND	-	
36	GND	GND	-	
37	AN1	Anode1	I	
38	AN2	Anode2	I	
39	CA1	Cathode1	I	
40	CA1	Cathode2	I	

LCD module connector

: 53748-0408 (MOLEX)



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	7

8. Input timing characteristics

8-1. Timing characteristics


	Item	Symbol	Min.	Тур.	Max.	Unit	Note
	Frequency	Fck	(-)	(13.1)	(-)	MHz	
Clock	Period	Тс	(-)	(76.5)	(-)	ns	
	Duty	Tch	(40)	(50)	(60)	ns	
Data (Po. Pr. Co. Cr.	Set up time	Tds	(5)	-	-	ns	
(R0~R5, G0~G5, B0~B5)	Hold time	Tdh	(10)	-	-	ns	
	Set up time	Tes	(5)	-	-	ns	
	Hold time	Teh	(10)	-	-	ns	
	D : 1	Th	(224)	(264)	(304)	Тс	
Enable	Period		(17)	(20)	-	μs	
Enable	Horizontal display period	Thd		92		Тс	
	Period	m	(810)	(825)	(850)	Th	
	renod	Tv	(15.4)	16.7	(18.2)	ms	
	Vertical display period	Tvd		800		Th	
Refresh rate		fv	(55)	60	(65)	Hz	

- 1) In case of lower frequency, the deterioration of the display quality, flicker etc., may occur.
- 2) If CK is fixed to "H" or "L" level for certain period while ENAB is supplied, the panel may be damaged.
- 3) When dimming LED by PWM, please adjust LCD operating signal timing and LED driving frequency, to optimize the display quality. There is a possibility that flicker is observed by the interference of LCD operating signal timing and LED driving condition (especially driving frequency), even if the condition satisfies above timing specification.
- 4) Do not make Tv and Th fluctuate.
- 5) CK count of each Horizontal Scanning Time should be always the same. Vertical invalid data period should be "n" X "Horizontal Scanning Time". (n: integer) Frame period should be always the same.




Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	8

8-2. Input timing characteristics



8-3. Input Data Signals and Display position on the screen





Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	9

9. Backlight characteristics

Temp. = $-20 \sim 70$ °C

Item		Symbol	Min.	Тур.	Max.	Unit	Note
Forward current	1)	IF	-	(60)	-	mA	Ta=-20~70°C
			-	(6.5)	(7.2)	V	IF=60mA, Ta=-20°C
Forward voltage	1)	VF	-	(6.2)	(6.8)	V	IF=60mA, Ta=25℃
			-	(6.0)	(6.6)	V	IF=60mA, Ta=70℃
Operating life time	2), 3)	Т	-	(70,000)	-	h	IF=60mA, Ta=25℃

- 1) For each "AN-CA"
- 2) When brightness decrease 50% of minimum brightness.

 The average life of a LED will decrease when the LCD is operating at higher temperatures.
- 3) Life time is estimated data.(Condition : IF=60mA, Ta=25 $^{\circ}$ C in chamber).
- 4) An input current below 15mA may reduce the brightness uniformity of the LED backlight. This is because the amount of light from each LED chip is different. Therefore, please evaluate carefully before finalizing the input current.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	10

10. Lot number identification

The lot number shall be indicated on the back of the backlight case of each LCD.

No1. - No5. above indicate

- 1. Year code
- 2. Month code
- 3. Date
- 4. Version Number
- 5. Country of origin (Japan or China)

Code 5 6 7 8 9 0	Year	2015	2016	2017	2018	2019	2020
	Code	5	6	7	8	9	0

Month	Jan.	Feb.	Mar.	Apr.	May	Jun.
Code	1	2	3	4	5	6

Month	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Code	7	8	9	X	Y	Z

11. Warranty

11-1. Incoming inspection

Please inspect the LCD within one month after your receipt.

11-2. Production warranty

Kyocera warrants its LCD's for a period of 12 months from the ship date. Kyocera shall, by mutual agreement, replace or re-work defective LCD's that are shown to be Kyocera's responsibility.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	11

12. Precautions for use

12-1. Installation of the LCD

- 1) A transparent protection plate shall be added to protect the LCD and its polarizer
- 2) The LCD shall be installed so that there is no pressure on the LSI chips.
- 3) The LCD shall be installed flat, without twisting or bending.
- 4) Please design the housing window so that its edges are between the active area and the effective area of the LCD screen.
- 5) A transparent protection sheet is attached to the polarizer. Please remove the protection film slowly before use, paying attention to static electricity.

12-2. Static electricity

- 1) Since CMOS ICs are mounted directly onto the LCD glass, protection from static electricity is required.
- 2) Workers should use body grounding. Operator should wear ground straps.

12-3. LCD operation

1) The LCD shall be operated within the limits specified. Operation at values outside of these limits may shorten life, and/or harm display images.

12-4. Storage

- 1) The LCD shall be stored within the temperature and humidity limits specified.

 Store in a dark area, and protect the LCD from direct sunlight or fluorescent light.
- 2) Always store the LCD so that it is free from external pressure onto it.

12-5. Usage

- 1) <u>DO NOT</u> store in a high humidity environment for extended periods. Polarizer degradation bubbles, and/or peeling off of the polarizer may result.
- 2) The front polarizer is easily scratched or damaged. Prevent touching it with any hard material, and from being pushed or rubbed.
- 3) The LCD screen may be cleaned by wiping the screen surface with a soft cloth or cotton pad using a little Ethanol.
- 4) Water may cause damage or discoloration of the polarizer. Clean condensation or moisture from any source immediately.
- 5) Always keep the LCD free from condensation during testing. Condensation may permanently spot or stain the polarizer.
- 6) Do not disassemble LCD because it will result in damage.
- 7) This Kyocera LCD has been specifically designed for use in general electronic devices, but not for use in a special environment such as usage in an active gas. Hence, when the LCD is supposed to be used in a special environment, evaluate the LCD thoroughly beforehand and do not expose the LCD to chemicals such as an active gas.
- 8) Please do not use solid-base image pattern for long hours because a temporary afterimage may appear. We recommend using screen saver etc. in cases where a solid-base image pattern must be used.
- 9) Liquid crystal may leak when the LCD is broken. Be careful not to let the fluid go into your eyes and mouth. In the case the fluid touches your body; rinse it off right away with water and soap.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAK04-00	TCG066AALPAANN-GN00	12


13. Reliability test data

Test item	Test condition	Test time	Jud	gement
High temp. atmosphere	80°C	240h	Display function Display quality Current consumption	: No defect : No defect : No defect
Low temp. atmosphere	-30°C	240h	Display function Display quality Current consumption	: No defect : No defect : No defect
High temp. humidity atmosphere	40°C 90% RH	240h	Display function Display quality Current consumption	: No defect : No defect : No defect
Temp. cycle	-30°C 0.5h R.T. 0.5h 80°C 0.5h	10cycles	Display function Display quality Current consumption	: No defect: No defect: No defect
High temp. operation	70°C	500h	Display function Display quality Current consumption	: No defect : No defect : No defect

- 1) Each test item uses a test LCD only once. The tested LCD is not used in any other tests.
- 2) The LCD is tested in circumstances in which there is no condensation.
- 3) The reliability test is not an out-going inspection.
- 4) The result of the reliability test is for your reference purpose only.

 The reliability test is conducted only to examine the LCD's capability.





Spec No.	TQ3C-8EAF0-E2YAK04-00
Date	March 18, 2015

KYOCERA INSPECTION STANDARD

TYPE: TCG066AALPAANN-GN00

KYOCERA DISPLAY CORPORATION

Original	Designed by:	Engineering de	ept.	Confirmed by	: QA dept.
Issue Date	Prepared	Checked	Approved	Checked	Approved
March 18, 2015	M. Koyama	Y. Yomazaki	W. Yano	O. Soto	I. Hamas



ı	Spec No.	Part No.	Page
	TQ3C-8EAF0-E2YAK04-00	TCG066AALPAANN-GN00	-

Revision record

	Data			Engineering dept.		Confirmed by : QA dept.	
	Date	Prepa		Checked	Approved	Checked	Approved
Rev.No.	Date	Page			Descripti	ons	



Spec No.	Part No.	Page
TQ3C-8EAF0-E2YAK04-00	TCG066AALPAANN-GN00	1

Visuals specification

1) Note

		. 1	Note		
General	reviewe 2. This ins	d by Kyocera, and an addi- spection standard about th	t defined within this inspection standard shall be tional standard shall be determined by mutual consent. e image quality shall be applied to any defect within the of the applicable to outside of the area.		
		ion conditions			
	Lumina		: 500 Lux min.		
		ion distance	300 mm.		
	Temper		: 25 ± 5°C		
	Direction		: Directly above		
Definition of inspection	Dot defect	Bright dot defect	The dot is constantly "on" when power applied to the LCD, even when all "Black" data sent to the screen.		
item			Inspection tool: 5% Transparency neutral density filter.		
			Count dot: If the dot is visible through the filter. Don't count dot: If the dot is not visible through the filter. RGBRGBRGB There is an electrode in the middle of the dot and one dot is shown in the left drawing. RGBRGBRGB Add drawing>		
		Black dot defect	The dot is constantly "off" when power applied to the		
			LCD, even when all "White" data sent to the screen.		
			Similar size compared to bright dot.		
		White dot	Pixel works electrically, however, circular/foreign		
		(Circular/foreign	particle makes dot appear to be "on" even when all		
		particle)	"Black" data is sent to the screen.		
		Adjacent dot	Adjacent dot defect is defined as two or more bright dot defects or black dot defects.		
			RGBRGBRGB RGBRGB dot defect		
	External	Bubble, Scratch,	Visible operating (all pixels "Black" or "White") and non		
	inspection	Foreign particle (Polarizer, Cell, Backlight)	operating.		
		Appearance inspection	Does not satisfy the value at the spec.		
	Others	CFL wires	Damaged to the CFL wires, connector, pin, functional failure or appearance failure.		
	Definition	Definition of cir	Definition of circle size Definition of linear size		
	of size	d = (a + b)	D)/2		



Spec No.	Part No.	Page
TQ3C-8EAF0-E2YAK04-00	TCG066AALPAANN-GN00	2

2) Standard

2) Standa	ru							
Classification Inspection item		Judgement standard						
Defect	Dot	Bright dot defect		Acceptable number : 4				
(in LCD	defect			Bright dot spacing : 5 mm or more			or more	
glass)		Black dot	defect	Acceptable number : 5				
				Black dot spacing : 5 mm or more				
	2 dot join Brig		Bright dot	Assistable and a second				
			defect	Acceptable number		: 2		
			Black dot defect	Acceptable number		: 3		
			dots join	Acceptable number : 0				
			lefects	Acceptable number : 5 Max				
Others		White dot, Dark dot						
				Size (mm)		Acceptable number		
				d ≤ 0.2		(Neglected)		
				0.2 < d ≦	≦ 0.4		5	
				0.4 < d ≦	0.5		3	
				0.5 < d			0	
External	inspection	Polarizer (Scratch)					
(Defect or	•		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	Width (mm)	Length (mm)	Acceptable number	
Polarizer or				$W \leq 0.1 \qquad -$		(Neglected)		
between Polarizer					L ≦	≦ 5.0	(Neglected)	
and LCD glass)				$0.1 < W \le 0.3$	5.0 < L		0	
and ECD glass)				0.3 < W	_		0	
		Polarizer (Bubble)					
				Size (mm)		Acceptable number		
				$d \leq 0.2$		(Neglected)		
				$0.2 < d \le 0.3$		5		
				$0.3 < d \le 0.5$		3		
				0.5 < d			0	
		Foreign pa	rticle					
		(Circular shape)		Size (mm)		Acceptable number		
				d ≦ 0.2		(Neglected)		
				$0.2 < d \le 0.4$		5		
				$0.4 < d \le 0.5$		3		
				$0.5 < ext{ d}$		0		
		Foreign pa	rticle					
		(Linear shape)		Width (mm)	Length	(mm)	Acceptable number	
		Scratch		$W \leq 0.03$		(111111/	(Neglected)	
		Derawii		0.00	L ≦ 2.0		(Neglected)	
				$0.03 < W \le 0.1$			3	
					4.0 < L		0	
				0.1 < W	_		(According to	
		i .						

