

# BC847/BC547 series

45 V, 100 mA NPN general-purpose transistors

Rev. 07 — 10 December 2008

Product data sheet

## 1. Product profile

### 1.1 General description

NPN general-purpose transistors in small plastic packages.

Table 1. Product overview

| Type number <sup>[1]</sup> | Package |        |          | PNP complement        |
|----------------------------|---------|--------|----------|-----------------------|
|                            | NXP     | JEITA  | JEDEC    |                       |
| BC847                      | SOT23   | -      | TO-236AB | BC857                 |
| BC847A                     |         |        |          | BC857A                |
| BC847B                     |         |        |          | BC857B                |
| BC847B/DG                  |         |        |          | -                     |
| BC847C                     |         |        |          | BC857C                |
| BC847W                     | SOT323  | SC-70  | -        | BC857W                |
| BC847AW                    |         |        |          | BC857AW               |
| BC847BW                    |         |        |          | BC857BW               |
| BC847BW/DG                 |         |        |          | -                     |
| BC847CW                    |         |        |          | BC857CW               |
| BC847T                     | SOT416  | SC-75  | -        | BC857T                |
| BC847AT                    |         |        |          | BC857AT               |
| BC847AT/DG                 |         |        |          | -                     |
| BC847BT                    |         |        |          | BC857BT               |
| BC847CT                    |         |        |          | BC857CT               |
| BC847AM                    | SOT883  | SC-101 | -        | BC857AM               |
| BC847BM                    |         |        |          | BC857BM               |
| BC847CM                    |         |        |          | BC857CM               |
| BC547 <sup>[2]</sup>       | SOT54   | SC-43A | TO-92    | BC557 <sup>[2]</sup>  |
| BC547B <sup>[2]</sup>      |         |        |          | BC557B <sup>[2]</sup> |
| BC547C <sup>[2]</sup>      |         |        |          | BC557C <sup>[2]</sup> |

[1] /DG: halogen-free

[2] Also available in SOT54A and SOT54 variant packages (see [Section 2](#)).

1.2 Features

- Low current
- Low voltage
- Three different gain selections

1.3 Applications

- General-purpose switching and amplification

1.4 Quick reference data

Table 2. Quick reference data

| Symbol    | Parameter                 | Conditions                               | Min | Typ | Max | Unit |
|-----------|---------------------------|------------------------------------------|-----|-----|-----|------|
| $V_{CEO}$ | collector-emitter voltage | open base                                | -   | -   | 45  | V    |
| $I_C$     | collector current         |                                          | -   | -   | 100 | mA   |
| $h_{FE}$  | DC current gain           | $V_{CE} = 5\text{ V}; I_C = 2\text{ mA}$ | 110 | -   | 800 |      |
|           | $h_{FE}$ group A          |                                          | 110 | 180 | 220 |      |
|           | $h_{FE}$ group B          |                                          | 200 | 290 | 450 |      |
|           | $h_{FE}$ group C          |                                          | 420 | 520 | 800 |      |

2. Pinning information

Table 3. Pinning











| Pin                          | Description | Simplified outline                                                                    | Graphic symbol                                                                        |
|------------------------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <b>SOT23, SOT323, SOT416</b> |             |                                                                                       |                                                                                       |
| 1                            | base        |  |  |
| 2                            | emitter     |                                                                                       |                                                                                       |
| 3                            | collector   |                                                                                       |                                                                                       |
|                              |             | 006aaa144                                                                             | sym021                                                                                |
| <b>SOT883</b>                |             |                                                                                       |                                                                                       |
| 1                            | base        |  |  |
| 2                            | emitter     |                                                                                       |                                                                                       |
| 3                            | collector   |                                                                                       |                                                                                       |
|                              |             | Transparent top view                                                                  | sym021                                                                                |

Table 3. Pinning ...continued

| Pin           | Description | Simplified outline                                                                   | Graphic symbol                                                                       |
|---------------|-------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
| SOT54         |             |                                                                                      |                                                                                      |
| 1             | emitter     |   |   |
| 2             | base        |                                                                                      |                                                                                      |
| 3             | collector   |                                                                                      |                                                                                      |
| SOT54A        |             |                                                                                      |                                                                                      |
| 1             | emitter     |   |   |
| 2             | base        |                                                                                      |                                                                                      |
| 3             | collector   |                                                                                      |                                                                                      |
| SOT54 variant |             |                                                                                      |                                                                                      |
| 1             | emitter     |  |  |
| 2             | base        |                                                                                      |                                                                                      |
| 3             | collector   |                                                                                      |                                                                                      |

3. Ordering information

Table 4. Ordering information

| Type number <sup>[1]</sup> | Package |                                          |         |
|----------------------------|---------|------------------------------------------|---------|
|                            | Name    | Description                              | Version |
| BC847                      | -       | plastic surface-mounted package; 3 leads | SOT23   |
| BC847A                     |         |                                          |         |
| BC847B                     |         |                                          |         |
| BC847B/DG                  |         |                                          |         |
| BC847C                     |         |                                          |         |
| BC847W                     | SC-70   | plastic surface-mounted package; 3 leads | SOT323  |
| BC847AW                    |         |                                          |         |
| BC847BW                    |         |                                          |         |
| BC847BW/DG                 |         |                                          |         |
| BC847CW                    |         |                                          |         |

Table 4. Ordering information ...continued

| Type number <sup>[1]</sup> | Package |                                                                               |         |
|----------------------------|---------|-------------------------------------------------------------------------------|---------|
|                            | Name    | Description                                                                   | Version |
| BC847T                     | SC-75   | plastic surface-mounted package; 3 leads                                      | SOT416  |
| BC847AT                    |         |                                                                               |         |
| BC847AT/DG                 |         |                                                                               |         |
| BC847BT                    |         |                                                                               |         |
| BC847CT                    |         |                                                                               |         |
| BC847AM                    | SC-101  | leadless ultra small plastic package; 3 solder lands; body 1.0 × 0.6 × 0.5 mm | SOT883  |
| BC847BM                    |         |                                                                               |         |
| BC847CM                    |         |                                                                               |         |
| BC547 <sup>[2]</sup>       | SC-43A  | plastic single-ended leaded (through hole) package; 3 leads                   | SOT54   |
| BC547B <sup>[2]</sup>      |         |                                                                               |         |
| BC547C <sup>[2]</sup>      |         |                                                                               |         |

[1] /DG: halogen-free

[2] Also available in SOT54 and SOT54 variant packages (see [Section 2](#) and [Section 9](#)).

## 4. Marking

Table 5. Marking codes

| Type number <sup>[1]</sup> | Marking code <sup>[2]</sup> | Type number <sup>[1]</sup> | Marking code <sup>[2]</sup> |
|----------------------------|-----------------------------|----------------------------|-----------------------------|
| BC847                      | 1H*                         | BC847AT                    | 1E                          |
| BC847A                     | 1E*                         | BC847AT/DG                 | B5                          |
| BC847B                     | 1F*                         | BC847BT                    | 1F                          |
| BC847B/DG                  | *BC                         | BC847CT                    | 1G                          |
| BC847C                     | 1G*                         | BC847AM                    | D4                          |
| BC847W                     | 1H*                         | BC847BM                    | D5                          |
| BC847AW                    | 1E*                         | BC847CM                    | D6                          |
| BC847BW                    | 1F*                         | BC547                      | C547                        |
| BC847BW/DG                 | G9*                         | BC547B                     | C547B                       |
| BC847CW                    | 1G*                         | BC547C                     | C547C                       |
| BC847T                     | 1N                          | -                          | -                           |

[1] /DG: halogen-free

[2] \* = -: made in Hong Kong  
 \* = p: made in Hong Kong  
 \* = t: made in Malaysia  
 \* = W: made in China

## 5. Limiting values

**Table 6. Limiting values**

*In accordance with the Absolute Maximum Rating System (IEC 60134).*

| Symbol    | Parameter                 | Conditions                       | Min      | Max  | Unit |
|-----------|---------------------------|----------------------------------|----------|------|------|
| $V_{CBO}$ | collector-base voltage    | open emitter                     | -        | 50   | V    |
| $V_{CEO}$ | collector-emitter voltage | open base                        | -        | 45   | V    |
| $V_{EBO}$ | emitter-base voltage      | open collector                   | -        | 6    | V    |
| $I_C$     | collector current         |                                  | -        | 100  | mA   |
| $I_{CM}$  | peak collector current    | single pulse;<br>$t_p \leq 1$ ms | -        | 200  | mA   |
| $I_{BM}$  | peak base current         | single pulse;<br>$t_p \leq 1$ ms | -        | 100  | mA   |
| $P_{tot}$ | total power dissipation   | $T_{amb} \leq 25$ °C             |          |      |      |
|           | SOT23                     |                                  | [1] -    | 250  | mW   |
|           | SOT323                    |                                  | [1] -    | 200  | mW   |
|           | SOT416                    |                                  | [1] -    | 150  | mW   |
|           | SOT883                    |                                  | [2][3] - | 250  | mW   |
|           | SOT54                     |                                  | [1] -    | 500  | mW   |
| $T_j$     | junction temperature      |                                  | -        | 150  | °C   |
| $T_{amb}$ | ambient temperature       |                                  | -65      | +150 | °C   |
| $T_{stg}$ | storage temperature       |                                  | -65      | +150 | °C   |

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

[2] Reflow soldering is the only recommended soldering method.

[3] Device mounted on an FR4 PCB with 60 µm copper strip line, standard footprint.

## 6. Thermal characteristics

**Table 7. Thermal characteristics**

| Symbol        | Parameter                                   | Conditions  | Min      | Typ | Max | Unit |
|---------------|---------------------------------------------|-------------|----------|-----|-----|------|
| $R_{th(j-a)}$ | thermal resistance from junction to ambient | in free air |          |     |     |      |
|               | SOT23                                       |             | [1] -    | -   | 500 | K/W  |
|               | SOT323                                      |             | [1] -    | -   | 625 | K/W  |
|               | SOT416                                      |             | [1] -    | -   | 833 | K/W  |
|               | SOT883                                      |             | [2][3] - | -   | 500 | K/W  |
|               | SOT54                                       |             | [1] -    | -   | 250 | K/W  |

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Reflow soldering is the only recommended soldering method.

[3] Device mounted on an FR4 PCB with 60 µm copper strip line, standard footprint.

## 7. Characteristics


**Table 8. Characteristics**

$T_{amb} = 25\text{ }^{\circ}\text{C}$  unless otherwise specified.

| Symbol      | Parameter                            | Conditions                                                                                                       | Min     | Typ | Max | Unit          |
|-------------|--------------------------------------|------------------------------------------------------------------------------------------------------------------|---------|-----|-----|---------------|
| $I_{CBO}$   | collector-base cut-off current       | $V_{CB} = 30\text{ V}; I_E = 0\text{ A}$                                                                         | -       | -   | 15  | nA            |
|             |                                      | $V_{CB} = 30\text{ V}; I_E = 0\text{ A}; T_j = 150\text{ }^{\circ}\text{C}$                                      | -       | -   | 5   | $\mu\text{A}$ |
| $I_{EBO}$   | emitter-base cut-off current         | $V_{EB} = 5\text{ V}; I_C = 0\text{ A}$                                                                          | -       | -   | 100 | nA            |
| $h_{FE}$    | DC current gain                      |                                                                                                                  |         |     |     |               |
|             | $h_{FE}$ group A                     | $V_{CE} = 5\text{ V}; I_C = 10\text{ }\mu\text{A}$                                                               | -       | 90  | -   |               |
|             | $h_{FE}$ group B                     | $V_{CE} = 5\text{ V}; I_C = 10\text{ }\mu\text{A}$                                                               | -       | 150 | -   |               |
|             | $h_{FE}$ group C                     | $V_{CE} = 5\text{ V}; I_C = 10\text{ }\mu\text{A}$                                                               | -       | 270 | -   |               |
|             | DC current gain                      | $V_{CE} = 5\text{ V}; I_C = 2\text{ mA}$                                                                         | 110     | -   | 800 |               |
|             | $h_{FE}$ group A                     | $V_{CE} = 5\text{ V}; I_C = 2\text{ mA}$                                                                         | 110     | 180 | 220 |               |
|             | $h_{FE}$ group B                     | $V_{CE} = 5\text{ V}; I_C = 2\text{ mA}$                                                                         | 200     | 290 | 450 |               |
|             | $h_{FE}$ group C                     | $V_{CE} = 5\text{ V}; I_C = 2\text{ mA}$                                                                         | 420     | 520 | 800 |               |
| $V_{CEsat}$ | collector-emitter saturation voltage | $I_C = 10\text{ mA}; I_B = 0.5\text{ mA}$                                                                        | -       | 90  | 200 | mV            |
|             |                                      | $I_C = 100\text{ mA}; I_B = 5\text{ mA}$                                                                         | [1] -   | 200 | 400 | mV            |
| $V_{BEsat}$ | base-emitter saturation voltage      | $I_C = 10\text{ mA}; I_B = 0.5\text{ mA}$                                                                        | [2] -   | 700 | -   | mV            |
|             |                                      | $I_C = 100\text{ mA}; I_B = 5\text{ mA}$                                                                         | [2] -   | 900 | -   | mV            |
| $V_{BE}$    | base-emitter voltage                 | $I_C = 2\text{ mA}; V_{CE} = 5\text{ V}$                                                                         | [2] 580 | 660 | 700 | mV            |
|             |                                      | $I_C = 10\text{ mA}; V_{CE} = 5\text{ V}$                                                                        | -       | -   | 770 | mV            |
| $C_C$       | collector capacitance                | $I_E = I_C = 0\text{ A}; V_{CB} = 10\text{ V}; f = 1\text{ MHz}$                                                 | -       | -   | 1.5 | pF            |
| $C_e$       | emitter capacitance                  | $I_C = I_E = 0\text{ A}; V_{EB} = 0.5\text{ V}; f = 1\text{ MHz}$                                                | -       | 11  | -   | pF            |
| $f_T$       | transition frequency                 | $I_C = 10\text{ mA}; V_{CE} = 5\text{ V}; f = 100\text{ MHz}$                                                    | 100     | -   | -   | MHz           |
| NF          | noise figure                         | $I_C = 200\text{ }\mu\text{A}; V_{CE} = 5\text{ V}; R_S = 2\text{ k}\Omega; f = 1\text{ kHz}; B = 200\text{ Hz}$ | -       | 2   | 10  | dB            |


[1] Pulse test:  $t_p \leq 300\text{ }\mu\text{s}$ ;  $\delta \leq 0.02$ .

[2]  $V_{BE}$  decreases by approximately 2 mV/K with increasing temperature.




$V_{CE} = 5\text{ V}$   
(1)  $T_{amb} = 150\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = -55\text{ }^{\circ}\text{C}$

Fig 1. Selection A: DC current gain as a function of collector current; typical values




$V_{CE} = 5\text{ V}$   
(1)  $T_{amb} = -55\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = 150\text{ }^{\circ}\text{C}$

Fig 2. Selection A: Base-emitter voltage as a function of collector current; typical values




$I_C/I_B = 20$   
(1)  $T_{amb} = 150\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = -55\text{ }^{\circ}\text{C}$

Fig 3. Selection A: Collector-emitter saturation voltage as a function of collector current; typical values




$I_C/I_B = 10$   
(1)  $T_{amb} = -55\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = 150\text{ }^{\circ}\text{C}$

Fig 4. Selection A: Base-emitter saturation voltage as a function of collector current; typical values




$V_{CE} = 5\text{ V}$   
(1)  $T_{amb} = 150\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = -55\text{ }^{\circ}\text{C}$

Fig 5. Selection B: DC current gain as a function of collector current; typical values




$V_{CE} = 5\text{ V}$   
(1)  $T_{amb} = -55\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = 150\text{ }^{\circ}\text{C}$

Fig 6. Selection B: Base-emitter voltage as a function of collector current; typical values



$I_C/I_B = 20$   
(1)  $T_{amb} = 150\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = -55\text{ }^{\circ}\text{C}$


Fig 7. Selection B: Collector-emitter saturation voltage as a function of collector current; typical values



$I_C/I_B = 10$   
(1)  $T_{amb} = -55\text{ }^{\circ}\text{C}$   
(2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
(3)  $T_{amb} = 150\text{ }^{\circ}\text{C}$


Fig 8. Selection B: Base-emitter saturation voltage as a function of collector current; typical values






- $V_{CE} = 5\text{ V}$
- (1)  $T_{amb} = 150\text{ }^{\circ}\text{C}$
  - (2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
  - (3)  $T_{amb} = -55\text{ }^{\circ}\text{C}$

Fig 9. Selection C: DC current gain as a function of collector current; typical values




- $V_{CE} = 5\text{ V}$
- (1)  $T_{amb} = -55\text{ }^{\circ}\text{C}$
  - (2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
  - (3)  $T_{amb} = 150\text{ }^{\circ}\text{C}$

Fig 10. Selection C: Base-emitter voltage as a function of collector current; typical values



- $I_C/I_B = 20$
- (1)  $T_{amb} = 150\text{ }^{\circ}\text{C}$
  - (2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
  - (3)  $T_{amb} = -55\text{ }^{\circ}\text{C}$


Fig 11. Selection C: Collector-emitter saturation voltage as a function of collector current; typical values




- $I_C/I_B = 10$
- (1)  $T_{amb} = -55\text{ }^{\circ}\text{C}$
  - (2)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
  - (3)  $T_{amb} = 150\text{ }^{\circ}\text{C}$

Fig 12. Selection C: Base-emitter saturation voltage as a function of collector current; typical values

8. Package outline



**Fig 19. Package outline SOT54 variant**

## 9. Packing information

**Table 9. Packing methods**

The indicated -xxx are the last three digits of the 12NC ordering code.[\[1\]](#)

| Type number <a href="#">[2]</a> | Package | Description                    | Packing quantity |      |       |
|---------------------------------|---------|--------------------------------|------------------|------|-------|
|                                 |         |                                | 3000             | 5000 | 10000 |
| BC847                           | SOT23   | 4 mm pitch, 8 mm tape and reel | -215             | -    | -235  |
| BC847A                          |         |                                |                  |      |       |
| BC847B                          |         |                                |                  |      |       |
| BC847B/DG                       |         |                                |                  |      |       |
| BC847C                          |         |                                |                  |      |       |
| BC847W                          | SOT323  | 4 mm pitch, 8 mm tape and reel | -115             | -    | -135  |
| BC847AW                         |         |                                |                  |      |       |
| BC847BW                         |         |                                |                  |      |       |
| BC847BW/DG                      |         |                                |                  |      |       |
| BC847CW                         |         |                                |                  |      |       |
| BC847T                          | SOT416  | 4 mm pitch, 8 mm tape and reel | -115             | -    | -135  |
| BC847AT                         |         |                                |                  |      |       |
| BC847AT/DG                      |         |                                |                  |      |       |
| BC847BT                         |         |                                |                  |      |       |
| BC847CT                         |         |                                |                  |      |       |
| BC847AM                         | SOT883  | 2 mm pitch, 8 mm tape and reel | -                | -    | -315  |
| BC847BM                         |         |                                |                  |      |       |
| BC847CM                         |         |                                |                  |      |       |
| BC547                           | SOT54   | bulk, straight leads           | -                | -412 | -     |
| BC547B                          |         |                                |                  |      |       |
| BC547C                          |         |                                |                  |      |       |

**Table 9. Packing methods ...continued**

The indicated -xxx are the last three digits of the 12NC ordering code.<sup>[1]</sup>

| Type number <sup>[2]</sup> | Package       | Description               | Packing quantity |      |       |
|----------------------------|---------------|---------------------------|------------------|------|-------|
|                            |               |                           | 3000             | 5000 | 10000 |
| BC547<br>BC547B<br>BC547C  | SOT54A        | tape and reel, wide pitch | -                | -    | -116  |
| BC547<br>BC547B<br>BC547C  | SOT54A        | tape ammopack, wide pitch | -                | -    | -126  |
| BC547<br>BC547B<br>BC547C  | SOT54 variant | bulk, delta pinning       | -                | -112 | -     |

[1] For further information and the availability of packing methods, see [Section 12](#).

[2] /DG: halogen-free

## 10. Revision history

**Table 10. Revision history**

| Document ID                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | Release date | Data sheet status     | Change notice | Supersedes                                                                                                  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|-----------------------|---------------|-------------------------------------------------------------------------------------------------------------|
| BC847_BC547_SER_7                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 20081210     | Product data sheet    | -             | BC847_BC547_SER_6                                                                                           |
| Modifications: <ul style="list-style-type: none"> <li>The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li><a href="#">Table 1 "Product overview"</a>: enhanced</li> <li><a href="#">Table 4 "Ordering information"</a>: enhanced</li> <li><a href="#">Table 5 "Marking codes"</a>: enhanced</li> <li><a href="#">Table 6 "Limiting values"</a>: I<sub>EBO</sub> conditions amended</li> <li><a href="#">Table 8 "Characteristics"</a>: symbol N for parameter noise figure redefined to NF</li> <li><a href="#">Table 9 "Packing methods"</a>: enhanced</li> <li><a href="#">Section 11 "Legal information"</a>: updated</li> </ul> |              |                       |               |                                                                                                             |
| BC847_BC547_SER_6                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 20050519     | Product data sheet    | -             | BC846_BC847_BC848_5,<br>BC847M_SERIES_2,<br>BC846T_847T_SERIES_3,<br>BC846W_BC847W_BC848W_4,<br>BC546_547_4 |
| BC846_BC847_BC848_5                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | 20040206     | Product specification | -             | BC846_BC847_BC848_4                                                                                         |
| BC847M_SERIES_2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 20040310     | Product specification | -             | BC847M_SERIES_1                                                                                             |
| BC846T_847T_SERIES_3                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 20001115     | Product specification | -             | BC846T_847T_2                                                                                               |
| BC846W_BC847W_<br>BC848W_4                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | 20020204     | Product specification | -             | BC846W_847W_3                                                                                               |
| BC546_547_4                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | 20041125     | Product specification | -             | BC546_547_3                                                                                                 |

## 11. Legal information

### 11.1 Data sheet status

| Document status <sup>[1][2]</sup> | Product status <sup>[3]</sup> | Definition                                                                            |
|-----------------------------------|-------------------------------|---------------------------------------------------------------------------------------|
| Objective [short] data sheet      | Development                   | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet    | Qualification                 | This document contains data from the preliminary specification.                       |
| Product [short] data sheet        | Production                    | This document contains the product specification.                                     |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

### 11.2 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

### 11.3 Disclaimers

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental

damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Terms and conditions of sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

### 11.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## 12. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

13. Contents

1 Product profile ..... 1

1.1 General description..... 1

1.2 Features ..... 2

1.3 Applications ..... 2

1.4 Quick reference data..... 2

2 Pinning information..... 2

3 Ordering information..... 3

4 Marking..... 4

5 Limiting values..... 5

6 Thermal characteristics..... 5

7 Characteristics..... 6

8 Package outline ..... 10

9 Packing information..... 11

10 Revision history..... 13

11 Legal information..... 14

11.1 Data sheet status ..... 14

11.2 Definitions..... 14

11.3 Disclaimers..... 14

11.4 Trademarks..... 14

12 Contact information..... 14

13 Contents ..... 15



Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.