



A = 2.54 * No. of Spaces
B = A + 10.16
C = A + 7.86

△ * Available circuits: 6,8,10,14,16,20,24,26,30, 34,40,44,50,60 and 64


Material:

* Contact: Brass

Ordering Code:

CH87 ** * V * **
① ② ③ ④ ⑤ ⑥

- ① Series No.
② No. of contacts
③ Plating option:
1 = 3.05μm(120μ") Min. Tin
over 1.27μm(50μ") Nickel
2 = Gold flash plated over 1.27μm(50μ") Nickel
④ V = Straight
⑤ Insulation: 1 = PBT UL 94V-0, Color Black
2 = PBT UL 94V-0, Color Black
(RoHS Compliant)
A = Nylon 6T UL 94V-0, Color Black
(RoHS Compliant)
⑥ Option code: 00 = Dim.D 3.1mm
01 = Dim.D 2.8mm



Recommended P.C. Board Layout

④					DATE	UNIT: mm / inch	TITLE: 2.54MM(.100") STRAIGHT DUAL ROW BOX PIN HEADER	 瀚荃股份有限公司 CviLux Corporation			
③	SUN	7/19-05	ECN05245		7/20-05	TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL:				
②	LYNN	11/10-04	ECN04444/ECR04103-0		7/20-05	.X ± 0.30/.012 X' ± 1'		DRAWING NO.	CH8701SI	PART NO.	CH87***V***
①	SUN	4/09/04	ECN04144		7/20-05	.XX ± 0.20/.008 X' ±	FINISH:	SCALE	2 / 1	SHEET	1 OF 1
SYM	NAME	DATE	REVISIONS		APPROVED BY:	.XXX ± 0.10/.004 .XX ±					

