




Dimensions shown are IEC/ANSI standards


## Specifications

<b>Classification:</b>	Lithium
<b>Chemical System:</b>	Manganese Dioxide/Li/Organic Electrolyte
<b>Designation:</b>	ANSI-5018LC, IEC-CR17345
<b>Nominal Voltage:</b>	3V
<b>Typical Voltage:</b>	3.2-3.3V
<b>Nominal Internal Impedance:</b>	0.25 ohm @ 1 kHz
<b>Typical Weight:</b>	17g
<b>Typical Volume:</b>	7.18 cm <sup>3</sup> (cubic centimeters)
<b>Operating Temp:</b>	-20°C to 75°C (-4°F to 167°F)
<b>Capacity:</b>	1550 mAh
<b>Self Discharge:</b>	1.4% per year

## Duracell 2/3A Typical Performance



Information and contents in this data sheet are for reference purposes only. They do not constitute any warranty and representation is subject to change without notice. For most current information and further details, please contact Duracell.

**DURACELL®****DL2/3A****Li/MNO<sub>2</sub>****Lithium/Manganese Dioxide Battery**
**DURACELL®**  
**BATTERIES**

Berkshire Corporate Park  
Bethel, CT 06801 U.S.A.  
Telephone: Toll free 1.800.544.5454  
Internet: [www.duracell.com](http://www.duracell.com)

**\*Delivered capacity is dependent on the applied load, intermittent usage, operating temperature and cut off voltage. Please refer to the charts and discharge data for examples of energy/service life that the battery will provide for various conditions.**

Information and contents in this data sheet are for reference purposes only. They do not constitute any warranty and representation is subject to change without notice. For most current information and further details, please contact Duracell.