





	TIN	3&4, 7&8	39.50 [1.555]	10	4-644867-0
	TIN	3&4, 6&7	35.53 [1.399]	9	3-644867-9
	TIN	4&5	31.57 [1.243]	8	3-644867-8
	TIN	4&5	27.61 [1.087]	7	3-644867-7
	TIN	3&4	23.65 [.931]	6	3-644867-6
	TIN	NONE	19.69 [.775]	5	3-644867-5
	TIN	NONE	15.72 [.619]	4	3-644867-4
	TIN	NONE	11.76 [.463]	3	3-644867-3
	TIN-LEAD	3&4, 7&8	39.50 [1.555]	10	1-644867-0
	TIN-LEAD	3&4, 6&7	35.53 [1.399]	9	644867-9
	TIN-LEAD	4&5	31.57 [1.243]	8	644867-8
	TIN-LEAD	4&5	27.61 [1.087]	7	644867-7
	TIN-LEAD	3&4	23.65 [.931]	6	644867-6
	TIN-LEAD	NONE	19.69 [.775]	5	644867-5
	TIN-LEAD	NONE	15.72 [.619]	4	644867-4
	TIN-LEAD	NONE	11.76 [.463]	3	644867-3
	FINISH	BACKWALL INTERRUPTION(S) BETWEEN POST	L	NO.OF POSITIONS	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN B. LEWIS	210CT196	 TE Connectivity	
		CHK R. SWING	210CT196		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLG ± — 1. PLG ± — 2. PLG ± 0.1 [0.005] 3. PLG ± — 4. PLG ± — ± 1°		NAME MTA-156 HEADER ASSEMBLY, POLARIZED LOCK, STRAIGHT, .045 SQUARE POST, TIN OR TIN-LEAD PLATED, WITHOUT RETENTION PEGS, SPECIAL	
		APD D. CLARK		SIZE CASE CODE DRAWING NO A1 00779 C-644867	
MATERIAL 		FINISH 		RESTRICTED TO	
CUSTOMER DRAWING		WEIGHT —		SCALE 5:1 SHEET 1 of 1 REV J1	