


Fast recovery bridge rectifiers. 2 Amps. to 6 Amps.

The plastic material carries U/L recognition 94V-0.

Type	Max Avg Rect Current $I_{F(AV)}$ @ T_A R load		Input Voltage Recommended V_{RMS}	Peak Inverse Voltage V_{RRM}	Max Fwd Peak Surge Current I_{FSM}	Max Fwd Voltage @ $T_A = 25^\circ C$ V_F at $I_{F(AV)}$		Max Rev Current @ $T_A = 25^\circ C$ I_R	Max, Reverse Recovery Time t_{rr}
	(A)	($^\circ C$)				(V)	(A)		
			(V)	(V)	(A)	(V)	(A)	(μA)	(ns)



FKBP200 Series. 2 AMPS. Plastic Case. Outline : 6

FKBP200	2.0	50	20	50	35	1.3	1.0	10	150
FKBP201	2.0	50	40	100	35	1.3	1.0	10	150
FKBP202	2.0	50	80	200	35	1.3	1.0	10	150
FKBP204	2.0	50	125	400	35	1.3	1.0	10	150
FKBP206	2.0	50	250	600	35	1.3	1.0	10	250
FKBP208	2.0	50	380	800	35	1.3	1.0	10	500
FKBP210	2.0	50	440	1000	35	1.3	1.0	10	500




FBR300 Series. 3 AMPS. Plastic Case. Outline: 7

FBR300	3.0	50	20	50	35	1.4	1.5	10	150
FBR301	3.0	50	40	100	35	1.4	1.5	10	150
FBR302	3.0	50	80	200	35	1.4	1.5	10	150
FBR304	3.0	50	125	400	35	1.4	1.5	10	150
FBR306	3.0	50	250	600	35	1.4	1.5	10	250
FBR308	3.0	50	380	800	35	1.4	1.5	10	500
FBR310	3.0	50	440	1000	35	1.4	1.5	10	500



FKBL400 Series. 4 AMPS. Plastic Case. Outline: 8

FKBL400	4.0	50	20	50	150	1.4	4.0	10	150
FKBL401	4.0	50	40	100	150	1.4	4.0	10	150
FKBL402	4.0	50	80	200	150	1.4	4.0	10	150
FKBL404	4.0	50	125	400	150	1.4	4.0	10	150
FKBL406	4.0	50	250	600	150	1.4	4.0	10	250
FKBL408	4.0	50	380	800	150	1.4	4.0	10	500
FKBL410	4.0	50	440	1000	150	1.4	4.0	10	500



FBR600 Series. 6 AMPS. Plastic Case. Outline: 9

FBR600	6.0	50	20	50	150	1.3	3.0	10	150
FBR601	6.0	50	40	100	150	1.3	3.0	10	150
FBR602	6.0	50	80	200	150	1.3	3.0	10	150
FBR604	6.0	50	125	400	150	1.3	3.0	10	150
FBR606	6.0	50	250	600	150	1.3	3.0	10	250
FBR608	6.0	50	380	800	150	1.3	3.0	10	500
FBR610	6.0	50	440	1000	150	1.3	3.0	10	500