

## Sensor/Actuator cable - SAC-5P-10,0-PVC/M12FS B-L - 1431720

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator cable, 5-position, PVC, Black RAL 9005, Free cable end, on Socket straight M12, A - standard, Cable length: 10 m

### Product Features

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ Our PVC cable for average mechanical strain



### Key commercial data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 1 PCE                                                                                                   |
| Minimum order quantity | 25 PCE                                                                                                  |
| GTIN                   | <br>4 046356 506427 |
| Custom tariff number   | 85444290                                                                                                |
| Country of origin      | CHINA                                                                                                   |

### Technical data

#### General data

|                                 |                                  |
|---------------------------------|----------------------------------|
| Rated current at 40°C           | 4 A                              |
| Rated voltage                   | 60 V                             |
| Number of positions             | 5                                |
| Volume resistance               | ≤ 5 mΩ                           |
| Insulation resistance           | ≥ 100 MΩ                         |
| Length of cable                 | 10 m                             |
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket) |

#### General characteristics

|                       |                                       |
|-----------------------|---------------------------------------|
| Standards/regulations | M12 plug-in connector IEC 61076-2-101 |
|-----------------------|---------------------------------------|

# Sensor/Actuator cable - SAC-5P-10,0-PVC/M12FS B-L - 1431720

## Technical data

### General characteristics

|                             |                                             |
|-----------------------------|---------------------------------------------|
| Coding                      | A - standard                                |
| Surge voltage category      | II                                          |
| Pollution degree            | 3                                           |
| Degree of protection        | IP65/IP68/IP69K                             |
| Insertion/withdrawal cycles | ≥ 100                                       |
| Contact material            | CuSn                                        |
| Contact surface material    | Ni/Au                                       |
| Contact carrier material    | TPU GF                                      |
| Material of grip body       | TPU, hardly inflammable, self-extinguishing |
| Material, knurls            | Zinc die-cast, nickel-plated                |
| Status display              | No                                          |

### Conductor data

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| Cable type                                    | PVC black                               |
| Cable type (abbreviation)                     | PVC                                     |
| Cable abbreviation                            | LiYY                                    |
| UL AWM style                                  | 2464 / 1729 (80°C/300 V)                |
| Conductor cross section                       | 5x 0.34 mm <sup>2</sup> (signal line)   |
| AWG signal line                               | 22                                      |
| Conductor structure signal line               | 42x 0.10 mm                             |
| Core diameter including insulation            | 1.45 mm ±0.02 mm                        |
| Thickness, insulation                         | ≥ 0.23 mm (Core insulation)             |
| Wire colors                                   | brown, white, blue, black, green-yellow |
| Overall twist                                 | 5 wires around filler to the core       |
| External sheath, color                        | Black RAL 9005                          |
| Outer sheath thickness                        | ≥ 0.76 mm                               |
| External cable diameter D                     | 5.9 mm ±0.15 mm                         |
| Minimum bending radius, fixed installation    | 5 x D                                   |
| Minimum bending radius, flexible installation | 10 x D                                  |
| Cable weight                                  | 51 kg/km                                |
| Outer sheath, material                        | PVC                                     |
| Material conductor insulation                 | PVC                                     |
| Conductor material                            | Bare Cu litz wires                      |
| Insulation resistance                         | ≥ 200 MΩ*km (at 20 °C)                  |
| Conductor resistance                          | max. 58 Ω/km (at 20 °C)                 |
| Nominal voltage, conductor                    | ≤ 300 V                                 |
| Test voltage, conductor                       | ≥ 3000 V                                |
| Flame resistance                              | As per UL-Style 2464                    |

## Sensor/Actuator cable - SAC-5P-10,0-PVC/M12FS B-L - 1431720

### Technical data

#### Conductor data

|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Flame resistance                | According to UL 758/1581 FT1                    |
| Resistance to oil               | According to DIN EN 60811-2-1, 168 h at 90°C    |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)    |
| Ambient temperature (operation) | -25 °C ... 80 °C (cable, flexible installation) |

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC001855 |
| ETIM 5.0 | EC001855 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 11     | 31251501 |
| UNSPSC 12.01  | 31251501 |
| UNSPSC 13.2   | 31251501 |
| UNSPSC 6.01   | 31251501 |
| UNSPSC 7.0901 | 31251501 |

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |

### Approvals

#### Approvals

---

#### Approvals

UL Listed / cUL Listed / cULus Listed

---

#### Ex Approvals

---

#### Approvals submitted

## Sensor/Actuator cable - SAC-5P-10,0-PVC/M12FS B-L - 1431720

### Approvals

#### Approval details


|                                                                                             |       |
|---------------------------------------------------------------------------------------------|-------|
| UL Listed  |       |
| Nominal current I <sub>N</sub>                                                              | 4 A   |
| Nominal voltage U <sub>N</sub>                                                              | 125 V |

|                                                                                              |       |
|----------------------------------------------------------------------------------------------|-------|
| cUL Listed  |       |
| Nominal current I <sub>N</sub>                                                               | 4 A   |
| Nominal voltage U <sub>N</sub>                                                               | 125 V |

|                                                                                                  |  |
|--------------------------------------------------------------------------------------------------|--|
| cULus Listed  |  |
|--------------------------------------------------------------------------------------------------|--|


### Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side


Cable cross section



PVC black [PVC]

## Sensor/Actuator cable - SAC-5P-10,0-PVC/M12FS B-L - 1431720

Dimensioned drawing



Circuit diagram



M12 x 1 socket, straight

Contact assignment of the M12 sockets