

F

E

D

C

B

A

10

9

8

7

6

5

4

3

2

1

F





E

D

C

B

A




PANEL CUT OUT
MAX. PANEL THICKNESS-4.5mm

CONNECTOR SPECIFICATION:

VOLTAGE RATING	250 V
AMPERAGE RATING	4 AMPS
PROTECTION	IP68
ASSEMBLY IS RoHS COMPLIANT	

ITEM	COMPONENT	MATERIAL	FINISH
5	LOCKNUT	BRASS	BRIGHT NICKEL PLATED
4	O-RING	VITON	BLACK
3	RECEPTACLE SHELLS	BRASS	BRIGHT NICKEL PLATED
2	INSERT	PUR (30% GLASS FILLED)	-
1	CONTACT	BRASS (CuZn36)	GOLD OVER NICKEL

MALE FACE VIEW



DESCRIPTION EC NO: WEU2010-0391 DRWN: LSTEMMLE CHKD: NS APPR: NSTAUDIG 26.02.10 2010/03/03	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				DRAWN BY LSTEMMLE	DATE 2010/02/15	MICRO CHANGE M12-3-5P-MALE-REC-PCB BACK PANEL MOUNT			
				CHECKED BY FP	DATE 2010/03/01				
				APPROVED BY NSTAUDIG	DATE 2010/03/03		MOLEX INCORPORATED		
		ANGULAR ± --- °		MATERIAL NO. SEE TABLE					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
		2		SIZE A3					
		REV							