




THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
BD	39		G	REV PER EC 0G3B-0317-03	24APR03	VF GS



SECTION B-B



SECTION A-A



1. WIRE RANGE 18-16 AWG.
 2. INSULATION RANGE 2.54-2.03 [.100-.080] DIA.
 3. FOR LOOSE PIECE PART SEE DWG 66589.
- ⚠ 0.76µm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27µm [.000050] MIN TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA,
BOTH OVER 1.27µm [.000050] MIN NICKEL.
- ⚠ TIN PLATED.
- ⚠ 2.54µm [.000100] MIN SILVER OVER 1.27µm [.000050] MIN NICKEL.
- ⚠ GOLD PLATING PER MIL-G-45204, SILVER PER QQ-S-365, TIN PER MIL-T-10727
AND NICKEL PER QQ-N-290.
- ⚠ 0.76µm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27µm [.000050] MIN TIN IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.27µm [.000050] MIN NICKEL.

OBSOLETE

REVERSE REELED FOR MINI-APPLICATOR	8	66579-7
-	6	66579-6
REVERSE REELED FOR MINI-APPLICATOR	4	66579-4
-	4	66579-3
REVERSE REELED FOR MINI-APPLICATOR	5	66579-2
-	5	66579-1
DESCRIPTION	FINISH	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL BRASS MIL-C-50	FINISH SEE TABLE ⚠

DWN V. FURLER 14MAY2003	Tyco Electronics Corporation Harrisburg, PA 17105	
CHK G. STEINHAUER 16MAY03	NAME CONTACT, PIN, STRIP, TYPE VI, MULTIMATE	
APVD G. STEINHAUER 16MAY03	SIZE A3	CAGE CODE 00779
PRODUCT SPEC -	DRAWING NO C-66579	RESTRICTED TO -
APPLICATION SPEC -	SCALE 8:5	SHEET 1 OF 1
WEIGHT -	CUSTOMER DRAWING	REV G