


RED INDICATES ORIGINAL

DWG SIZE 	DATA CONTAINED IN THIS DOCUMENT IS PROPERTY OF TROMPETER ELECTRONICS, INC. AND SHALL NOT BE REPRODUCED, COPIED OR LOANED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.	REVISIONS			105-0376		SH 1C
		REV	ECO	DESCRIPTION	DWN	APPROVED	DATE
		H	12581	ADDED: -15, -16 & -17; SH 2 REDRAWN; SEE ECO	DKC	<i>WML</i>	10-2-83


TABLE 1	
DASH NO	DESCRIPTION
-1	TERM (NO CHAIN)
-2	TERM WITH 2.5 BRASS CHAIN
-3	TERM WITH 2.5 NYLON CHAIN
-4	TERM WITH 3.0 BRASS CHAIN
-5	TERM WITH 3.0 NYLON CHAIN
-6	TERM WITH 6.0 BRASS CHAIN
-7	TERM WITH 6.0 NYLON CHAIN
-8	TERM WITH 4.0 BRASS CHAIN
-9	TERM WITH 4.0 NYLON CHAIN

TABLE 2	
DASH NO	"A" DIA "B" DIA "C" DIM "D" DIA
-02	.630 .750 1.065 .450
-03	.505 .625 .941 .369
-04	.439 .562 .878 .355
-05	.380 .500 .816 .325
-06	.317 .437 .753 .295
-07	.281 .408 .722 .278
-08	.610 .750 1.065 .450
-09	.567 .687 1.003 .419
-008	.330 .450 .766 .300


INCH	MM	INCH	MM	INCH	MM	INCH	MM	INCH	MM
.005	0.13	.200	7.37	.410	10.64	.625	15.88	.941	23.90
.010	0.25	.295	7.49	.437	11.10	.830	18.00	1.003	25.48
.030	0.76	.300	7.62	.436	11.15	.867	17.45	1.066	27.08
.032	0.81	.317	8.05	.450	11.43	.722	18.34	2.5	63.50
.062	1.57	.325	8.26	.500	12.70	.750	19.05	3.0	76.20
.140	3.55	.330	8.38	.505	12.83	.753	19.13	4.0	101.60
.200	5.08	.355	9.02	.56	14.22	.766	19.40	4.5	114.30
.25	6.35	.380	9.65	.562	14.27	.816	20.73	6.0	152.40
.278	7.06	.388	9.85	.567	14.40	.827	21.01	7.0	177.80
.281	7.14	.406	10.31	.610	15.48	.878	22.30	10.0	254.00




-1 SHOWN
NO CHAIN, STAINLESS STEEL
ROPE OR MOUNTING LUG




-2-△ THRU -11-△ SHOWN
STANDARD CHAIN & BASIC MOUNTING LUG



-12-△ THRU
-17-△ SHOWN
STAINLESS STEEL ROPE
AND BASIC MOUNTING LUG



-2-△ -02 THRU
-11-△ -008 SHOWN
STANDARD CHAIN AND BULKHEAD JACK
MOUNTING LUG



-12-△ -02 THRU
-17-△ -008 SHOWN
STAINLESS STEEL ROPE
AND BULKHEAD JACK
MOUNTING LUG


△ NOTE LENGTH FOR SST ROPE WITH
MTG LUG OPTION IS NOT MEASURED
TO CENTER OF BULKHEAD MTG LUG

5. EXAMPLE OF COMPLETE MODEL NO:
TN1-2-△ -02
- BASIC MODEL NO
TN1 (50 OHM)
UTN1 (75 OHM)
- CHAIN/ROPE MATL
AND LENGTH
(SEE TABLE 1)
- BULKHEAD JACK MOUNTING LUG
(OPTIONAL) WITH BRASS OR
NYLON CHAIN AND STAINLESS
STEEL ROPE (SEE TABLE 2)

4. TERMINATED MALE COAXIAL 50 & 75 OHM N TYPE
PLUG WITH CHAIN & MOUNTING LUG OPTIONS

△ RESISTANCE VALUE IN OHMS (1/2W, 1%)
SHOWN SHORTED TO CASE AND RESISTOR

2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE IN INCHES



QTY	DESCRIPTION	PART NUMBER	ITEM
10, UNLESS SPECIFIED			
BY ± .005			
WIDE			
ANGLES			
DWN 1 DKC 9-30-88			
CHK 6M 10-6-88			
ENGR 7/7			
APPR 1/1			
NEXT ASSY			
SCALE 2/1			
DATE 11-27-72			
SHEET			
IC			

14949	105-0376	H
-------	----------	---

TROMPETER ELECTRONICS, INC.	TN1/UTN1
--------------------------------	----------

14949	105-0376	H
-------	----------	---

14949	105-0376	H
-------	----------	---