

MICRO SWITCH
FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL INC.
FED. MFG. CODE 91929

**SMALL PRECISION
LIMIT SWITCH**

CATALOG LISTING
914CE3-3K

M
914CE3-3K

DRAWING
NUMBER

ISSUE

REVISIONS

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19


20

21


22

23

RELEASE NO. PR-16944
CHECK
1/6 DEC 88
FO-52848-B



NOTE
1 - ZINC HOUSING FINISHED WITH GREY PAINT



CIRCUIT DIAGRAM

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - 5 LBS MAX

DIFFERENTIAL TRAVEL - - - .004 MAX
OVERTRAVEL - - - - - .118 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

5A 1/10 HP 125 OR 250 VAC

RJ ©

SCALE FULL DO NOT SCALE PRINT

THIRD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
ONE PLACE (.0) $\pm .030$
TWO PLACE (.00) $\pm .015$
THREE PLACE (.000) $\pm .005$
ANGLES $\pm$

WEIGHT