









SECTION L—L
SCALE 8:1




SEE SHEET 2 FOR HOLE PATTERN


3.56 [.140]		1-145154-2
3.18 [.125]		145154-8
2.54 [.100]		145154-4
2.54 [.100]		145154-3
2.54 [.100]		145154-2
2.54 [.100]		145154-1
W	FINISH	PART NUMBER

SUPERSEDED BY 145154-4
OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: R BROWN 6/9/95 CHK: M BOWERS 6/9/95		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.01] 3 PLC ± 0.127 [.005] 4 PLC ± — ANGLES ± ±°		NAME CONNECTOR ASSEMBLY, 60 DUAL POSITION, 127 [.050] SERIES,	
		AFVD — PRODUCT SPEC 108-14034 APPLICATION SPEC 114-26012		SIZE A1	
MATERIAL 		WEIGHT —		CAGE CODE 00779	
FINISH 		DRAWING NO 145154		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 OF 2 REV G	



RECOMMENDED MATING BOARD EDGE CONFIGURATION



RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN
(CONNECTOR SIDE SHOWN)