

LOC	
CE	
DIST	
16	

8

Geom. Spec: N/A



B ————— A

Geom. Spec: N/A

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

A	Rev Per EC#	RELEASE	7/29/2008	-	J
P	LTR	REVISION RECORD	DATE	DIN	AF

DIMENSIONS:
meters



Restricted To:

QW Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
QK Jeremy Duncan					
APVD Jeremy Duncan					
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO C- 1906001		SHEET 1 of 4	REV A

Product	Secure	MM	State	N/A
Duplex Secure				
MM				
State				
N/A				

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	7/29/2008	-	JD		
P	LTR		REVISION RECORD	DATE	DIN	APVD		

Qty	U of M	Description	Item No.
2	piece	Trace Label	10
2	piece	CONN SUBASSY, MM, SC 1.6MM	9
4	piece	Eyelet/Shrink tube assembly - White	8
2	piece	SC Duplex Clip	7
AR	meter	2 fiber, 50/125, 2.0mm, Twinzip, Orange, OFNR (Riser)	6
2	piece	2.5mm ferrule cover	5
2	piece	SC Simplex Housing, Beige	4
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	3
1	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DIM Cable Assy Configurator ORK Jeremy Duncan APVO Jeremy Duncan NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex		MATERIAL - HEAT TREAT -	
		0.125 PL ± 0.125 PL ± 0.125 PL ± 0.125 PL ± 0.125 PL ±	0.125 PL ± 0.125 PL ± 0.125 PL ± 0.125 PL ± 0.125 PL ±	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
Restricted To:				SCALE NTS SIZE A2	DRAWING NO. C-1906001	SHEET 2 of 4	REV A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	7/29/2008	-		JE
P	LTR		REVISION RECORD	DATE	DIN		AP

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

DBN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Jeremy Duncan		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Jeremy Duncan					
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex					
SCALE NTS		SIZE A2		DRAWING NO C- 1906001	
				SHEET 3 of 4	
				REV A	

	USED ON
--	---------

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

THIS DRAWING IS A CONTROLLED DOCUMENT.

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

	A	Rev Per EC#	RELEASE	7/29/2008	-	JD			
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DWG Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Jeremy Duncan			
APVD	Jeremy Duncan			
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1906001	SHEET 4 of 4	REV A

8

7

6

5

4

3

2

1