


AEH-ALH80 Series

144 Watts

Total Power: 144 Watts
Input Voltage: 48 V
of Outputs: Single



Special Features

- Ultra high efficiency
- Open frame (ALH80) and Baseplate (AEH80)
- Redundant output power pins (with single pair option)
- Positive or negative enable logic control option
- Low output ripple and noise
- High capacitive load limit on start-up
- Remote sense compensation
- Regulation to zero load
- Fixed frequency switching (400 kHz)
- Meets basic insulation

Safety

- UL, cUL 60950 Recognized
- TUV EN60950 Licensed

Electrical Specifications

Input

Input range:	36-75 Vdc
Input surge:	100 V / 100 ms
Efficiency:	87% @ 1.8 V (typical)

Output

Regulation: (Line, Load, Temp)	< 2%
Ripple and noise ¹ :	50 mVp-p (typical)
Remote sense:	Up to 10% Vo
Output voltage adjust range:	± 10% Vo, nominal
Transient response:	4% deviation with 50 to 75% step load 300 µs recovery
Overvoltage protection:	130% Vo,nominal (latching)
Overcurrent protection:	120% Io,max (latching)
Overtemperature protection:	Shutdown - autorecovery mode
Isolation voltage:	1500 Vdc

Control

Enable:	TTL compatible (positive or negative enable options)
---------	--

Environmental Specifications

Operating temperature:	-40 °C to +100 °C baseplate (AEH80) -40 °C to +85 °C Ambient Air (ALH80)
Storage temperature:	-55 °C to +125 °C
Overtemperature protection:	115 °C PCB temperature typical
MTBF:	> 1 million hours



Ordering Information

Input Voltage	Output Voltage	Efficiency ²	Model Number
48 V	1.2 V @ 80 A	83%	AEH80K48(N)-(3)
48 V	1.5 V @ 80 A	85%	AEH80M48(N)-(3)
48 V	1.8 V @ 80 A	87%	AEH80Y48(N)-(3)
48 V	1.8 V @ 80 A	87%	AEH80Y48N-63T
48 V	1.2 V @ 80 A	83%	ALH80K48(N)-(3)
48 V	1.5 V @ 80 A	85%	ALH80M48(N)-(3)
48 V	1.8 V @ 80 A	87%	ALH80Y48(N)-(3)

Notes:

Typical efficiency measured at nominal input voltage at an ambient temperature of $T_a = 25^\circ\text{C}$


Options:

Suffix "N": = for Negative Enable (default is Positive Enable without suffix "N")


Suffix "-3": = Standard half brick pinout (pins 6 and 10 omitted)

Standard pin length is 5 mm nominal. Consult factory for other options.

OPEN FRAME (ALH)



BASEPLATE (AEH)



Pin Assignments

Pin Number	Function
Pin 1	+Vin
Pin 2	Enable (On/Off)
Pin 3	Case (AEH)
Pin 4	-Vin
Pin 5	+ Output
Pin 6	+ Output (optional pin)
Pin 7	+ Sense
Pin 8	Trim
Pin 9	- Sense
Pin 10	- Output (optional pin)
Pin 11	- Output

Notes:

- 20 MHz bandwidth. External 10uF tant. capacitor + 0.1uF cer. capacitor placed from +V out to -V out.
- Requires a 2.2 mf, 100V film capacitor connected between +V in and -V in to meet FCC class A and ETS300-386-1 requirements for conducted noise. Consult Factory for filtering information to meet FCC class B, VDE or EIC specifications.
- Suffix "-6" for 3.7mm nominal pin length, "3" for standard halfbrick pinout (Pin 6 & 10 omitted), "T" for tuned version for specific transient response requirement. Minimum capacitance required. Refer to TRN for details.
- All specifications are typical at nominal line, full load, and 25°C unless otherwise noted.
- All specifications subject to change without notice. Mechanical drawings are for reference only.
- Technical Reference Notes should be consulted for detailed information when available.
- Warranty: 1yr

Americas

5810 Van Allen Way
Carlsbad, CA 92008
USA
Telephone: +1 760 930 4600
Facsimile: +1 760 930 0698

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
Telephone: +44 (0) 1384 842 211
Facsimile: +44 (0) 1384 843 355

Asia (HK)

14/F, Lu Plaza
2 Wing Yip Street
Kwun Tong, Kowloon
Hong Kong
Telephone: +852 2176 3333
Facsimile: +852 2176 3888

For global contact, visit:

www.Emerson.com/EmbeddedPower
techsupport.embeddedpower@emerson.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

Emerson Network Power.
The global leader in enabling
business-critical continuity.

- AC Power
- Connectivity
- DC Power
- Embedded Computing
- Embedded Power**
- Monitoring
- Outside Plant
- Power Switching & Controls
- Precision Cooling
- Racks & Integrated Cabinets
- Services
- Surge Protection

EmersonNetworkPower.com

Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co.
©2008 Emerson Electric Co.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Emerson Network Power:

[ALH80K48](#) [ALH80K48-3](#) [ALH80K48-3L](#) [ALH80K48-L](#) [ALH80K48N](#) [ALH80K48N-3L](#) [ALH80M48](#) [ALH80M48-3](#)
[ALH80M48-3L](#) [ALH80M48N-3L](#) [ALH80Y48-L](#)