



10 9 8 7 6 5 4 3 2 1



NOTES :


- 1) MATERIAL :
HOUSING : HIGH TEMPERATURE LIQUID CRYSTAL POLYMER, UL94V-0
COLOUR : BLACK
CONTACTS : COPPER ALLOY
LATCHES : HIGH TEMPERATURE NYLON, UL94V-0
COLOUR : NATURAL (OFF-WHITE)
- 2) FINISH :
CONTACT AREA : 0.76 MICROMETER (30 MICROINCH) MIN GOLD OVER
1.25 MICROMETER (50 MICROINCH) MIN NICKEL
SOLDER LEADS : 2.54 MICROMETER (100 MICROINCH) MIN TIN OVER
1.25 MICROMETER (50 MICROINCH) MIN NICKEL
- 3) ACCEPTS 1.0 mm THICK MEMORY MODULE PER JEDEC MO-244
FOR 244 CKTS AND MO-258 FOR 200 CKTS.
- 4) PRODUCT SPECIFICATION : PS-87918-001
- 5) PACKAGING SPECIFICATION: PRODUCT SHALL BE PACKED IN TRAY.
SEE TABLE ON SHEET 4.

- △6) DATE CODE SHALL BE MARKED LEGIBLY AS SHOWN :YYDDDD
- △7) PART NUMBER SHALL BE MARKED LEGIBLY AS SHOWN.
87918-XXXX(REFER TO TABLE)




ADDED PKG SPEC EC NO: S2012-0054 DRWN: JAKEEWEH CHKD: CTEH APPR: SHLENI REV		DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
						DRAWN BY DATE		TITLE MINI DIMM, 0.60MM PITCH 244/200 CKTS STANDARD R/A				
						EDMUND 2004/08/17						
						4 PLACES ± --- ± ---		CHECKED BY DATE		MOLEX MOLEX INCORPORATED		
		3 PLACES ± --- ± ---		SRRAMESH 2005/01/25								
		2 PLACES ± 0.13 ± ---		APPROVED BY DATE		DOCUMENT NO. SD-87918-001						
		1 PLACE ± 0.25 ± ---		GGLLEE 2005/01/25								
		ANGULAR ± 1 °		MATERIAL NO.		SHEET NO. 1 OF 4						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE								
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						


9 8 7 6 5 4 3 2 1



SHEET NO.
2 OF 4



RECOMMENDED PCB LAYOUT



ADDED PKG SPEC EC NO: S2012-0054 DRWN: JAKEWEW CHKD: CTEH APPR: SHLENI	2011/07/15	2011/08/03	2011/08/23	QUALITY SYMBOLS F _A =0 F _C =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.13</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± 0.25</td><td>± ---</td></tr><tr><td colspan="3">ANGULAR ± 1 °</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.13	± ---	1 PLACE	± 0.25	± ---	ANGULAR ± 1 °			DIMENSION STYLE MM ONLY DRAWN BY DATE EDMUND 2004/08/17 CHECKED BY DATE SRRAMESH 2005/01/25 APPROVED BY DATE GGLEE 2005/01/25 MATERIAL NO.	SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE MINI DIMM, 0.60MM PITCH 244/200 CKTS STANDARD R/A MOLEX INCORPORATED DOCUMENT NO. SD-87918-001	SHEET NO. 3 OF 4
		mm	INCH																										
	4 PLACES	± ---	± ---																										
	3 PLACES	± ---	± ---																										
	2 PLACES	± 0.13	± ---																										
1 PLACE	± 0.25	± ---																											
ANGULAR ± 1 °																													
REV	DESCRIPTION	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																										
B3																													

