





Technical drawing of a shaft and housing assembly. The drawing shows a cross-section of the assembly with the following dimensions and tolerances:

- Shaft diameter: $\varnothing 3.36 \pm 0.05$ [$.132 \pm .002$]
- Housing bore diameter: $\varnothing 3.33 \pm 0.05$ [$.131 \pm .002$]
- Shaft length: 10.06 ± 0.10 [$.396 \pm .004$]
- Housing length: 1.37 ± 0.10 [$.054 \pm .004$]
- Shaft step height: 2.97 [$.117$]
- Housing step height: 2.90 [$.114$]
- Label: MATING FACE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 14 OCT 97 C. OBERMAN R. STONE 15 OCT 97 GHK R. STEINHAUER 09 JAN 98 RPO		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.15 [0.05] 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME MINIATURE RECTANGULAR MALE BLOCK, 34 POSITION, M SERIES	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE A1	
MATERIAL PHENOLIC, BLACK		FINISH —		CAGE CODE 00779	
		WEIGHT —		DRAWING NO C-200837	
		CUSTOMER DRAWING		SCALE 2:1 SHEET 1 OF 1 REV Z	

AMP 4805 REV 31MAR2000