














DESCRIPTION: **RIGHT ANGLE .590" MALE PLASTIC D-SUB**



Technical drawing of a mechanical part, likely a bearing housing, showing dimensions in millimeters. The drawing includes a cross-section view with various features labeled with dimensions: 14.99, 0.590, 0.112, 2.84, 0.110, 2.79, 0.232, 0.389, 1.25, and 3.18. A note <C> is also present.

177-XXX-110-XX1

ELECTRICALS:
CURRENT RATING: 5 AMPS

	PLASTIC SHELL		METAL SHELL WITH INSIDE GROUND STRAPS		METAL SHELL WITH RETAINING CLIP GROUND		PLASTIC SHELL WITH PLASTIC SNAP LOCK
	06		16		36		S6
.120" DIA. HOLE							
	07		17		37		S7
4-40 FLUSH INSERT							
	08		18		38		S8
4-40 HEX STANDOFF FEMALE SCREWLOCK							
	09		19		39		S9 with washers
4-40 ROUND STANDOFF FEMALE SCREWLOCK							

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		
	DRAWN: PAM JENKINS		DATE: 11-3-98
	CHECKED:	DATE:	
NorComp	SCALE:	SHEET 2 OF 2	REV 3
	DWG NO. 177 SERIES HARDWARE		