




1 AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.

2 STANDOFFS: POSN 12 (9) STANDOFFS, AS SHOWN.
POSN 16 (12) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 20 (15) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 24 (18) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 28 (21) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 32 (24) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 36 (27) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 40 (30) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 44 (33) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 48 (36) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 52 (39) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 56 (42) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 60 (45) STANDOFFS, 3 PER DIAGONAL ROW.



3 FINISH: BRIGHT TIN—LEAD .000100—.000200 THK OVER
NICKEL .000050 MIN THK.

4 HEIGHT AFTER TERMINATION IS .238 REF.

5 CAVITY IDENTIFICATION MOLDED IN THIS AREA.

6 FINISH: BRIGHT TIN .000100—.000200 THK OVER
NICKEL .000050 MIN THK.

RECOMMENDED HOLE LAYOUT



		2.950	2.950	3.274	2.950	2.950	59	60	6-111035-3
		2.150	2.150	2.474	2.150	2.150	43	44	5-111035-9
		1.950	1.950	2.274	1.950	1.950	39	40	5-111035-8
		1.750	1.750	2.074	1.750	1.750	35	36	5-111035-7
		1.550	1.550	1.874	1.550	1.550	31	32	5-111035-6
		1.150	1.150	1.474	1.150	1.150	23	24	5-111035-4
		.950	.950	1.274	.950	.950	19	20	5-111035-3
		.750	.750	1.074	.750	.750	15	16	5-111035-2
		2.950	2.950	3.274	2.950	2.950	59	60	1-111035-3
OBSOLETE		2.750	2.750	3.074	2.750	2.750	55	56	1-111035-2
OBSOLETE		2.550	2.550	2.874	2.550	2.550	51	52	1-111035-1
OBSOLETE		2.350	2.350	2.674	2.350	2.350	47	48	1-111035-0
		2.150	2.150	2.474	2.150	2.150	43	44	111035-9
		1.950	1.950	2.274	1.950	1.950	39	40	111035-8
		1.750	1.750	2.074	1.750	1.750	35	36	111035-7
		1.550	1.550	1.874	1.550	1.550	31	32	111035-6
OBSOLETE		1.350	1.350	1.674	1.350	1.350	27	28	111035-5
		1.150	1.150	1.474	1.150	1.150	23	24	111035-4
		.950	.950	1.274	.950	.950	19	20	111035-3
		.750	.750	1.074	.750	.750	15	16	111035-2
OBSOLETE		.550	.550	.874	.550	.550	11	12	111035-1
	FINISH	F	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG J. PEACHEY	05-MAR-86			TE Connectivity	
						CHK. M. SCULLY	23-MAY-86				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APP'D D. HOFFMAN	23-MAY-86	NAME			
INCHES						PRODUCT SPEC		KIT, AMP-LATCH PADDLEBOARD			
		0 PLC ± .				APPLICATION SPEC		PREASSEMBLED, .100 LONG POSTS			
		1 PLC ± .				114-40005		FULL ROW, FULL TIN PLATED CONTACTS			
		2 PLC ± .				SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		3 PLC ± . G05				WEIGHT		A-1	00779	C-111035	-
		4 PLC ± .				FINISH		SCALE		SHEET	1 OF 1
MATERIAL		ANGLES				CONTACTS		CUSTOMER DRAWING		REV	
HOLD PARTS: 94V-0 RATES		CONTRACTS PH BRZ PER GD-9-750				A-1		SCALE		1 OF 1	