


EP17 LM259X Inductor
47 uHy 3.70 ADC



ELECTRICAL SPECS:

- 1: INDUCTANCE: @ 10 kHz, 0.1 Vrms
(1 thru 4 to 5 thru 8) = 47 - 60 uHy
- 2: DCRs:
(1 thru 4 to 5 thru 8) = 0.040 Ohms Max.
- 3: SRF: 2.0 MHz Min
- 4: HIPOT: 500 VDC
Winding to core (2 Sec., 5 mA Max)

All pins may not be used.
Specifications at room temperature of 25 C.

A	3/28/03		KAM	Production Release		
REV.	DATE	ECN	BY	DESCRIPTION		
TOLERANCES ON				Newava Tech. Watertown, SD 57201 605-886-0264		
.XXX	.XX	ANGLE				
+	-	+	-	47 uHy Inductor 3.70 ADC		
				DATE		
DRAWN:				SCALE	MODEL	DRAWING NO.
CHECKED: -						
APPROVED: -				NEXT ASSY:		
THIS PRINT MUST NOT BE COPIED IN WHOLE OR IN PART						OR USED DETRIMENTALLY TO OUR INTEREST
						SHEET 1 OF 1