





Phase Control SCR, 35 A



TO-247AC



DESCRIPTION/FEATURES

The 40TPS...APbF High Voltage Series of silicon controlled rectifiers are specifically designed for medium power switching and phase control applications. The glass passivation technology used has reliable operation up to 125 °C junction temperature. Low Igt parts available.



RoHS*
COMPLIANT

Typical applications are in input rectification (soft start) and these products are designed to be used with Vishay HPP input diodes, switches and output rectifiers which are available in identical package outlines.

This product has been designed and qualified for industrial level and lead (Pb)-free ("PbF" suffix).

PRODUCT SUMMARY

V_T at 40 A	< 1.45 V
I_{TSM}	500 A
V_{RRM}	800/1200 V

MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VALUES	UNITS
$I_{T(AV)}$	Sinusoidal waveform	35	A
I_{RMS}		55	
V_{RRM}/V_{DRM}		800/1200	V
I_{TSM}		500	A
V_T	40 A, $T_J = 25\text{ }^{\circ}\text{C}$	1.45	V
dV/dt		1000	V/ μs
dI/dt		100	A/ μs
T_J		- 40 to 125	$^{\circ}\text{C}$

VOLTAGE RATINGS

PART NUMBER	V_{RRM}/V_{DRM} , MAXIMUM REPETITIVE PEAK AND OFF-STATE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM}/I_{DRM} AT 125 °C mA
40TPS08APbF	800	900	10
40TPS12APbF	1200	1300	
40TPS08PbF	800	900	
40TPS12PbF	1200	1300	

* Pb containing terminations are not RoHS compliant, exemptions may apply

40TPS...APbF/40TPS...PbF High Voltage Series

Vishay High Power Products Phase Control SCR, 35 A



ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average on-state current	I _{T(AV)}	T _C = 79 °C, 180° conduction half sine wave		35	A
Maximum continuous RMS on-state current as AC switch	I _{T(RMS)}			55	
Maximum peak, one-cycle non-repetitive surge current	I _{TSM}	10 ms sine pulse, rated V _{RRM} applied	Initial T _J = T _J maximum	500	
		10 ms sine pulse, no voltage reapplied		600	
Maximum I ² t for fusing	I ² t	10 ms sine pulse, rated V _{RRM} applied		1250	A ² s
		10 ms sine pulse, no voltage reapplied		1760	
Maximum I ² √t for fusing	I ² √t	t = 0.1 to 10 ms, no voltage reapplied		12 500	A ² √s
Low level value of threshold voltage	V _{T(TO)1}	T _J = 125 °C		1.02	V
High level value of threshold voltage	V _{T(TO)2}			1.23	
Low level value of on-state slope resistance	r _{t1}			9.74	mΩ
High level value of on-state slope resistance	r _{t2}			7.50	
Maximum peak on-state voltage	V _{TM}	110 A, T _J = 25 °C		1.85	V
Maximum rate of rise of turned-on current	di/dt	T _J = 25 °C		100	A/μs
Maximum holding current	I _H			150	mA
Maximum latching current	I _L			300	
Maximum reverse and direct leakage current	I _{RRM} /I _{DRM}	T _J = 25 °C	V _R = Rated V _{RRM} /V _{DRM}	0.5	
		T _J = 125 °C		10	
Maximum rate of rise of off-state voltage 40TPS08	dV/dt	T _J = T _J maximum, linear to 80 % V _{DRM} , R _g -k = Open		500	V/μs
Maximum rate of rise of off-state voltage 40TPS12				1000	

TRIGGERING					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum peak gate power	P _{GM}			10	W
Maximum average gate power	P _{G(AV)}			2.5	
Maximum peak gate current	I _{GM}			2.5	A
Maximum peak negative gate voltage	- V _{GM}			10	V
Maximum required DC gate voltage to trigger	V _{GT}	T _J = - 40 °C	Anode supply = 6 V resistive load	4.0	V
		T _J = 25 °C		2.5	
		T _J = 125 °C		1.7	
Maximum required DC gate current to trigger	I _{GT}	T _J = - 40 °C		270	mA
		T _J = 25 °C		150	
		T _J = 125 °C		80	
		T _J = 25 °C, for 40TPS08APbF and 40TPS12APbF		40	
Maximum DC gate voltage not to trigger	V _{GD}	T _J = 125 °C, V _{DRM} = Rated value		0.25	V
Maximum DC gate current not to trigger	I _{GD}			6	mA



40TPS...APbF/40TPS...PbF High Voltage Series

Phase Control SCR, 35 A Vishay High Power Products

THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	T _J , T _{Stg}		- 40 to 125	°C
Maximum thermal resistance, junction to case	R _{thJC}	DC operation	0.6	°C/W
Maximum thermal resistance, junction to ambient	R _{thJA}		40	
Maximum thermal resistance, case to heatsink	R _{thCS}	Mounting surface, smooth and greased	0.2	
Approximate weight			6	g
			0.21	oz.
Mounting torque	minimum		6 (5)	kgf · cm (lbf · in)
	maximum		12 (10)	
Marking device		Case style TO-247AC	40TPS08A	
			40TPS12A	
			40TPS08	
			40TPS12	

40TPS...APbF/40TPS...PbF High Voltage Series

Vishay High Power Products Phase Control SCR, 35 A




Fig. 1 - Current Rating Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 3 - On-State Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current



40TPS...APbF/40TPS...PbF High Voltage Series

Phase Control SCR, 35 A Vishay High Power Products




Fig. 7 - On-State Voltage Drop Characteristics




Fig. 8 - Gate Characteristics




Fig. 9 - Thermal Impedance Z_{thJC} Characteristics

40TPS...APbF/40TPS...PbF High Voltage Series

Vishay High Power Products Phase Control SCR, 35 A



ORDERING INFORMATION TABLE

Device code	40	T	P	S	12	A	PbF
	1	2	3	4	5	6	7
	1	-	Current rating (40 = 40 A)				
	2	-	Circuit configuration: T = Thyristor				
	3	-	Package: P = TO-247				
	4	-	Type of silicon: S = Standard recovery rectifier				
	5	-	Voltage ratings			08 = 800 V 12 = 1200 V	
	6	-	• A = Low Igt selection 40 mA maximum • None = Standard Igt selection				
	7	-	• None = Standard production • PbF = Lead (Pb)-free				

LINKS TO RELATED DOCUMENTS	
Dimensions	http://www.vishay.com/doc?95223
Part marking information	http://www.vishay.com/doc?95226

**DIMENSIONS** in millimeters and inches**Lead assignments****Diodes**

1. - Anode/open
2. - Cathode
3. - Anode

SYMBOL	MILLIMETERS		INCHES		NOTES
	MIN.	MAX.	MIN.	MAX.	
A	4.65	5.31	0.183	0.209	
A1	2.21	2.59	0.087	0.102	
A2	1.50	2.49	0.059	0.098	
b	0.99	1.40	0.039	0.055	
b1	0.99	1.35	0.039	0.053	
b2	1.65	2.39	0.065	0.094	
b3	1.65	2.37	0.065	0.094	
b4	2.59	3.43	0.102	0.135	
b5	2.59	3.38	0.102	0.133	
c	0.38	0.86	0.015	0.034	
c1	0.38	0.76	0.015	0.030	
D	19.71	20.70	0.776	0.815	3
D1	13.08	-	0.515	-	4

SYMBOL	MILLIMETERS		INCHES		NOTES
	MIN.	MAX.	MIN.	MAX.	
D2	0.51	1.30	0.020	0.051	
E	15.29	15.87	0.602	0.625	3
E1	13.72	-	0.540	-	
e	5.46 BSC		0.215 BSC		
FK	2.54		0.010		
L	14.20	16.10	0.559	0.634	
L1	3.71	4.29	0.146	0.169	
N	7.62 BSC		0.3		
ΦP	3.56	3.66	0.14	0.144	
$\Phi P1$	-	6.98	-	0.275	
Q	5.31	5.69	0.209	0.224	
R	4.52	5.49	1.78	0.216	
S	5.51 BSC		0.217 BSC		

Notes

- (1) Dimensioning and tolerancing per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6) ΦP to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- (7) Outline conforms to JEDEC outline TO-247 with exception of dimension c



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.