

SLIM BODY FLAT RIBBON IDC CABLES

(2.54 mm) .100" PITCH • IDSS/IDSD/IDMS/IDMD SERIES



IDSS/IDMS/IDMD

Mates:

TSW, MTSW, TSM, EJH,
PHT, HMTSW, HTSW,
HW, DW, EW, ZW, MTLW

IDSD

Mates:

TST, HTST, ZST, EJH

SERIES	ROW OPTION	NO. PINS PER ROW
IDM = Standard Tail Male Plug	S = Single	-02 thru -32 = IDMS/IDMD
IDS = Socket	D = Double (Color coded cable Not available for 31 thru 36 pins/row. See -G option.)	-02 thru -36 = IDSS/IDSD

SPECIFICATIONS

Insulator Material:

Black Glass Filled Polyester

Contact (IDSS/IDSD):

BeCu

Terminal (IDMS/IDMD):

Phosphor Bronze

Plating:

Au over 50 μ " (1.27 μ m) Ni or
Sn over 100 μ " (2.54 μ m) Cu or
50 μ " (1.27 μ m) Ni

Wire:

28 AWG 7/36 stranded
Tinned Copper

Operating Temp Range:

-20 °C to +105 °C
(Rainbow Cable)
-40 °C to +105 °C
(Gray Cable)

Current Rating (IDMD):

3 A per pin
(2 pins powered)

Voltage Rating:



425 VAC/600 VDC

Lead Size Range:

(0.56 mm) .022" SQ to
(0.71 mm) .028" SQ

Lead Insertion Depth:

(5.59 mm) .220" to
(6.22 mm) .245"



ALSO AVAILABLE

Molded-To-Position IDC Assemblies

Low Profile





Skinny side locks

Dual beam contacts

Single and double row

(6.35mm) .025" square and
(5.84mm) .230" length tail available



Visit samtec.com?HCSD, samtec.com?HCSS,
samtec.com?HCMD or samtec.com?HCMS
for more detailed information.



Note:

This Series is non-standard,
non-returnable.

samtec.com?IDSS, samtec.com?IDSD, samtec.com?IDMS or samtec.com?IDMD



END ASSEMBLY

-S

= Single End
(Socket or Male Plug on one end)

-D

= Double End
(Socket or Male Plug on each end)

-T

= Transfer End
(Male Plug on one end with socket on other.
Begin part number with IDM)

ASSEMBLED LENGTH

-"XX.XX"

= Assembled Length

OPTION

-T

= Tin Plating
(Both Ends)

-C

= Tin IDM,
10 μ " (0.25 μ m) Gold IDS
(-T End Assembly Required)

-A

= Tin IDS,
10 μ " (0.25 μ m) Gold IDM
(-T End Assembly Required)

-P "XX"

= Polarized
Specify "XX" as position.
For Double the same position
will be polarized on both ends.
(Not available on IDM unless transfer,
then only the socket is polarized.)

-G

= Gray Cable
Specify -G for Gray cable.
Gray cable has one red edge.
IDSS and IDMS uses
(2.54 mm) .100" centerline cable.
IDSD and IDMD uses
(1.27 mm) .050" centerline cable.
Cable is 28 AWG 7/36 copper wire.
Standard cable is same as
above except color

-ST "X"

= Stripped & Tinned
(Specify Suffix from table)
(All dimensions are $\pm 1/16$ " (1.59 mm)
(Not available in 28 positions and higher)

-B "XX"

= Breakout
(Specify "XX" as number of
conductors to be broken out)
(Breakout starts with Number 1 lead
indicated by brown wire or red stripe.
Shown on top side)

-RW

= Reverse Wiring
(#1 wire opposite position #1)

-S "XX"

= Daisy Chain, Single
(When mating double row
connector with two single row
connectors, the outer most single will
be connected to Conductor #1 and
the inside single to Conductor #2)

-D "XX"

= Daisy Chain, Double

-W "XX"

= Wiring Reverse Daisy Chain, Single
(Same as -S "XX" except outer strip
connected to Conductor #2 and inside
strip connected to Conductor #1)

-R

= Reversed

-M


= Middle Reversed
(Requires -SXX, -WXX or -DXX)

-O

= Outside Reversed
(Requires -SXX, -WXX or -DXX)



Assembled Length (-"XX.XX")



Polarized (-P "XX")


-ST8	1/8" (3.18)
-ST4	1/4" (6.35)
-ST2	1/2" (12.70)
-ST3	3/8" (19.53)

Stripped & Tinned (-ST "X")



Breakout starts with
Number 1 lead indicated
by brown wire or red stripe.
Shown on top side.


Breakout (-B "X")




Daisy Chain Single (-S "XX")



Reversed (-R)



Middle Reversed (-M)



Outside Reversed (-O)